


CAT 6 RISER CABLE


23/4 CMR/FT4 REEL IN BOX




SPEC SHEET




0E-CAT6RBL




0E-CAT6RBK



0E-CAT6RWH



0E-CAT6RYW



0E-CAT6RGN

Physical Characteristics

Conductor: 23 AWG Solid Bare Annealed Copper

Insulation: HDPE (High Density Polyethylene)

Conductor Color Code:

- Pair 1: Blue - White/Blue
- Pair 2: Orange - White/Orange
- Pair 3: Green - White/Green
- Pair 4: Brown - White/Brown

Spline: FR Polyolefin

Rip Cord: Applied longitudinally under jacket

Jacket: PVC (Flame-Retardant, SUN RES & RoHS Compliant)

Jacket Legend:

- 0000FT CAT 6 4 PR 23 AWG E507576 (UL) CMR c(UL)us FT4 SUN RES 75C (RoHS)
- UL VERIFIED TO TIA-568.2-D CAT 6 ##### RM# A B C D E F 1 2 3 4 5 6 7 8 9

Nominal Cable Diameter (in.): 0.232

Nominal Cable Net Weight (lbs./1000ft.): 27.60


Minimum Bend Radius (in.): 1.0

Maximum Pulling Force (lbs.): 25

Temperature Rating (°F):

- Installation: +32 to +140
- Storage & Operation: -4 to +167

Operating Voltage: 300V



Applications

IEEE802.3: 1000BASE-T, 100 BASE-TX,

10 BASE-T, ANSI/TIA/EIA 854:

1000BASE-TX, 155Mp/s, 1.2 Gb/s ATM,

ANSI x3.263: 100Mb/s, IEEE 802.3af

DTE Power (PoE),

Digital Video



For more information contact
your ADI Sales person or visit
adiglobal.com/adiexclusivebrands

CAT6 RISER CABLE

23/4 CMR/FT4 REEL IN BOX



Standard Compliance

- ANSI/TIA-568.2-D
- ANSI/TIA-862 (Building Automation)
- IEC 11801 Ed.2.0 (Class E)
- ICEA S-102-700 (Category 6)
- NEC/CEC Type CMR (UL 1666) for Riser
- UL 444
- RoHS Compliant Directive 2011/65/EU

Certifications



Certifications for Management System

ISO 9001: 2008, ISO 14001: 2004, OHSAS 18001

Electrical Characteristics

Max. Capacitance	Max. DC Resistance	Dielectric Strength	Characteristic Impedance
(nF/100m @ 1 kHz)	(Ω /100m @ 68°F)	(DC-kV, 2s)	(Ω 1~100 MHz)
5.6	9.38	2.5	100 \pm 15

Item	Attenuation at 20°C	NEXT	PS NEXT	ACRF	PS ACRF	Return Loss	PD	PD Skew	
Unit	dB/100m (Max.)	dB/100m (Min.)	dB/100m (Min.)	dB/100m (Min.)	dB/100m (Min.)	dB/100m (Min.)	ns/100m (Max.)	ns/100m (Max.)	
Transmission Characteristics	1 MHz	2.0	74.3	72.3	67.8	64.8	20.0	570	45
	4 MHz	3.8	65.3	63.3	55.8	52.8	23.0	552	45
	10 MHz	6.0	59.3	57.3	47.8	44.8	25.0	545	45
	16 MHz	7.6	56.2	54.2	43.7	40.7	25.0	543	45
	20 MHz	8.5	54.8	52.8	41.8	38.8	25.0	542	45
	31.25 MHz	10.7	51.9	49.9	37.9	34.9	23.6	540	45
	62.5 MHz	15.4	47.4	45.4	31.9	28.9	21.5	539	45
	100 MHz	19.8	44.3	42.3	27.8	24.8	20.1	538	45
	250 MHz	32.8	38.3	36.3	19.8	16.8	17.3	536	45
	300 MHz	36.4	37.1	35.1	18.3	15.3	16.8	536	45
400 MHz	43.0	35.3	33.3	15.8	12.8	15.9	536	45	

* Spec meets ANSI/TIA 568.2-D standard. Sweep tested to 400 MHz. All values are dB/100m (328 ft.)



For more information contact your ADI Sales person or visit adiglobal.com/adiexclusivebrands