

MAGNETIC LOCK 600 lbs HOLDING FORCE

0E-MAG600DB



This professional grade 600 lbs. Double Door Magnetic Lock is UL listed and finished in anodized aluminum. It is the perfection solution for many access control applications.

- 600 lbs. (272 kg) Holding Force per Door
- Designed for interior traffic control on out-swing doors
- Weather and Heavy duty vandal resistant construction
- Compatible with access/egress systems
- Locking mounting bolts
- On board MOV power surge protection prevents damage to mag lock
- 24 Month Warranty
- Performance Levels:
 - Destructive Attack: Level I
 - Standby Power: Level I
 - Line Security: Level I
 - Endurance: Level IV

- Product Certification:



PART #: **0E-MAG600DB**

UPC: **840049306349**

Voltage: 12/24 VDC

Current Draw: 2 x 510mA @ 12VDC
2 x 285mA @ 24VDC

Static Strength: 2 x 600 lbs. (Factory Tested)
2 x 500 lbs. (UL verified)

Dynamic Strength: 2 x 50 ft-lbs.

Temp. Range: 32°F - 131°F (0°C - 55°C)

Body Dimensions: 19-3/4"W x 2"H x 1-1/8"D
(500mm x 50mm x 29mm)

Armature Plate: 2 x 7-5/32"W x 1-3/4"H x 15/32"D
2 x (182mm x 44mm x 12mm)