

Data Sheet



HF45 Series

4.5" OD Commercial Filter Housings

- ✓ Available with pressure relief valves
- ✓ Made with durable Polypropylene
- ✓ Ideal for high flow applications



HYDRONIX HF45 SERIES COMMERCIAL FILTER HOUSINGS

are high durability commercial filter housings for 10" and 20" length cartridges. HF45 Series housings have excellent chemical resistance and are ideal for many high flow residential, commercial and light industrial applications.

HYDRONIX HF45 SERIES COMMERCIAL FILTER HOUSINGS

accept 4 1/2" diameter cartridges and feature larger ports to allow for a greater flow of liquid to pass through the housing. They are ideal for your larger capacity filtration needs and are made from durable Polypropylene.



This housing is tested and Certified by NSF International against NSF/ANSI Standard 42 for materials and structural integrity requirements.

COMPONENT

	Part Number	Description	Case Quantity	Box Dimension (Inches)	Weight (lbs)	Weight (kgs)
10" 3/4" PORT	HF45-10BLBK34	NSF 10" Blue 4.5" Body, 3/4" Black Cap	6	16 x 24 x 16	37	16.78
	HF45-10BLBK34PR	NSF 10" Blue 4.5" Body, 3/4" Black Cap w/PR	6	16 x 24 x 16	37	16.78
	HF45-10BKBK34	NSF 10" Black 4.5" Body, 3/4" Black Cap	6	16 x 24 x 16	37	16.78
	HF45-10BKBK34PR	NSF 10" Black 4.5" Body, 3/4" Black Cap w/PR	6	16 x 24 x 16	37	16.78
	HF45-10GRBK34PR	NSF 10" Grey 4.5" Body, 3/4" Black Cap w/PR	6	16 x 24 x 16	37	16.78
	HF45-10CLBK34	10" Clear 4.5" Body, 3/4" Black Cap	6	16 x 24 x 16	40	18.14
	HF45-10CLBK34PR	10" Clear 4.5" Body, 3/4" Black Cap w/PR	6	16 x 24 x 16	40	18.14
20"	HF45-20BLBK34	NSF 20" Blue 4.5" Body, 3/4" Black Cap	4	16 x 16 x 24	37	16.78
	HF45-20BLBK34PR	NSF 20" Blue 4.5" Body, 3/4" Black Cap w/PR	4	16 x 16 x 24	37	16.78
	HF45-20BKBK34	NSF 20" Black 4.5" Body, 3/4" Black Cap	4	16 x 16 x 24	37	16.78
3/4" PORT	HF45-20BKBK34PR	NSF 20" Black 4.5" Body, 3/4" Black Cap w/PR	4	16 x 16 x 24	37	16.78
	HF45-20GRBK34PR	NSF 20" Grey 4.5" Body, 3/4" Black Cap w/PR	4	16 x 16 x 24	37	16.78
	HF45-20CLBK34	20" Clear 4.5" Body, 3/4" Black Cap	4	16 x 16 x 24	40	18.14
	HF45-20CLBK34PR	20" Clear 4.5" Body, 3/4" Black Cap w/PR	4	16 x 16 x 24	40	18.14
10" 1" PORT	HF45-10BLBK10	NSF 10" Blue 4.5" Body, 1" Black Cap	6	16 x 24 x 16	37	16.78
	HF45-10BLBK10PR	NSF 10" Blue 4.5" Body, 1" Black Cap w/PR	6	16 x 24 x 16	37	16.78
	HF45-10BKBK10	NSF 10" Black 4.5" Body, 1" Black Cap	6	16 x 24 x 16	37	16.78
	HF45-10BKBK10PR	NSF 10" Black 4.5" Body, 1" Black Cap w/PR	6	16 x 24 x 16	37	16.78
	HF45-10GRBK10PR	NSF 10" Grey 4.5" Body, 1" Black Cap w/PR	6	16 x 24 x 16	37	16.78
	HF45-10CLBK10	10" Clear 4.5" Body, 1" Black Cap	6	16 x 24 x 16	40	18.14
	HF45-10CLBK10PR	10" Clear 4.5" Body, 1" Black Cap w/PR	6	16 x 24 x 16	40	18.14
20" 1" PORT	HF45-20BLBK10	NSF 20" Blue 4.5" Body, 1" Black Cap	4	16 x 16 x 24	37	16.78
	HF45-20BLBK10PR	NSF 20" Blue 4.5" Body, 1" Black Cap w/PR	4	16 x 16 x 24	37	16.78
	HF45-20BKBK10	NSF 20" Black 4.5" Body, 1" Black Cap	4	16 x 16 x 24	37	16.78
	HF45-20BKBK10PR	NSF 20" Black 4.5" Body, 1" Black Cap w/PR	4	16 x 16 x 24	37	16.78
	HF45-20GRBK10PR	NSF 20" Grey 4.5" Body, 1" Black Cap w/PR	4	16 x 16 x 24	37	16.78
	HF45-20CLBK10	20" Clear 4.5" Body, 1" Black Cap	4	16 x 16 x 24	40	18.14
	HF45-20CLBK10PR	20" Clear 4.5" Body, 1" Black Cap w/PR	4	16 x 16 x 24	40	18.14
10"	HF45-10BLBK15	NSF 10" Blue 4.5" Body, 1.5" Black Cap	6	16 x 24 x 16	37	16.78
1.5"	HF45-10BLBK15PR	NSF 10" Blue 4.5" Body, 1.5" Black Cap w/PR	6	16 x 24 x 16	37	16.78
PORT	HF45-10CLBK15	10" Clear 4.5" Body, 1.5" Black Cap	6	16 x 24 x 16	40	18.14
20"	HF45-20BLBK15	NSF 20" Blue 4.5" Body, 1.5" Black Cap	4	16 x 16 x 24	37	16.78
	HF45-20BLBK15PR	NSF 20" Blue 4.5" Body, 1.5" Black Cap w/PR	4	16 x 16 x 24	37	16.78
1.5" PORT	HF45-20CLBK15	20" Clear 4.5" Body, 1.5" Black Cap	4	16 x 16 x 24	40	18.14
	HF45-20CLBK15PR	20" Clear 4.5" Body, 1.5" Black Cap w/PR	4	16 x 16 x 24	40	18.14
)-Ring	HF45-ORING	Hydronix O-ring For HF45 Housing	-	-	-	_



HF45 SERIES

4.5" OD Commercial Filter Housings Data Sheet

Materials of Construction

Opaque Housing: Polypropylene
Clear Housing: Polycarbonate
Cap: Polypropylene
O-Ring: Buna-N
Button Assembly: Stainless Steel, EPDM


and Polypropylene

Applications


- Ice makersMisting Units
- Food Processing
- Food ProcessiAnalytical
- Wineries
- Reverse Osmosis
- Residential Plumbing
- Photography
- · Commercial Pre-filtration
- Beverage

Operating Data

Maximum Temperature: 100° F (37.7°C) Maximum Pressure: 90 psi (6.21 bar)



Model # Guide



Distributed by:



Installation Guidelines

WARNING: READ THESE INSTRUCTIONS BEFORE CHANGING OR INSTALLING. FOLLOW THESE INSTRUCTIONS TO REDUCE RISK OF DANGER.

Caution: filter housing must be protected against freezing and extreme temperatures. Filter housings should not be in direct contact with sunlight for a prolonged period of time since uv rays can make housings brittle. Pressure should always be measured before installation and water pressure regulators should be installed in the main line or in front of the housing if water pressure exceeds manufacturers' maximum water pressure: 90 psi. Installers should make sure filters and replacement filters are the correct length and are not too long so as to not cause undo strain and stress on the housing. A leak detector must be installed on all installations where high pressure, water hammer and pressure spikes are known or suspected to be present and on all installations where pressure is over 60 psi. Failure to the above may result in cracking of the filter housing, water leakage and water damage.

Caution: all filtration systems contain other parts that have a limited service life. Exhaustion of the service life of those parts often cannot be easily detected. Commonly, it is only after leakage has been observed or water damage has occurred that one is made aware that the service life has been exhausted.

Important notice: to prevent costly repairs or possible water damage we strongly recommend that the bowl or sump of all plastic housings be replaced periodically: every 5 years for clear sumps, and every 4 years for opaque sumps. If your sump has been in use for more than the recommended period, it should be replaced immediately. Be sure to date any new or replacement sump for future reference and indicate the next recommended replacement date.

Warranty: limited three (3) year warranty from the date of sale for material defects only. Warranty is limited to repair or replacement of product only. Any misuse, misinstallation, lack of maintenance, exceeding maximum pressure or failure to follow these instructions will void limited warranty.

DISCLAIMER OF WARRANTIES. Except as expressly warranted in writing by hydronix water technology, the goods sold by hydronix water technology are purchased by the buyer "as is." Hydronix water technology does not warrant that the goods are of merchantable quality or that they can be used for any particular purpose. Except as expressly warranted in writing by hydronix water technology, hydronix water technology makes no representation or warranty of any kind with respect to the products.

LIMITATION OF LIABILITY. In no event shall hydronix water technology be liable to the purchaser or any other entity for more than the invoice price received by hydronix water technology for any non-conforming products. Hydronix water technology shall not be liable to the purchaser or any other entity for personal injury, property damage, or any direct, indirect, special, incidental, consequential, punitive, exemplary, or other damages of any kind, including without limitation the cost of procurement of substitute goods, the loss of profits, products, or production, or the interruption of business, however caused and on any theory of liability, and whether or not hydronix water technology has been advised of the possibility of such damages. The essential purpose of this provision is to limit the liability of hydronix water technology arising out of the sale of products to the purchaser whether for breach of contract, negligence, or otherwise. These limitations shall apply notwithstanding any failure of essential purpose of any limited remedy and not withstanding the provisions of any other agreement between hydronix water technology and the purchaser.

WARNING: Do not use with water that is microbiologically unsafe or of unknown quality without adequate disinfection before or after the system.

This housing is tested and Certified by NSF International against NSF/ANSI Standard 42 for materials and structural integrity requirements.



*For the complete list of our NSF Certified products, please visit the Hydronix Water Technology page on the official NSF website: <u>www.nsf.org</u>



JUST ADD WATER™

P.O. Box 2235 Chino Hills, CA 91709 | USA sales@hydronixwater.com • www.HydronixWater.com