## **SPEC SHEET**



## MULTI-VOLTAGE RELAY MODULE

0E-FRLY24V10 SUITABLE FOR FIRE ALARM AND OTHER APPLICATIONS



OE-FRLY24V10 is an encapsulated multi-voltage relay suited to applications requiring a remote relay for control or status feedback. It includes long flying leads selectable for the input control voltage to be applied. A red LED indicates relay coil is energized. Applications include Fire Alarm Control, security systems, HVAC, temperature control, lighting systems and energy management. OE-FRLY24V10 is UL 864 listed for Fire Alarm Control Equipment. Includes mnting./wiring hardware.

- VOLTAGE INPUT: 24VDC, 24VAC ,120 VAC
- CURRENT DRAW: @24VDC = 15mA; @24VAC, 60HZ = 52mA; @120VAC, 60HZ = 38mA
- POLARIZED COIL INPUT: DC CONTROL INPUT ONLY
- CONTACTS: DRY FORM C SPDT
- CONTACT RATINGS: @5VDC = 250µA/ 0.35 P.F.;
  @24VDC = 7A/ 0.35 P.F.; @120VAC = 10A
- RED LED INDICATES RELAY COIL IS ENERGIZED
- WIRE TYPE: SIX (6) 12" 18AWG FLYING LEADS
- OPER. TEMP: 32°F TO 120°F (0°C TO 49°C), RH 93%

PART #:	0E-FRLY24V10
UPC:	811914027034
LENGTH: WIDTH: HEIGHT: WEIGHT:	<ul><li>1.5" (CASE ONLY)</li><li>1.2" (CASE ONLY)</li><li>0.8" (CASE ONLY)</li><li>2.4 OUNCES</li></ul>





FOR MORE INFORMATION, CONTACT YOUR ADI SALES PERSON.

wboxtech.com