

# Angle seat valve VZXF-L-M22C-M-B-N114-290-H3B1-50-7

FESTO

Part number: 1002540



## Data sheet

| Feature                          | Value  |
|----------------------------------|--|
| Type code                        | VZXF   |
| Structural design                | Poppet valve with piston actuator  |
| Actuation type                   | Pneumatic  |
| Sealing principle                | Soft   |
| Mounting position                | Any  |
| Type of mounting                 | Line installation  |
| Cable connection                 | Threaded sleeve 1 1/4 as per ANSI/ASME B 1.20.1  |
| Nominal width                    | 29 mm  |
| Valve function                   | 2/2, closed, monostable  |
| Flow direction                   | Non-reversible   |
| Medium pressure                  | 0 bar ... 7 bar  |
| Nominal pressure of fitting PN   | 16   |
| Exhaust air function             | Without flow control option  |
| Reset method                     | Mechanical spring  |
| Type of control                  | Externally controlled  |
| Pneumatic connection             | Internal thread G1/8   |
| Operating pressure               | 6 bar ... 10 bar   |
| Symbol                           | 00991367   |
| Medium                           | Vapor<br>Hydraulic fluid based on mineral oil<br>Inert gas<br>Mineral oil<br>Water<br>Filtered compressed air, 200 µm filter mesh<br>Neutral liquids |
| Flow direction                   | Under valve seat, for gaseous and liquid media   |
| Operating medium                 | Compressed air as per ISO 8573-1:2010 [7:4:4]  |
| Max. viscosity                   | 600 mm <sup>2</sup> /s   |
| Temperature of medium            | -10 °C ... 80 °C   |
| Ambient temperature              | -10 °C ... 60 °C   |
| Flow rate Kv                     | 6 m <sup>3</sup> /h  |
| Note on materials                | Contains paint-wetting impairment substances<br>RoHS-compliant   |
| Valve housing material           | Red brass  |
| Material number, fitting housing | CC499K   |
| Spindle seal material            | NBR  |
| Seat seal material               | PTFE   |
| Product weight                   | 1900 g   |

| <b>Feature</b>                             | <b>Value</b>                           |
|--|--|
| CE marking (see declaration of conformity) | as per EU pressure equipment directive |
| Corrosion resistance class (CRC)           | 1 - Low corrosion stress               |
| Drive housing material                     | Brass                                  |