



# Pneumatic valve VL-5/3E-3/4-D-4

Part number: 12464

FESTO



## Data sheet

Feature	Value
Type code	VL
Valve function	5/3, exhausted
Actuation type	Pneumatic
Width	76 mm
Standard nominal flow rate	4800 l/min
Pneumatic working port	Sub-base, size 4 as per ISO 5599-1 G3/4
Operating pressure	-0.9 bar ... 16 bar
Structural design	Piston gate valve
Reset method	Mechanical spring
Nominal width	18 mm
Width dimension	82 mm
Exhaust air function	With flow control option
Sealing principle	Soft
Mounting position	Any
Conforms to standard	ISO 5599-1
Manual override	None
ISO code	408
Type of control	Direct
Flow direction	Reversible
Symbol	00991021
Lap	Overlap
Pilot pressure	3 bar ... 16 bar
Switching time off	170 ms
On switching time	50 ms
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Temperature of medium	-10 °C ... 60 °C
Noise level	85 dB(A)
Pilot medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Ambient temperature	-10 °C ... 60 °C
Product weight	2000 g
Type of mounting	On sub-base With through-hole and screw
Pilot air port 12	Sub-base, size 4 as per ISO 5599-1
Pilot air port 14	Sub-base, size 4 as per ISO 5599-1

<b>Feature</b>	<b>Value</b>
Pneumatic connection 1	Sub-base, size 4 as per ISO 5599-1
Pneumatic connection 2	Sub-base, size 4 as per ISO 5599-1
Pneumatic connection 3	Sub-base, size 4 as per ISO 5599-1
Pneumatic connection 4	Sub-base, size 4 as per ISO 5599-1
Pneumatic connection 5	Sub-base, size 4 as per ISO 5599-1
Note on materials	RoHS-compliant
Seals material	NBR
Housing material	Aluminum