



Air solenoid valve MFH-5/3G-D-2-C

Part number: 151854

FESTO



Data sheet

| Feature | Value |
|--|--|
| Valve function | 5/3, closed |
| Actuation type | Electrical |
| Width | 54 mm |
| Standard nominal flow rate | 2300 l/min |
| Pneumatic working port | Sub-base, size 2 as per ISO 5599-1 G3/8 |
| Operating voltage | Via solenoid coil, to be ordered separately |
| Operating pressure | 3 bar ... 10 bar |
| Structural design | Piston gate valve |
| Reset method | Mechanical spring |
| Maritime classification | See certificate |
| Degree of protection | IP65 |
| Nominal width | 11.5 mm |
| Width dimension | 56 mm |
| Type code | MFH |
| Exhaust air function | With flow control option |
| Sealing principle | Soft |
| Mounting position | Any |
| Conforms to standard | ISO 5599-1 |
| Manual override | Detenting via accessory Non-detenting |
| ISO code | 256 |
| Type of control | Pilot-controlled |
| Pilot air supply port | Internal |
| Flow direction | Non-reversible |
| Symbol | 00991080 |
| Lap | Overlap |
| Switching time off | 63 ms |
| On switching time | 33 ms |
| Max. positive test pulse with 0 signal | 2200 µs |
| Max. negative test pulse on 1 signal | 3700 µs |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Vibration resistance | Transport application test with severity level 1 as per FN 942017-4 and EN 60068-2-6 |
| Shock resistance | Shock test with severity level 2 as per FN 942017-5 and EN 60068-2-27 |

| Feature | Value |
|---------------------------|--|
| Temperature of medium | -10 °C ... 60 °C |
| Noise level | 85 dB(A) |
| Ambient temperature | -5 °C ... 40 °C |
| Product weight | 820 g |
| Electrical connection | Via F coil, to be ordered separately |
| Type of mounting | On sub-base With through-hole and screw |
| Pilot exhaust air port 82 | M5 |
| Pilot exhaust air port 84 | M5 |
| Pneumatic connection 1 | Sub-base, size 2 as per ISO 5599-1 |
| Pneumatic connection 2 | Sub-base, size 2 as per ISO 5599-1 |
| Pneumatic connection 3 | Sub-base, size 2 as per ISO 5599-1 |
| Pneumatic connection 4 | Sub-base, size 2 as per ISO 5599-1 |
| Pneumatic connection 5 | Sub-base, size 2 as per ISO 5599-1 |
| Note on materials | RoHS-compliant |
| Seals material | HNBR NBR |
| Housing material | Die-cast aluminum |