

ISO cylinder DNC-32-80-PPV-A

Part number: 163308

FESTO



Data sheet

| Feature | Value |
|--|--|
| Stroke | 80 mm |
| Piston diameter | 32 mm |
| Piston rod thread | M10x1.25 |
| Type code | DNC |
| Cushioning | Pneumatic cushioning, adjustable at both ends |
| Mounting position | Any |
| Conforms to standard | ISO 15552 |
| Piston rod end | External thread |
| Structural design | Piston Piston rod Profile barrel |
| Position sensing | For proximity sensor |
| Symbol | 00991235 |
| Variants | Piston rod at one end |
| Operating pressure | 0.06 MPa ... 1.2 MPa |
| Operating pressure | 0.6 bar ... 12 bar |
| Mode of operation | Double-acting |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| Ambient temperature | -20 °C ... 80 °C |
| Impact energy in the end positions | 0.1 J |
| Cushioning length | 20 mm |
| Theoretical force at 6 bar, retracting | 415 N |
| Theoretical force at 6 bar, advancing | 483 N |
| Moving mass at 0 mm stroke | 162 g |
| Additional weight per 10 mm stroke | 30 g |
| Basic weight with 0 mm stroke | 517 g |
| Additional moving mass per 10 mm stroke | 9 g |
| Type of mounting | With internal thread With accessories |
| Pneumatic connection | G1/8 |
| Note on materials | RoHS-compliant |
| Cover material | Die-cast aluminum Coated |
| Seals material | TPE-U(PU) |
| Piston rod material | High-alloy steel |

| Feature | Value |
|-----------------------------|---|
| Material of cylinder barrel | Wrought aluminum alloy Smooth anodized |