


# Micro filter LFMA-1-D-MAXI-NPT

Part number: 173738

FESTO



## Data sheet

| Feature                                       | Value  |
|---|--|
| Series  | D  |
| Size  | Maxi   |
| Type code                                     | LFMA   |
| Grade of filtration                           | 0.01 µm  |
| Condensate drain                              | Manual, non-detenting                                      |
| Symbol  | 00991519   |
| Operating pressure                            | 1 bar ... 16 bar   |
| Operating medium                              | Compressed air as per ISO 8573-1:2010 [6:8:4]<br>Inert gas |
| Air quality class at the output               | Compressed air as per ISO 8573-1:2010 [1:7:2]<br>Inert gas |
| Max. standard flow rate for air quality class | 2200 l/min   |
| Min. standard flow rate for air quality class | 480 l/min  |
| Filter efficiency                             | 99.9999 %  |
| Bowl guard                                    | Metal bowl guard   |
| Corrosion resistance class (CRC)              | 2 - Moderate corrosion stress                              |
| Temperature of medium                         | 1.5 °C ... 60 °C   |
| Ambient temperature                           | -10 °C ... 60 °C   |
| Residual oil content                          | 0.01 mg/m <sup>3</sup>                                     |
| Type of mounting                              | Optionally:<br>Line installation<br>With mounting bracket  |
| Mounting position                             | Vertical   |
| Pneumatic connection 1                        | 1 NPT  |
| Pneumatic connection 2                        | 1 NPT  |
| Housing material                              | Die-cast zinc  |
| Compressed air filter material                | Borosilicate fiber   |
| Material of bowl                              | PC   |
| Note on materials                             | Free of copper and PTFE<br>RoHS-compliant                  |