


Proximity sensor SIES-Q8B-PS-S-L

Part number: 178295

FESTO



Data sheet

| Feature | Value |
|--|---|
| Type code | SIES |
| Conforms to standard | EN 60947-5-2 |
| Symbol | 00991701 |
| Certification | RCM compliance mark c UL us - Listed (OL) |
| CE marking (see declaration of conformity) | As per EU EMC directive |
| Note on materials | Free of copper and PTFE RoHS-compliant |
| Rated operating distance | 1.5 mm |
| Assured operating distance | 1.2 mm |
| Reduction factors | Aluminum = 0.45 Stainless steel St 18/8 = 0.8 Copper = 0.4 Brass = 0.55 Steel St 37 = 1.0 |
| Ambient temperature | -25 °C ... 70 °C |
| Repetition accuracy | 0.07 mm |
| Switching output | PNP |
| Switching element function | N/O contact |
| Max. switching frequency | 3500 Hz |
| Max. switching frequency DC | 1500 Hz |
| Max. output current | 200 mA |
| Voltage drop | 2 V |
| Short-circuit protection | Pulsed |
| DC operating voltage range | 10 V ... 30 V |
| Residual ripple | 10 % |
| Idle current | ≤10 mA |
| Reverse polarity protection | for all electrical connections |
| Electrical connection | 3-pin M8x1 Plug |
| Size | 8x8x59 mm |
| Type of mounting | With internal thread |
| Mounting type | Flush |
| Product weight | 12 g |
| Housing material | Die-cast zinc Chrome-plated Nickel-plated |

| Feature | Value |
|--|----------------|
| Switching status indication | LED yellow |
| Degree of protection | IP67 |
| Selection of additional sensor information | Special design |
| Electrical output | PNP |
| Selection of sensor version | Standard |