

Vacuum suction cup holder ESH-HCL-5-G

Part number: 189231

FESTO



Data sheet

Feature	Value
Suction cup holder height compensator	30 mm
Volume	6.06 cm ³
Type code	ESH
Mounting position	Vertical
Structural design	Vacuum connection at top with height compensation
Classification of suction cup holder	Size 5
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7::-]
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-10 °C ... 60 °C
Product weight	169 g
Type of mounting	With lock nut
Suction cup mounting	M10
Vacuum connection	G1/8
Note on materials	RoHS-compliant
Retaining bracket material	Aluminum Tempered steel High-alloy steel Brass, nickel-plated POM