


Ball valve actuator unit VZBA-1"-GGG-63-32L-F0405-V4V4T-PP30-R-90-C

FESTO

Part number: 1914789



Data sheet

Feature	Value
Type code	VZBA
Structural design	3-way ball valve Drilled L hole
Actuation type	Pneumatic
Mounting position	Any
Type of mounting	Line installation
Fitting connection	Rp1
Switching position indication	Slot direction = flow direction
Nominal width DN	25
Operating pressure	6 bar ... 8.4 bar
Nominal pressure of fitting PN	63
Symbol	00995329
Medium	Compressed air as per ISO 8573-1:2010 [:-:-] Inert gas Water – no water vapor Neutral liquids
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Temperature of medium	-10 °C ... 200 °C
Ambient temperature	-10 °C ... 80 °C
Flow rate Kv type L	11.8 m ³ /h
Max. surface temperature of assembly	TX
Explosion group of assembly	IIC, IIIC
Note on materials	Contains paint-wetting impairment substances RoHS-compliant
Housing material	High-alloy stainless steel
Material number of housing	1.4408
Seals material	PTFE PTFE-reinforced
Ball material	High-alloy stainless steel
Material number for ball	1.4408
Shaft material	High-alloy stainless steel
Material number for shaft	1.4401
Product weight	2650 g
Explosion prevention and protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)

Feature	Value
Explosive ambient temperature	-10°C ≤ Ta ≤ +60°C
Corrosion resistance class (CRC)	3 - High corrosion stress