

Proximity sensor SMTSO-8E-PS-M12-LED-24

Part number: 191986

FESTO



Data sheet

Feature	Value
Type code	SMTSO
Design	for T-slot
Symbol	00991153
Certification	RCM compliance mark
CE marking (see declaration of conformity)	As per EU EMC directive
Special features	Welding field resistant Resistant to welding spatter
Note on materials	Free of copper and PTFE
Measuring principle	Magneto-inductive
Ambient temperature	-25 °C ... 70 °C
Repetition accuracy	0.2 mm
Switching output	PNP
Switching element function	N/O contact
On time	38 ms
Switch-off time	20 ms
Max. output current	200 mA
Max. switching capacity DC	6 W
Voltage drop	≤1.8 V
Residual current	≤0.01 mA
Short-circuit protection	yes
Overload protection	Available
DC operating voltage range	10 V ... 30 V
Reverse polarity protection	for all electrical connections
Electrical connection 1, connection type	Plug
Electrical connection 1, connection technology	M12x1 A-coded as per EN 61076-2-101
Electrical connection 1, number of pins/wires	3
Electrical connection 1, type of mounting	Screw-type lock
Electrical connection for input 1, connection pattern	00995573
Connection outlet orientation	Transverse
Max. tightening torque plug	0.5 Nm
Type of mounting	With accessories
Product weight	19 g
Housing material	Wrought aluminum alloy PA TPE-U(PU) High-alloy stainless steel
Switching status indication	LED yellow

Feature	Value
Degree of protection	IP65 IP67
Resistance to interference from magnetic fields	45 - 65 Hz Alternating magnetic field