


# Mini slide DGSL-4-30-PA

Part number: 543912

FESTO



## Data sheet

Feature	Value
Stroke	30 mm
Adjustable end-position range/front length	25.5 mm
Adjustable end-position range/rear length	13.5 mm
Piston diameter	6 mm
Type code	DGSL
Drive unit operating mode	Yoke
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Guide	Ball bearing cage guide
Structural design	Yoke Piston Piston rod Slide
Position sensing	For proximity sensor
Symbol	00991263
Operating pressure	0.25 MPa ... 0.8 MPa
Operating pressure	2.5 bar ... 8 bar
Max. speed	0.5 m/s
Repetition accuracy	0.3 mm
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	0 - No corrosion stress
Ambient temperature	0 °C ... 60 °C
Impact energy in the end positions	0.015 J
Cushioning length	0.9 mm
Max. force F <sub>y</sub>	387 N
Max. force F <sub>z</sub>	387 N
Max. torque M <sub>x</sub>	2 Nm
Max. torque M <sub>y</sub>	2 Nm
Max. torque M <sub>z</sub>	2 Nm
Theoretical force at 6 bar, retracting	13 N
Theoretical force at 6 bar, advancing	17 N
Moving mass	38 g
Product weight	108 g
Alternative connections	See product drawing

<b>Feature</b>	<b>Value</b>
Type of mounting	With through-hole
Pneumatic connection	M3
Note on materials	Free of copper and PTFE RoHS-compliant
Cover material	Wrought aluminum alloy
Seals material	HNBR
Housing material	Wrought aluminum alloy
Piston rod material	High-alloy stainless steel