


Basic valve LFR-D-7-MIDI-A

Part number: 546464

FESTO



Data sheet



| Feature | Value |
|--|--|
| Size | Midi |
| Type code | LFR |
| Series | D |
| Actuator lock | Rotary knob with detent |
| Mounting position | Vertical +/- 5° |
| Grade of filtration | 40 µm |
| Condensate drain | Fully automatic |
| Structural design | Filter regulator with pressure gauge |
| Max. condensate volume | 42.983 ml |
| Bowl guard | Metal bowl guard |
| Symbol | 00991584 |
| Pressure gauge | G1/4 prepared |
| Operating pressure | 1.931 bar ... 12.411 bar |
| Pressure regulation range | 0.476 bar ... 7.239 bar |
| Max. pressure hysteresis | 0.207 bar |
| Standard nominal flow rate | 9343.22 l/min |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:9:-] Inert gas |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| Storage temperature | -10 °C ... 60 °C |
| Air quality class at the output | Compressed air as per ISO 8573-1:2010 [7:8:4] Inert gas |
| Temperature of medium | 5 °C ... 60 °C |
| Ambient temperature | 5 °C ... 60 °C |
| Product weight | 893.025 g |
| Type of mounting | Optionally: Line installation With accessories |
| Note on materials | RoHS-compliant |
| Housing material | Die-cast zinc |
| Material of bowl | PC |