


ISO cylinder DSNU-25-400-PPS-A

Part number: 559293

FESTO



Data sheet

| Feature | Value |
|--|--|
| Stroke | 400 mm |
| Piston diameter | 25 mm |
| Piston rod thread | M10x1.25 |
| Type code | DSNU |
| Cushioning | Self-adjusting pneumatic end-position cushioning |
| Mounting position | Any |
| Conforms to standard | CETOP RP 52 P ISO 6432 |
| Piston rod end | External thread |
| Structural design | Piston Piston rod Cylinder barrel |
| Position sensing | For proximity sensor |
| Symbol | 00992970 |
| Variants | Piston rod at one end |
| Operating pressure | 0.1 MPa ... 1 MPa |
| Operating pressure | 1 bar ... 10 bar |
| Mode of operation | Double-acting |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| Ambient temperature | -20 °C ... 80 °C |
| Impact energy in the end positions | 0.3 J |
| Cushioning length | 17 mm |
| Theoretical force at 6 bar, retracting | 247.4 N |
| Theoretical force at 6 bar, advancing | 294.5 N |
| Moving mass at 0 mm stroke | 71 g |
| Additional weight per 10 mm stroke | 11 g |
| Basic weight with 0 mm stroke | 238 g |
| Additional moving mass per 10 mm stroke | 6 g |
| Type of mounting | With accessories |
| Pneumatic connection | G1/8 |
| Note on materials | RoHS-compliant |
| Cover material | Wrought aluminum alloy Plain anodized |
| Seals material | NBR TPE-U(PU) |

| Feature | Value |
|-----------------------------|----------------------------|
| Piston rod material | High-alloy stainless steel |
| Material of cylinder barrel | High-alloy stainless steel |