



Parallel gripper HGPT-25-A-B

Part number: 560204

FESTO



Data sheet

Feature	Value
Size	25
Stroke per gripper jaw	6 mm
Max. interchangeability	≤0.2 mm
Max. gripper jaw angular play ax, ay	≤0.1 deg
Max. gripper jaw backlash Sz	≤0.02 mm
Rotational symmetry	≤0.2 mm
Pneumatic gripper repetition accuracy	≤0.04 mm
Type code	HGPT
Number of gripper jaws	2
Mounting position	Any
Mode of operation	Double-acting
Gripper function	Parallel
Structural design	Inclined plane Positively driven motion sequence
Position sensing	For proximity sensor
Symbol	00991894
Total gripping force at 6 bar, opening	266 N
Total gripping force at 6 bar, closing	248 N
Operating pressure	3 bar ... 8 bar
Operating pressure for sealing air	0 bar ... 0.5 bar
Max. operating frequency of pneumatic gripper	≤3 Hz
Min. opening time at 6 bar	26 ms
Min. closing time at 6 bar	32 ms
Max. mass per external gripper finger	110 g
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Degree of protection	IP40
Ambient temperature	5 °C ... 60 °C
Gripping force per gripper jaw at 6 bar, opening	133 N
Gripping force per gripper jaw at 6 bar, closing	124 N
Mass moment of inertia	0.983 kgcm ²
Maximum force on gripper jaw Fz, static	1200 N
Maximum torque on gripper jaw, Mx static	50 Nm
Maximum torque on gripper jaw, My static	45 Nm
Maximum torque on gripper jaw, Mz static	35 Nm

Feature	Value
Relubrication interval for guidance elements	5 MioCyc
Product weight	266 g
Type of mounting	Optionally: With internal thread and centering sleeve Via through-hole and centering sleeve With through-hole and dowel pin With internal thread and dowel pin
Sealing air pneumatic connection	M5
Pneumatic connection	M5
Note on materials	Free of copper and PTFE RoHS-compliant
Cover cap material	High-alloy stainless steel
Housing material	Aluminum Anodized
Gripper jaw material	Steel Hardened