


Fork light barrier SOOF-M-FL-SM-C80-P

Part number: 553557

FESTO



Data sheet

Feature	Value
Type code	SOOF
Symbol	00995956
Certification	RCM compliance mark c UL us - Listed (OL)
CE marking (see declaration of conformity)	As per EU EMC directive
Note on materials	Contains paint-wetting impairment substances RoHS-compliant
Measured variable	Position
Measuring principle	Optoelectronic
Method of measurement	Fork light barrier
Type of light	Red
Minimum object diameter	0.3 mm
Note on min. object diameter	0.2 mm with high resolution mode 1.0 mm with power mode 0.3 mm with speed mode 0.3 mm with standard mode
Ambient temperature	-25 °C ... 60 °C
Repetition accuracy	0.02 mm
Switching output	Push-pull NPN PNP
Switching element function	Switchable
Hysteresis	≤0.1 mm
Max. switching frequency	5000 Hz
Note on switching frequency	1500 Hz with high resolution mode 8000 Hz with speed mode 5000 Hz with standard mode 250 Hz with power mode
Max. output current	100 mA
Timer function	Via IO-Link®
Short-circuit protection	Pulsed
Protocol	IO-Link®
IO-Link®, protocol version	Device V 1.1
IO-Link®, profile	Smart sensor profile
IO-Link®, function classes	Teach channel Binary data channel (BDC) Diagnostics Process data variable (PDV) Identification
IO-Link®, communication mode	COM2 (38,4 kBd)

Feature	Value
IO-Link®, SIO mode support	Yes
IO-Link®, port class	A
IO-Link®, process data width OUT	0 Byte
IO-Link®, process data width IN	2 Byte
IO-Link®, process data content IN	12 bit PDV (signal level) 1 bit BDC (stability) 1 bit BDC (switching signal)
IO-Link®, service data contents IN	32 bit switching counter 16 bit maximum signal level 16 bit temperature 16 bit minimum signal level 8 bit teach-in quality
IO-Link®, minimum cycle time	2.3 ms
IO-Link®, data memory required	73 byte
DC operating voltage range	10 V ... 30 V
Residual ripple	± 5 %
Idle current	30 mA
Reverse polarity protection	for all electrical connections
Electrical connection	3-pin M8x1 Plug
Size	Clevis 80x55 mm
Fork gap	80 mm
Product weight	118 g
Housing material	Die-cast metal, coated
Switching status indication	LED yellow
Setting options	IO-Link® Potentiometer
Degree of protection	IP67
Insulation voltage	500 V
Surge resistance	0.8 kV
Corrosion resistance class (CRC)	0 - No corrosion stress
Contamination level	3