



Air solenoid valve

VUVG-B14-T32U-AZT-F-1P3

FESTO

Part number: 566514



Data sheet

| Feature | Value |
|--|--|
| Valve function | 2x3/2, open, monostable |
| Actuation type | Electrical |
| Valve size | 14 mm |
| Standard nominal flow rate | 510 l/min ... 580 l/min |
| Pneumatic working port | Flange |
| Operating voltage | 24V DC |
| Operating pressure | 0.15 MPa ... 1 MPa |
| Operating pressure | 1.5 bar ... 10 bar |
| Structural design | Piston gate valve |
| Reset method | Pneumatic spring |
| Certification | RCM compliance mark c UL us - Recognized (OL) |
| Degree of protection | IP40 IP65 With plug socket |
| Nominal width | 4.6 mm |
| Type code | VUVG |
| Exhaust air function | With flow control option |
| Sealing principle | Soft |
| Mounting position | Any |
| Manual override | Detenting Non-detenting Covered |
| Type of control | Pilot-controlled |
| Pilot air supply port | External |
| Symbol | 00992906 |
| Lap | Overlap |
| Pilot pressure MPa | 0.15 MPa ... 0.8 MPa |
| Pilot pressure | 1.5 bar ... 8 bar |
| Suitability for vacuum | no |
| Switching time off | 25 ms |
| On switching time | 9 ms |
| Duty cycle | 100% |
| Max. positive test pulse with 0 signal | 700 µs |
| Max. negative test pulse on 1 signal | 900 µs |
| Coil characteristics | 24 V DC: 1.0 W 24 V DC: low-current phase 0.3 W, high-current phase 1.0 W |

| Feature | Value |
|--|--|
| Permissible voltage fluctuations | +/- 10 % |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Vibration resistance | Transport application test with severity level 2 as per FN 942017-4 and EN 60068-2-6 |
| Restricted ambient and media temperature | -5 - 50 °C Without holding power reduction |
| Shock resistance | Shock test with severity level 2 as per FN 942017-5 and EN 60068-2-27 |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| Temperature of medium | -5 °C ... 60 °C |
| Pilot medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Ambient temperature | -5 °C ... 60 °C |
| Product weight | 89 g |
| Electrical connection | Via electrical sub-base |
| Type of mounting | On terminal strip |
| Note on materials | RoHS-compliant |
| Seals material | HNBR NBR |
| Housing material | Wrought aluminum alloy |