



Air solenoid valve VSCS-B-M32-MD-WA-3AC1

FESTO

Part number: 571065



Data sheet

Feature	Value
Valve function	3/2, closed, monostable
Actuation type	Electrical
Width	15 mm
Standard nominal flow rate	18 l/min
Pneumatic working port	Sub-base, size 15 mm as per ISO 15218
Operating voltage	230V AC
Operating pressure	0 MPa ... 1 MPa
Operating pressure	0 psi ... 145 psi
Reset method	Mechanical spring
CE marking (see declaration of conformity)	As per EU low voltage directive
Degree of protection	IP65
Type code	VSCS
Sealing principle	Soft
Mounting position	Any
Conforms to standard	ISO 15218
Manual override	Detenting Non-detenting
Type of control	Direct
Flow direction	Non-reversible
Symbol	00991308
Lap	Underlap
Note on forced dynamization	Switching frequency at least once a week
Switching time off	6 ms
On switching time	6 ms
Duty cycle	100%
Coil characteristics	230 V AC: 50/60 Hz, initial power 2.9 VA, holding power 2.1 VA
Permissible voltage fluctuations	-15 % / +10 %
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Vibration resistance	Transport application test with severity level 2 as per FN 942017-4 and EN 60068-2-6
Shock resistance	Shock test with severity level 2 as per FN 942017-5 and EN 60068-2-27
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Temperature of medium	-10 °C ... 50 °C
Ambient temperature	-10 °C ... 50 °C

Feature	Value
Electrical connection	Form C as per DIN EN 175301-803
Pneumatic connection 1	Sub-base
Pneumatic connection 2	Sub-base
Pneumatic connection 3	Sub-base
Note on materials	RoHS-compliant
Seals material	NBR