

Solenoid coil VACN-N-K11-1-0.5-U4-M

Part number: 8029146

FESTO



Data sheet

Feature	Value
Type code	VACN
Actuation type	Electrical
Mounting position	Any
Duty cycle	100%
Insulation class	H
Enameled wire insulation class	H
Coil characteristics	24 V DC: 4.6 W
Permissible voltage fluctuations	+/- 10 %
Maritime classification	See certificate
Explosion protection certification outside the EU	Class I, Div. 1 (CA) Class I, Div. 1 (US) Class I, Div. 2 (CA) Class II, Div. 1 (CA) Class II, Div. 1 (US) Class III, Div. 1 (CA) Class III, Div. 1 (US) EPL Gb (US)
Explosion prevention and protection	Zone 1 (US) Class I, Div. 1 (CA) Class I, Div. 2 (CA) Class II, Div. 1 (CA) Class III, Div. 1 (CA) Class I, Div. 1 (US) Class II, Div. 1 (US) Class III, Div. 1 (US)
Certificate issuing authority	CSA 265489 DNVGL-TAA000011J FM 3053936
Type of ignition protection for gas	AEx m II T4 Ex m II T4
Explosive ambient temperature	-20°C ≤ Ta ≤ +60°C
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Degree of protection	IP65
Ambient temperature	-20 °C ... 60 °C
Product weight	207 g
Electrical connection	Cable
Cable length	0.61 m
Type of mounting	With knurled nut
Note on materials	Contains paint-wetting impairment substances RoHS-compliant

Feature	Value
Housing material	Polymer Steel
Material of winding	Copper