

Connecting cable NEBC-R3G4-ES-1-S-R3G4-ET

Part number: 8040455

FESTO



Data sheet

Feature	Value
Type code	NEBC
Cable designation	With label holder
Contact durability	50
Product weight	89.5 g
Electrical connection 1, function	Field device end
Electrical connection 1, design	Rectangular
Electrical connection 1, connection type	Plug
Electrical connection 1, cable outlet	Straight
Electrical connection 1, connection technology	RJ45 as per IEC 60603-7-3
Electrical connection 1, number of pins/wires	8
Electrical connection 1, occupied pins/wires	4
Electrical connection 1, type of mounting	Snap-locking
Electrical connection for input 1, connection pattern	00995653
Electrical connection 2, function	Control side
Electrical connection 2, design	Rectangular
Electrical connection 2, connection type	Plug
Electrical connection 2, cable outlet	Straight
Electrical connection 2, connection technology	RJ45 as per IEC 60603-7-3
Electrical connection 2, number of pins/wires	8
Electrical connection 2, occupied pins/wires	4
Electrical connection 2, type of mounting	Snap-locking
DC operating voltage range	0 V ... 30 V
Current rating at 40°C	1.3 A
Surge resistance	0.8 kV
Note on surge resistance	Due to screening, a leakage flow of up to 20 mA is permissible.
Transmission characteristics	In accordance with category 5, EN 50173, class D According to category 5, ISO/IEC 11801, class D
Ethernet cable specification	Typ: CAT.5
Cable length	1 m
Cable characteristic	Suitable for energy chains
Connector cable test conditions	Flexural strength: as per Festo standard Test conditions on request Cable chain: 2 million cycles, bending radius 100 mm
Bending radius, fixed cable installation	≥40 mm
Bending radius, flexible cable installation	≥100 mm
Cable diameter	6.7 mm

Feature	Value
Cable diameter tolerance	± 0.3 mm
Cable design	4 x 0.34 mm ² (star quad)
Nominal conductor cross section	0.34 mm ²
Nominal conductor cross section	AWG22
Degree of protection	IP20
Special features	Oil-resistant
Ambient temperature	-25 °C ... 80 °C
Ambient temperature with flexible cable installation	-20 °C ... 60 °C
Storage temperature	-25 °C ... 80 °C
CE marking (see declaration of conformity)	As per EU RoHS directive
Note on materials	Free of copper and PTFE RoHS-compliant
Contamination level	3
Corrosion resistance class (CRC)	1 - Low corrosion stress
Material of cable sheath	TPE-U(PUR)
Color cable sheath	Green
Housing material	Brass, nickel-plated PA
Housing colour	Black
Material of pin contacts	Brass Gold-plated
Insulating sheath material	PE