


Air solenoid valve

VUVS-LT30-M32U-MD-N38-F8

FESTO

Part number: 8036723



Data sheet

| Feature | Value |
|------------------------------------------|--------------------------------------------------------------------------------------|
| Valve function | 3/2, open, monostable |
| Actuation type | Electrical |
| Valve size | 31 mm |
| Standard nominal flow rate | 1600 l/min |
| Pneumatic working port | 3/8 NPT |
| Operating voltage | Via solenoid coil, to be ordered separately |
| Operating pressure | 2.5 bar ... 10 bar |
| Structural design | Plate seat |
| Reset method | Mechanical spring |
| Certification | c UL us - Recognized (OL) |
| Nominal width | 7.9 mm |
| Type code | VUVS |
| Exhaust air function | With flow control option |
| Sealing principle | Soft |
| Mounting position | Any |
| Manual override | Detenting Non-detenting |
| Type of control | Pilot-controlled |
| Pilot air supply port | Internal |
| Flow direction | Non-reversible |
| Symbol | 00991140 |
| Lap | Underlap |
| b-value | 0.2 |
| C value | 7 l/sbar |
| Switching time off | 36 ms |
| On switching time | 14 ms |
| Max. positive test pulse with 0 signal | 2000 µs |
| Max. negative test pulse on 1 signal | 3600 µs |
| Coil characteristics | See solenoid coil, to be ordered separately |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Vibration resistance | Transport application test with severity level 2 as per FN 942017-4 and EN 60068-2-6 |
| Shock resistance | Shock test with severity level 2 as per FN 942017-5 and EN 60068-2-27 |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| Temperature of medium | -10 °C ... 60 °C |

| Feature | Value |
|---------------------------|-------------------------------------------------------|
| Pilot medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Ambient temperature | -10 °C ... 60 °C |
| Product weight | 305 g |
| Type of mounting | Optionally: On terminal strip With through-hole |
| Venting hole connection | Not ducted |
| Pilot exhaust air port 82 | 10-32 UNF-2B |
| Pneumatic connection 1 | 3/8 NPT |
| Pneumatic connection 2 | 3/8 NPT |
| Pneumatic connection 3 | 3/8 NPT |
| Note on materials | RoHS-compliant |
| Seals material | HNBR NBR TPE-U(PU) |
| Housing material | Die cast aluminum, painted |
| Piston slide material | Wrought aluminum alloy |
| Material of screws | Steel, galvanized |