


Connecting cable NEBV-Z4WA2L-P-E-10-N-LE2-S1

Part number: 8047670

FESTO



Data sheet

Feature	Value
Type code	NEBV
Signal status display	LED yellow
Additional functions	Protective circuit
Cable designation	Without label holder
Contact durability	50
Product weight	170 g
Electrical connection 1, function	Field device end
Electrical connection 1, design	Rectangular
Electrical connection 1, connection type	Socket
Electrical connection 1, cable outlet	Angled
Electrical connection 1, connection technology	Connection diagram ZC, metric screw
Electrical connection 1, number of pins/wires	2
Electrical connection 1, occupied pins/wires	2
Electrical connection 1, type of mounting	On air solenoid valve with M2 central screw
Electrical connection for input 1, connection pattern	00995625
Electrical connection 2, function	Control side
Electrical connection 2, connection type	Cable
Electrical connection 2, connection technology	Open end
Electrical connection 2, number of pins/wires	2
Electrical connection 2, occupied pins/wires	2
DC operating voltage range	20.4 V ... 26.4 V
Nominal operating voltage DC	24 V
Surge resistance	2.4 kV
Reverse polarity protection	Bipolar
Protective earth connection	Not available
Cable length	10 m
Cable characteristic	Suitable for energy chains
Connector cable test conditions	Test conditions on request
Bending radius, flexible cable installation	≥29 mm
Cable diameter	2.9 mm
Cable diameter tolerance	± 0.1 mm
Cable design	2 x 0.14 mm ²
Nominal conductor cross section	0.14 mm ²

Feature	Value
Degree of protection	IP65
Note on degree of protection	In mounted state
Ambient temperature	-10 °C ... 50 °C
CE marking (see declaration of conformity)	As per EU RoHS directive
Note on materials	RoHS-compliant
Contamination level	3
Corrosion resistance class (CRC)	3 - High corrosion stress
Material of cable sheath	TPE-U(PUR)
Color cable sheath	Gray
Housing material	TPE-U(PU)
Housing colour	Black
Material of screws	Stainless steel
Material of pin contacts	Copper alloy, tin-plated
Insulating sheath material	PP