


# Connecting cable NEBL-M8G4-E-7.5-N-LE4

Part number: 8065113

FESTO



## Data sheet

Feature	Value
Type code	NEBL
Conforms to standard	EN 61076-2-104
Explosion prevention and protection	Observe the information on the certificate Zone 2 (ATEX) Zone 22 (ATEX)
Cable designation	Without label holder
Product weight	269 g
Electrical connection 1, function	Field device end
Electrical connection 1, design	Round
Electrical connection 1, connection type	Socket
Electrical connection 1, cable outlet	Straight
Electrical connection 1, connection technology	M8x1 A-coded as per EN 61076-2-104
Electrical connection 1, number of pins/wires	4
Electrical connection 1, occupied pins/wires	4
Electrical connection 1, type of mounting	Screw-type lock with hexagon AF 9 and longitudinal knurl
Electrical connection for input 1, connection pattern	00991872
Electrical connection 2, function	Control side
Electrical connection 2, connection type	Cable
Electrical connection 2, connection technology	Open end
Electrical connection 2, number of pins/wires	4
Electrical connection 2, occupied pins/wires	4
DC operating voltage range	0 V ... 30 V
Nominal operating voltage DC	24 V
Operating voltage range AC	0 V ... 30 V
Nominal operating voltage AC	24 V
Current rating at 40°C	5.6 A
Note on acceptable current load at 40°C	5.3 A at 60°C
Surge resistance	0.8 kV
Protective earth connection	Not available
Shield	no
Cable length	7.5 m
Cable characteristic	Suitable for energy chains
Connector cable test conditions	Test conditions on request
Bending radius, fixed cable installation	≥15 mm

Feature	Value
Bending radius, flexible cable installation	≥50 mm
Cable diameter	4.8 mm
Cable diameter tolerance	± 0.15 mm
Cable design	4 x 0.5 mm <sup>2</sup>
Nominal conductor cross section	0.5 mm <sup>2</sup>
Wire ends	Stripped Cut off bluntly
Degree of protection	IP65 IP67 IP69K
Note on degree of protection	In mounted state
Special features	Oil-resistant
Ambient temperature	-40 °C ... 85 °C
Ambient temperature with flexible cable installation	-20 °C ... 85 °C
Storage temperature	-40 °C ... 85 °C
Note on materials	RoHS-compliant Halogen-free
Contamination level	3
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Material of cable sheath	TPE-U(PUR)
Color cable sheath	Black
Housing material	TPE-U(PUR)
Housing colour	Black
Material of screw-type lock	Brass, nickel-plated
Seals material	FPM
Material of pin contacts	Copper alloy, gold-plated
Insulating sheath material	PP