




# SAFETY DATA SHEET

## 1. Identification

<b>Product identifier</b>	<b>Food Grade Penetrating Oil - 11 oz</b>
<b>Other means of identification</b>	
<b>Product Code</b>	No. 03086 (Item# 1003355)
<b>Recommended use</b>	Machine oil and lubricant
<b>Recommended restrictions</b>	None known.
<b>Manufacturer/Importer/Supplier/Distributor information</b>	
<b>Manufactured or sold by:</b>	
<b>Company name</b>	CRC Industries, Inc.
<b>Address</b>	885 Louis Dr. Warminster, PA 18974 US
<b>Telephone</b>	
<b>General Information</b>	215-674-4300
<b>Technical Assistance</b>	800-521-3168
<b>Customer Service</b>	800-272-4620
<b>24-Hour Emergency (CHEMTREC)</b>	800-424-9300 (US)
<b>Website</b>	www.crcindustries.com

## 2. Hazard(s) identification

<b>Physical hazards</b>	Flammable aerosols Gases under pressure	Category 2 Compressed gas
<b>Health hazards</b>	Aspiration hazard	Category 1
<b>Environmental hazards</b>	Not classified.	
<b>OSHA defined hazards</b>	Not classified.	
<b>Label elements</b>		

<b>Signal word</b>	Danger
<b>Hazard statement</b>	Flammable aerosol. Contains gas under pressure; may explode if heated. May be fatal if swallowed and enters airways.
<b>Precautionary statement</b>	
<b>Prevention</b>	Keep away from heat/sparks/open flames/hot surfaces. - No smoking. Do not spray on an open flame or other ignition source. Pressurized container: Do not pierce or burn, even after use. Use with adequate ventilation. Open doors and windows or use other means to ensure a fresh air supply during use and while product is drying. If you experience any symptoms listed on this label, increase ventilation or leave the area.
<b>Response</b>	If swallowed: Immediately call a poison center/doctor. Do NOT induce vomiting.
<b>Storage</b>	Store locked up. Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F. Exposure to high temperature may cause can to burst.
<b>Disposal</b>	Dispose of contents/container in accordance with local/regional/national/international regulations.
<b>Hazard(s) not otherwise classified (HNOC)</b>	None known.
<b>Supplemental information</b>	None.

## 3. Composition/information on ingredients

### Mixtures

Chemical name	Common name and synonyms	CAS number	%
distillates (petroleum), hydrotreated light		64742-47-8	60 - 70
white mineral oil		8042-47-5	30 - 40
carbon dioxide		124-38-9	1 - 3

Specific chemical identity and/or percentage of composition has been withheld as a trade secret.

#### 4. First-aid measures

<b>Inhalation</b>	Move to fresh air. Call a physician if symptoms develop or persist.
<b>Skin contact</b>	Rinse with water. Get medical attention if irritation develops and persists.
<b>Eye contact</b>	Rinse with water. Get medical attention if irritation develops and persists.
<b>Ingestion</b>	Call a physician or poison control center immediately. Rinse mouth. Do not induce vomiting. If vomiting occurs, keep head low so that stomach content doesn't get into the lungs.
<b>Most important symptoms/effects, acute and delayed</b>	Aspiration may cause pulmonary edema and pneumonitis. Headache. Nausea, vomiting. Diarrhea.
<b>Indication of immediate medical attention and special treatment needed</b>	Provide general supportive measures and treat symptomatically. Keep victim under observation. Symptoms may be delayed.
<b>General information</b>	Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves.

#### 5. Fire-fighting measures

<b>Suitable extinguishing media</b>	Water fog. Alcohol resistant foam. Dry chemical powder. Dry chemicals. Carbon dioxide (CO2).
<b>Unsuitable extinguishing media</b>	Do not use water jet as an extinguisher, as this will spread the fire.
<b>Specific hazards arising from the chemical</b>	Contents under pressure. Pressurized container may rupture when exposed to heat or flame. During fire, gases hazardous to health may be formed.
<b>Special protective equipment and precautions for firefighters</b>	Firefighters must use standard protective equipment including flame retardant coat, helmet with face shield, gloves, rubber boots, and in enclosed spaces, SCBA.
<b>Fire-fighting equipment/instructions</b>	In case of fire: Stop leak if safe to do so. Move containers from fire area if you can do so without risk. Cool containers exposed to heat with water spray and remove container, if no risk is involved. Containers should be cooled with water to prevent vapor pressure build up. Use standard firefighting procedures and consider the hazards of other involved materials. In the event of fire and/or explosion do not breathe fumes.
<b>General fire hazards</b>	Flammable aerosol. Contents under pressure. Pressurized container may rupture when exposed to heat or flame. Will burn if involved in a fire.

#### 6. Accidental release measures

<b>Personal precautions, protective equipment and emergency procedures</b>	Keep unnecessary personnel away. Keep people away from and upwind of spill/leak. Keep out of low areas. Many gases are heavier than air and will spread along ground and collect in low or confined areas (sewers, basements, tanks). Wear appropriate protective equipment and clothing during clean-up. Emergency personnel need self-contained breathing equipment. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Ventilate closed spaces before entering them. Local authorities should be advised if significant spillages cannot be contained. For personal protection, see section 8 of the SDS.
<b>Methods and materials for containment and cleaning up</b>	Eliminate all ignition sources (no smoking, flares, sparks, or flames in immediate area). Keep combustibles (wood, paper, oil, etc.) away from spilled material. This product is miscible in water. This material is classified as a water pollutant under the Clean Water Act and should be prevented from contaminating soil or from entering sewage and drainage systems which lead to waterways. Stop the flow of material, if this is without risk. Wipe up with absorbent material (e.g. cloth, fleece). Clean surface thoroughly to remove residual contamination. For waste disposal, see section 13 of the SDS.
<b>Environmental precautions</b>	Avoid discharge into drains, water courses or onto the ground.

## 7. Handling and storage

### Precautions for safe handling

Pressurized container: Do not pierce or burn, even after use. Do not use if spray button is missing or defective. Do not spray on a naked flame or any other incandescent material. Do not smoke while using or until sprayed surface is thoroughly dry. Do not cut, weld, solder, drill, grind, or expose containers to heat, flame, sparks, or other sources of ignition. Use caution around energized equipment. The metal container will conduct electricity if it contacts a live source. This may result in injury to the user from electrical shock and/or flash fire. Avoid prolonged or repeated contact with skin. Avoid prolonged exposure. Use only in well-ventilated areas. Wear appropriate personal protective equipment. Wash hands thoroughly after handling. Observe good industrial hygiene practices. For product usage instructions, see the product label.

### Conditions for safe storage, including any incompatibilities

Level 3 Aerosol.

Pressurized container. Protect from sunlight and do not expose to temperatures exceeding 50°C/122 °F. Do not puncture, incinerate or crush. Do not handle or store near an open flame, heat or other sources of ignition. This material can accumulate static charge which may cause spark and become an ignition source. Store in tightly closed container. Store in a well-ventilated place. Stored containers should be periodically checked for general condition and leakage. Store away from incompatible materials (see Section 10 of the SDS).

## 8. Exposure controls/personal protection

### Occupational exposure limits

#### US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)

Components	Type	Value	Form
carbon dioxide (CAS 124-38-9)	PEL	9000 mg/m3	
		5000 ppm	
white mineral oil (CAS 8042-47-5)	PEL	5 mg/m3	Mist.

#### US. ACGIH Threshold Limit Values

Components	Type	Value	Form
carbon dioxide (CAS 124-38-9)	STEL	30000 ppm	
	TWA	5000 ppm	
white mineral oil (CAS 8042-47-5)	TWA	5 mg/m3	Inhalable fraction.

#### US. NIOSH: Pocket Guide to Chemical Hazards

Components	Type	Value	Form
carbon dioxide (CAS 124-38-9)	STEL	54000 mg/m3	
		30000 ppm	
	TWA	9000 mg/m3	
		5000 ppm	
distillates (petroleum), hydrotreated light (CAS 64742-47-8)	TWA	100 mg/m3	
white mineral oil (CAS 8042-47-5)	STEL	10 mg/m3	Mist.
	TWA	5 mg/m3	Mist.

### Biological limit values

No biological exposure limits noted for the ingredient(s).

### Appropriate engineering controls

Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level.

### Individual protection measures, such as personal protective equipment

#### Eye/face protection

Wear safety glasses with side shields (or goggles).

#### Skin protection

##### Hand protection

Wear protective gloves such as: Nitrile. Neoprene.

<b>Other</b>	Wear suitable protective clothing.
<b>Respiratory protection</b>	If engineering controls are not feasible or if exposure exceeds the applicable exposure limits, use a NIOSH-approved cartridge respirator with an organic vapor cartridge. Use a self-contained breathing apparatus in confined spaces and for emergencies. Air monitoring is needed to determine actual employee exposure levels.
<b>Thermal hazards</b>	Wear appropriate thermal protective clothing, when necessary.
<b>General hygiene considerations</b>	When using do not smoke. Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants.

---

## 9. Physical and chemical properties

### Appearance

<b>Physical state</b>	Liquid.
<b>Form</b>	Aerosol.
<b>Color</b>	Clear.
<b>Odor</b>	Odorless.
<b>Odor threshold</b>	Not available.
<b>pH</b>	Not available.
<b>Melting point/freezing point</b>	-76 °F (-60 °C) estimated
<b>Initial boiling point and boiling range</b>	432 °F (222.2 °C) estimated
<b>Flash point</b>	200.0 °F (93.3 °C) Setafash
<b>Evaporation rate</b>	Very slow.
<b>Flammability (solid, gas)</b>	Not available.
<b>Upper/lower flammability or explosive limits</b>	
<b>Flammability limit - lower (%)</b>	0.5 % estimated
<b>Flammability limit - upper (%)</b>	5.5 % estimated
<b>Vapor pressure</b>	1625.2 hPa estimated
<b>Vapor density</b>	> 1 (air = 1)
<b>Relative density</b>	0.82 estimated
<b>Solubility(ies)</b>	
<b>Solubility (water)</b>	Negligible.
<b>Partition coefficient (n-octanol/water)</b>	Not available.
<b>Auto-ignition temperature</b>	428 °F (220 °C) estimated
<b>Decomposition temperature</b>	Not available.
<b>Viscosity</b>	Not available.
<b>Percent volatile</b>	97.5 % estimated

---

## 10. Stability and reactivity

<b>Reactivity</b>	The product is stable and non-reactive under normal conditions of use, storage and transport.
<b>Chemical stability</b>	Material is stable under normal conditions.
<b>Possibility of hazardous reactions</b>	No dangerous reaction known under conditions of normal use.
<b>Conditions to avoid</b>	Heat, flames and sparks. Contact with incompatible materials.
<b>Incompatible materials</b>	Strong oxidizing agents.
<b>Hazardous decomposition products</b>	Carbon oxides.

---

## 11. Toxicological information

### Information on likely routes of exposure

<b>Inhalation</b>	Prolonged inhalation may be harmful.
-------------------	--------------------------------------

**Skin contact** Based on available data, the classification criteria are not met.

**Eye contact** Based on available data, the classification criteria are not met.

**Ingestion** Droplets of the product aspirated into the lungs through ingestion or vomiting may cause a serious chemical pneumonia.

**Symptoms related to the physical, chemical and toxicological characteristics** Aspiration may cause pulmonary edema and pneumonitis. Headache. Nausea, vomiting. Diarrhea.

**Information on toxicological effects**

**Acute toxicity** May be fatal if swallowed and enters airways.

Product	Species	Test Results
Food Grade Penetrating Oil - 11 oz		
<b>Acute</b>		
<b>Dermal</b>		
LD50	Rabbit	2534 mg/kg
<b>Inhalation</b>		
LC50	Rat	61577 ppm, 4 hours 61 mg/l, 4 hours
<b>Oral</b>		
LD50	Rat	5080 mg/kg

Components	Species	Test Results
distillates (petroleum), hydrotreated light (CAS 64742-47-8)		
<b>Acute</b>		
<b>Dermal</b>		
LD50	Rabbit	> 2000 mg/kg
<b>Inhalation</b>		
LC50	Rat	> 5 mg/l, 4 hours
<b>Oral</b>		
LD50	Rat	> 5000 mg/kg

**Skin corrosion/irritation** Prolonged skin contact may cause temporary irritation.

**Serious eye damage/eye irritation** Direct contact with eyes may cause temporary irritation.

**Respiratory or skin sensitization**

**Respiratory sensitization** Not a respiratory sensitizer.

**Skin sensitization** This product is not expected to cause skin sensitization.

**Germ cell mutagenicity** No data available to indicate product or any components present at greater than 0.1% are mutagenic or genotoxic.

**Carcinogenicity** Not classifiable as to carcinogenicity to humans.

**IARC Monographs. Overall Evaluation of Carcinogenicity**

white mineral oil (CAS 8042-47-5) 3 Not classifiable as to carcinogenicity to humans.

**OSHA Specifically Regulated Substances (29 CFR 1910.1001-1053)**

Not listed.

**US. National Toxicology Program (NTP) Report on Carcinogens**

Not listed.

**Reproductive toxicity** This product is not expected to cause reproductive or developmental effects.

**Specific target organ toxicity - single exposure** Not classified.

**Specific target organ toxicity - repeated exposure** Not classified.

**Aspiration hazard** May be fatal if swallowed and enters airways.

**Chronic effects** Prolonged inhalation may be harmful.

---

## 12. Ecological information

<b>Ecotoxicity</b>	The product is not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment.
<b>Persistence and degradability</b>	No data is available on the degradability of any ingredients in the mixture.
<b>Bioaccumulative potential</b>	No data available.
<b>Mobility in soil</b>	No data available.
<b>Other adverse effects</b>	No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.

---

## 13. Disposal considerations

<b>Disposal instructions</b>	If discarded, this product is considered a RCRA ignitable waste, D001. Empty container can be recycled. Collect and reclaim or dispose in sealed containers at licensed waste disposal site. Contents under pressure. Dispose in accordance with all applicable regulations.
<b>Hazardous waste code</b>	D001: Waste Flammable material with a flash point <140 F
<b>Contaminated packaging</b>	Since emptied containers may retain product residue, follow label warnings even after container is emptied. Empty containers should be taken to an approved waste handling site for recycling or disposal.

---

## 14. Transport information

### DOT

<b>UN number</b>	UN1950
<b>UN proper shipping name</b>	Aerosols, flammable, Limited Quantity
<b>Transport hazard class(es)</b>	
<b>Class</b>	2.1
<b>Subsidiary risk</b>	-
<b>Label(s)</b>	2.1
<b>Packing group</b>	Not applicable.
<b>Special precautions for user</b>	Read safety instructions, SDS and emergency procedures before handling.
<b>Special provisions</b>	N82
<b>Packaging exceptions</b>	306
<b>Packaging non bulk</b>	None
<b>Packaging bulk</b>	None


### IATA

<b>UN number</b>	UN1950
<b>UN proper shipping name</b>	Aerosols, flammable, Limited Quantity
<b>Transport hazard class(es)</b>	
<b>Class</b>	2.1
<b>Subsidiary risk</b>	-
<b>Packing group</b>	Not applicable.
<b>ERG Code</b>	10L
<b>Special precautions for user</b>	Read safety instructions, SDS and emergency procedures before handling.
<b>Other information</b>	
<b>Passenger and cargo aircraft</b>	Allowed with restrictions.
<b>Cargo aircraft only</b>	Allowed with restrictions.

### IMDG

<b>UN number</b>	UN1950
<b>UN proper shipping name</b>	AEROSOLS, Limited Quantity
<b>Transport hazard class(es)</b>	
<b>Class</b>	2.1
<b>Subsidiary risk</b>	-
<b>Packing group</b>	Not applicable.
<b>Environmental hazards</b>	
<b>Marine pollutant</b>	No.
<b>EmS</b>	F-D, S-U
<b>Special precautions for user</b>	Read safety instructions, SDS and emergency procedures before handling.

DOT; IMDG



IATA



---

## 15. Regulatory information

### US federal regulations

This product is a "Hazardous Chemical" as defined by the OSHA Hazard Communication Standard, 29 CFR 1910.1200.

#### TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

#### SARA 304 Emergency release notification

Not regulated.

#### OSHA Specifically Regulated Substances (29 CFR 1910.1001-1053)

Not listed.

#### CERCLA Hazardous Substance List (40 CFR 302.4)

Not listed.

#### CERCLA Hazardous Substances: Reportable quantity

Not listed.

Spills or releases resulting in the loss of any ingredient at or above its RQ require immediate notification to the National Response Center (800-424-8802) and to your Local Emergency Planning Committee.

### Other federal regulations

#### Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List

Not regulated.

#### Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

Not regulated.

#### Safe Drinking Water Act (SDWA)

Not regulated.

#### Food and Drug Administration (FDA)

Not regulated.

### Superfund Amendments and Reauthorization Act of 1986 (SARA)

#### Classified hazard categories

Flammable (gases, aerosols, liquids, or solids)  
Gas under pressure  
Aspiration hazard

#### SARA 302 Extremely hazardous substance

Not listed.

#### SARA 311/312 Hazardous chemical

Yes

#### SARA 313 (TRI reporting)

Not regulated.

## US state regulations

### US. New Jersey Worker and Community Right-to-Know Act

carbon dioxide (CAS 124-38-9)

### US. Massachusetts RTK - Substance List

carbon dioxide (CAS 124-38-9)

white mineral oil (CAS 8042-47-5)

### US. Pennsylvania Worker and Community Right-to-Know Law

carbon dioxide (CAS 124-38-9)

distillates (petroleum), hydrotreated light (CAS 64742-47-8)

white mineral oil (CAS 8042-47-5)

### US. Rhode Island RTK

carbon dioxide (CAS 124-38-9)

distillates (petroleum), hydrotreated light (CAS 64742-47-8)

white mineral oil (CAS 8042-47-5)

### California Proposition 65

California Safe Drinking Water and Toxic Enforcement Act of 1986 (Proposition 65): This material is not known to contain any chemicals currently listed as carcinogens or reproductive toxins. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).

### US. California. Candidate Chemicals List. Safer Consumer Products Regulations (Cal. Code Regs, tit. 22, 69502.3, subd. (a))

distillates (petroleum), hydrotreated light (CAS 64742-47-8)

white mineral oil (CAS 8042-47-5)

## Volatile organic compounds (VOC) regulations

### EPA

**VOC content (40 CFR 51.100(s))** 98.4 %

**Consumer products (40 CFR 59, Subpt. C)** Not regulated

### State

**Consumer products** This product is regulated as a Penetrant. This product is compliant for use in all 50 states.

**VOC content (CA)** 0 %

**VOC content (OTC)** 0 %

## International Inventories

Country(s) or region	Inventory name	On inventory (yes/no)*
Australia	Australian Inventory of Chemical Substances (AICS)	Yes
Canada	Domestic Substances List (DSL)	Yes
Canada	Non-Domestic Substances List (NDSL)	No
China	Inventory of Existing Chemical Substances in China (IECSC)	Yes
Europe	European Inventory of Existing Commercial Chemical Substances (EINECS)	Yes
Europe	European List of Notified Chemical Substances (ELINCS)	No
Japan	Inventory of Existing and New Chemical Substances (ENCS)	No
Korea	Existing Chemicals List (ECL)	Yes
New Zealand	New Zealand Inventory	Yes
Philippines	Philippine Inventory of Chemicals and Chemical Substances (PICCS)	Yes
Taiwan	Taiwan Chemical Substance Inventory (TCSI)	Yes
United States & Puerto Rico	Toxic Substances Control Act (TSCA) Inventory	Yes

\*A "Yes" indicates that all components of this product comply with the inventory requirements administered by the governing country(s)

A "No" indicates that one or more components of the product are not listed or exempt from listing on the inventory administered by the governing country(s).

## 16. Other information, including date of preparation or last revision

<b>Issue date</b>	01-20-2021
<b>Prepared by</b>	Allison Yoon
<b>Version #</b>	01



**Further information**

CRC # 555C/1002575

**Disclaimer**

The information contained in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. This information is accurate to the best of CRC's knowledge or obtained from sources believed by CRC to be accurate. Before using any product, read all warnings and directions on the label. For further clarification of any information contained on this (M)SDS consult your supervisor, a health & safety professional, or CRC Industries, Inc..

**Revision information**

This document has undergone significant changes and should be reviewed in its entirety.