





Note that all unique customer requirements (i.e tolerance) need to be verified thru Alfa Laval.



D 21
Alloy 316
S1,S2,S3,S4



HEATING SURFACE
NETWEIGHT 24.0 kg
OPERATING WEIGHT
PLATE MATERIAL Alloy 316
PLATE GROUPING 1*11H/1*12H

T1 T2 T3 T4 locations on back side correspond to S1 S2 S3 S4 on front side

(4X) 5/16"-18x25 UNC

ALL DIMENSIONS IN MILLIMETERS

SIDE	MEDIA	INLET	TEMP.	OUTLET	TEMP.	FLOW RATE	PRESSURE DROP	LIQUID VOL.
1								2.31 dm ³
2								2.52 dm ³

PRESSURE VESSEL APPROVAL

UL/CRN

CBH110-24H S89 (3287133774)

www.alfalaval.com

CUSTOMER NAME / REF. NO.

TOTAL LENGTH 116.4 mm
TOTAL WIDTH 191.0 mm
TOTAL HEIGHT 616.0 mm

COMPANY / REF.

8/24/2017
REV 0