



**AMERICAN EAGLE**<sup>®</sup>  
**FOOD MACHINERY, INC.**

**AE-10NA**  
**10 Quart Countertop**  
**Planetary Mixer**

773.376.0800 (P) • 773.376.2010 (F) • 3131 S. Canal St. Chicago, IL 60616

**Lower Your Total Cost Of Ownership With American Eagle® Mixers! All-Inclusive Accessories, Competitive Pricing, And Reliability Make Us The Value Leader In The Industry.**

### Quality Design

- Powerful 2/3 HP Motor
- 100% Gear-Driven Transmission, Precision Milled, Heat Treated Steel Alloy Gears And Shafts
- Heavy Duty, Rigid Cast Iron Construction
- Industry Standard #12 Hub For Additional Attachments
- Enamel Coating Resists Scratches, Dents, And Rust
- Thermal Overload Protection With Reset
- ETL Certified To Conform To NSF/ANSI 8, CSA, CE Standards
- Heavy Duty, 6 Foot Hard Wired Power Cable And Plug



### Standard Features

- Power Indicator Light
- 3 Fixed Speeds
- Safety Guard with Auto-Shutoff
- Start/Stop Button
- 1 Year Limited Warranty\*

### Standard Accessories

- High Polish 10 Quart Stainless Steel Bowl
- Aluminum Dough Hook
- Stainless Steel Wire Whip
- Aluminum Beater



### Other Available Sizes

- AE-20NA 20 Quart Planetary Mixer
- AE-30NA 30 Quart Planetary Mixer
- AE-40PA 40 Quart Planetary Mixer
- AE-60N4A 60 Quart Planetary Mixer
- AE-80N4A 80 Quart Planetary Mixer (Special Order Only)

Proud Member of:  
  
 North American Association of  
 Food Equipment Manufacturers

**Quality • Value • Reliability**



**AMERICAN EAGLE**<sup>®</sup>  
**FOOD MACHINERY, INC.**

**AE-10NA**  
**10 Quart Countertop**  
**Planetary Mixer**

sales@ameagle.biz • www.americaneaglemachine.com

Call Our Order Hotline 800.836.5756 For Details On Optional Accessories To Maximize Productivity!

### Machine Specifications

Model	Capacity	Motor	Voltage V/HZ/PH	Transmission	Agitator Speeds (RPMs)**	Safety Guard	Power Bowl Lift	Timer
AE-10NA	10 Quarts	2/3 HP	115/60/1	Gear Driven	1st: 135 2nd: 243 3rd: 478	Yes	No	No

### Optional Accessories

- AE-G12NH Meat Grinder Head
- AE-VS12NH Vegetable Cutter
- AE-TS12H Meat Tenderizer
- AE-JS12H Jerky Slicer
- AE-MC12NH Meat Cutter



**AE-G12NH**



**AE-TS12H**



**AE-JS12H**



**AE-MC12NH**

#### Optional AE-G12NH Meat Grinder Attachment

- 100% Stainless Steel Construction
- Includes Feeder Pan, Knife, Sausage Stuffer, Meat Pusher, 3/16" plate, 1/4" plate
- Meat Grinder Plate Sizes Available: 1/16" (2mm), 5/32" (4mm), 3/16" (6mm), 1/4" (8mm), 5/16" (10mm), 1/2" (12mm), 9/16" (14mm), 5/8" (16mm), 11/16" (18mm), Stuffing Plate (0mm)

#### Optional AE-VS12NH Vegetable Cutter

- High Polish Cast Aluminum Construction
- Dual Hopper Chamber Accommodates Large Variety of Item
- Slicer Plate Adjusts to: 1/16" (No Spacer), 1/8" (Thin Spacer), 3/16" (Thick Spacer)
- Shredder/Grating Plate Sizes Available: 5/16", 1/4"

### Dimensions and Shipping Information

Model	Overall Dimensions	Foot Print	Net Weight	Shipping Dimensions***	Ship Weight	Freight Class
AE-10NA	19.1" L x 16.1" W x 25" H	19.1"L x 16.1"W	149 lbs.	18.25"W x 21.5"L x 30.5"H	189 lbs.	85

\*Warranty must be registered. Use of high speed with dough will void warranty, changing speeds improperly will void warranty

\*\*To change speeds, first turn off the machine. Move the lever into position so that the gears lock, then resume mixing.

\*\*\*Crates are affixed to a skid (pallet). The weight and dimensions of this skid are included above and may vary from shipment to shipment.

Proud Member of:  
  
 North American Association of  
 Food Equipment Manufacturers

**Quality • Value • Reliability**