

PC 006



ECONOMY GRADE, CO-EXTRUDED CLOTH DUCT TAPE



TYPICAL APPLICATIONS

- For non-critical, general use in packaging, bundling, sealing, repairing, holding and waterproofing
- Also used in the remediation/abatement industry as a gooseneck tape

PRODUCT FEATURES

- Good conformability
- Will not twist or curl during application
- Made using Polybonded CO-EX Technology®

CONSTRUCTION

Overall Grade/Function: Economy
Backing: Polyethylene film with a cloth carrier
Adhesive: Natural rubber

STANDARD WIDTH(S)

48 mm 72 mm

STANDARD LENGTH(S)

55 m
Contact your Shurtape sales representative for other available sizes

STANDARD CORE SIZE

3 in

STORAGE AND USAGE CONDITIONS

Tape should be stored in its original packaging in a cool, dry area away from direct sunlight and should be used within 12 months of date of shipment. Surfaces to which tape is applied should be clean, dry and free of grease, oil or other contaminants.

COLOR(S)



PHYSICAL PROPERTIES	STANDARD	METRIC
Tensile Strength	26 lbs/in width	45.5 N/10 mm
Adhesion to Stainless Steel	60 oz/in width	6.57 N/10 mm
Thickness	6 mils	0.15 mm
Elongation	20%	20%
Service Temperature Range	40 F to 200 F	4 C to 93 C

Physical and performance characteristics shown above are obtained from tests recommended by PSTC, ASTM, government agencies or Shurtape Technologies, LLC, Quality Assurance and Technical Service departments and do not represent a guarantee of product performance. Individual rolls may vary slightly from these averages. The user should determine whether the product is fit for a particular purpose and is suitable for the user's method of application before use.

