



AMERICAN EAGLE[®]
FOOD MACHINERY, INC.

**AE-DM32/DM31
 AE-DMMS28
 Commercial
 Dough Moulders**

773.376.0800 (P) • 773.376.2010 (F) • 3131 S. Canal St. Chicago, IL 60616

Enhance Your Dough Processing Capabilities With American Eagle® Dough Moulders! Two Stage Design Automatically Sheets, Then Curls Dough

Quality Design On All Models

- Enamel White Paint Finish Resists Rust And Corrosion
- Heavy Duty Cast Iron Frame And Steel Panels
- Thermal Overload Protection Helps Protects Motor
- Stainless Steel Curling Chains, Sanitary Polyurethane Conveyor Belts
- 1 Year Limited Warranty*



AE-DM32



AE-DM32, Full Size For Rapid Processing!

- Powerful 1 HP Motor, On/Off Button, 4 Roller Sheeter, 220V
- Durable Gear, Chain, And Belt Driven Transmission
- Easily Accessible Precise Roller And Conveyor Belt Adjustments
- Convenient Top Workspace With Mounted Tray Support And Flour Tray



AE-DM31



AE-DM31, Dual Level Compact Design!

- Powerful 1/2HP Motor, 4 Roller Sheeter, 115V or 220V**
- Heavy Duty Stainless Steel Rollers
- Durable Gear And Chain Driven Transmission
- Ergonomically Friendly Front Facing Controls And Input/Output
- Independent On/Off, Emergency Stop Button



AE-DMMS28



AE-DMMS28, Dual Mode Sheeter or Moulder!

- Powerful 1/2HP Motor, 2 Stainless Steel Roller Sheeter, 220V
- Unique Dual Mode Forward/Reverse Conveyor For Moulding Or Sheeter Only Operation
- Durable Gear And Chain Driven Transmission
- Independent On/Off, Emergency Stop Button

Proud Member of:

 North American Association of
 Food Equipment Manufacturers

Quality • Value • Reliability



AMERICAN EAGLE[®]
FOOD MACHINERY, INC.

AE-DM32/DM31
AE-DMMS28
Commercial
Dough Moulders

sales@ameagle.biz • www.americaneaglemachine.com

American Eagle® Dough Moulders Are Ideal For Supermarket Bakeries And Retail Bake Shops!
Easy To Use, Intuitive Controls Are Simple To Operate And Require Minimal Training.

Detailed Specifications

Model	Motor	Power Spec V/HZ/PH/Amps	Pieces/ Hour***	Roller Size	Dough Piece Weight Range	Sheeter Roller Adjustment Range	Pressure Board Adjustment Range
AE-DM32	1 HP	220 / 60 / 1 / 6A	700-1000	3.75" Dia x 15.25" L 9.5cm Dia x 39cm L	1.1oz to 10.1oz 30g to 285g	0.06" to 0.87" 1.5mm to 22mm	.38" to 2.2" 9.5mm to 56mm
AE-DM31	1/2 HP	115 / 60 / 1 / 8A 220 / 60 / 1 / 4A**	600-800	3" Dia x 12" L 7.6cm Dia x 30cm L	1.1oz to 8.5oz 30g to 240g	0.03" to 1.02" 1mm to 26mm	.38" to 1.6" 9.5mm to 41mm
AE-DMMS28	1/2 HP	220 / 60 / 1 / 4A	400-600	3.75" Dia x 13" L 9.5cm Dia x 33cm L	1.1oz to 12.3oz 30g to 350g	0.06" to 0.59" 1.5mm to 15mm	.38" to 1.6" 9.5mm to 41mm

Mould Dough Into A Large Variety Of Different Shapes Perfect For:
Knotted Dinner Rolls, Pretzels, Challah, Asian Sweet Breads, Artisan Breads, And More!



Dimensions and Shipping Information

Model	Overall Dimensions	Net Weight	Shipping Dimensions****	Ship Weight	Freight Class
AE-DM32	53" L x 26" W x 42.5" H (135cm x 66cm x 108cm)	451 lbs (204 kg)	60" L x 33" W x 52" H (152cm x 84cm x 132cm)	567 lbs (257 kg)	85
AE-DM31	40" L x 24" W x 42.5" H (102cm x 61cm x 108cm)	310 lbs (141 kg)	40.5" L x 29" W x 50.5" H (103cm x 74cm x 128cm)	389 lbs (176 kg)	85
AE-DMMS28***	39.4" L x 20.9" W x 41.7" H (100cm x 53cm x 106cm)	320 lbs (145 kg)	37" L x 25" W x 49" H (94cm x 64cm x 124cm)	399 lbs (181 kg)	85

* Warranty must be registered. Improper Installation or electrical connection will void warranty

** Special Order Item. Normal Lead Time is 6-8 weeks for manufacturing/delivery

*** Estimated From Continuous Operation

**** Crates may be affixed to a skid (pallet). The weight and dimensions of this skid are included above and may vary on each shipment.



Quality • Value • Reliability