



AMERICAN EAGLE®
FOOD MACHINERY, INC.

AE-GV22 Countertop Vegetable Cutter Kit

773.376.0800 (P) • 773.376.2010 (F) • 3131 S. Canal St. Chicago, IL 60616

**Save Time and Labor With An American Eagle®
 Vegetable Cutter Kit! Process Vegetables And Cheeses
 With Unmatched Efficiency. Even Handles Tomatoes!**

Quality Design

- Powerful 1.5HP Motor, Sealed And Permanently Lubricated 100% Gear Driven Transmission
- Durable And Lightweight Cast Aluminum Chamber Enclosure, Available In Polished Or Matte Finish
- Ball Bearing Mounted Drive Shaft For Extra Smooth Operation
- Unique Dual Hopper Design, 2.5" Diameter Top, 6 x 7" Bottom
- Sanitary Stainless Steel Motor Unit, No Sharp Corners/Seams
- Standard #12 Hub, Motor Can Power Other Attachments, Vegetable Cutter Can Be Used On Other #12 Hubs

Standard Features

- Integrated Food Pusher With Large Ergonomic Handle
- Heavy Duty, 6 Foot Power Cable And NEMA 5-15P Plug
- Thermal Overload Protection With Reset Button
- 1 Year Limited Warranty*



Polished Finish

Standard Accessories

- Cylindrical Plastic Food Pusher
- Includes Choice Of One 1/4" or 5/16" Stainless Steel Shredding Disk With Aluminum Holder
- Substitute With Slicing Disk At Additional Cost



Matte Finish



Available Disk Options

- Extra 1/4" or 5/16" Stainless Steel Shredding Disk With Aluminum Holder
- Stainless Steel Slicing Disk With Aluminum Holder, Adjustable To 1/16", 1/8", 3/16" Thickness Using Removable Spacers
- "S" Style Slicing Disk Is Precision-Milled And Sharpened For Superb Results And Clean Cuts

Proud Member of:

 North American Association of
 Food Equipment Manufacturers

Quality • Value • Reliability



AMERICAN EAGLE[®]
FOOD MACHINERY, INC.

AE-GV22 Countertop Vegetable Cutter Kit

sales@ameagle.biz • www.americaneaglemachine.com

Lower Your Total Cost Of Ownership With An American Eagle® Vegetable Cutter! Quality Design, Competitive Pricing, And Reliable Support Make Us The Value Leader In The Industry.

Specifications


Model	Motor	Voltage V/HZ/PH	Amp	RPMs**	Recommended RPM Range	Cheese Productivity***	Vegetable Productivity***
AE-GV22	1.5HP	115/60/1	16	170	170-340	100-400 lbs / Hour	Up To 675 lbs / Hour

Options And Variations

SKU	Finish	Included Disk
AE-GV22-P-1/4	Polished	1/4" Shred
AE-GV22-P-5/16	Polished	5/16" Shred
AE-GV22-P-SK	Polished	Slicing
AE-GV22-M-1/4	Matte	1/4" Shred
AE-GV22-M-5/16	Matte	5/16" Shred
AE-GV22-M-SK	Matte	Slicing

Ball Bearing Mounted Drive Shaft, Disks, And Chamber Enclosure Separates For Easy Cleaning

Motor Has Standard #12 Hub That Can Power An Optional Meat Tenderizer, Meat Grinder, Meat Cutter, Or Jerky Slicer Attachment!



Top Hopper Designed To Easily Feed Longer Pieces Like Cucumbers, Carrots, And Celery. Large Bottom Hopper Is Perfect For Whole Potatoes, Cheese Blocks, Lettuce, Cabbage, Tomatoes, Onions, Fruits, And More!



Polished



Matte

Dimensions and Shipping Information

Model	Assembled Product Dimensions	Disassembled Dimensions	Net Weight	Shipping Dimensions	Ship Weight#
AE-GV22	27" L x 12.5" W x 19" H	Motor: 13" L x 10" W x 15.5" H Attachment: 17" L x 13" W x 14" H	86 lbs (39 kg)	Box 1: 17" L x 14" W x 17.5" H Box 2: 19.5" L x 15.5" W x 13" H	96 lbs (44 kg)

* Warranty Must Be Registered, Improper Wiring To Electrical Service Will Void Warranty, Improper Installation Or Over-Loading Voids Warranty. Extended Warranty Available At Extra Cost.

** RPM Is Fixed. #12 Hub Cutter Attachment Can Be Used On A Different Motor With Higher RPMs Required For Certain Kinds Of Processing. Recommended Range is 170 RPM to 340 RPM When Attachment Is Used With Other Motors.

*** Capacity Will Be Diminished Based On Cheese Hardness, Cheese Productivity Is Estimated Based On Softer Cheese. Ratings Are Estimated Based On Continuous Operation

Ships In Two Boxes, Estimated Combined Dimensional Weight



Quality • Value • Reliability