



ISO-9001 Registered Quality System.

Sales, Service & Distribution Center

Newark, NJ 07105

Phone: 973-589-9150

Fax: 973-589-4432

Manufacturing, Sales, Service & Distribution Center

Toledo, OH 43605

Phone: 419-691-2491

Fax: 419-693-3806

Sales and Tech Service Support

Phone: 1-800-733-4755

PRODUCT DATA**LUBRIPLATE POLY HP-2****DESCRIPTION**

LUBRIPLATE Poly HP-2 is a polyurea-thickened lubricating grease formulated for improved bearing protection and longer electric motor life.

APPLICATIONS

Fortified with corrosion and oxidation inhibitors, LUBRIPLATE Poly HP-2 is an excellent choice for the lubrication and protection of high-speed electric motor bearings, as well as other industrial applications:

- ⇒ Electric Motor Bearings
- ⇒ High Temperature Bearing Applications
- ⇒ Pump Bearings

ADVANTAGES

- ⇒ Recommended by major bearing and electric motor manufacturers.
- ⇒ LUBRIPLATE Poly HP-2 under mechanical stress performs better, compared to competitor polyurea-based electric motor greases.
- ⇒ Performs very well in high temperature applications.

STORAGE RECOMMENDATIONS

- ⇒ Products should be stored between 40°F-120°F
- ⇒ Products should be stored in a dry covered environment
- ⇒ Products should not be stored in warm, direct sunlight
- ⇒ Improper storage conditions can significantly alter the shelf life of the product. Such conditions would include temperature, moisture, open containers, etc.

**Typical Test Data**

PROPERTY	TEST METHOD	TYPICAL RESULTS*
Thickener		Polyurea
Worked Penetration: 60 Strokes	ASTM D-217	265
NLGI No.		2
Worked Penetration: 100,000 Strokes	ASTM D-217	40 (Change)
Dropping Point	ASTM D-2265	500°F/260°C
Oxidation Stability/Grease Life	ASTM D-3336	1,000 hrs.+
Four Ball Wear: 40kg, 1200RPM, 75°C, 1hr.	ASTM D-2266	0.45
Mineral Oil Viscosity: SUS @ 100°F	ASTM D-2161	650
cSt @ 40°C	ASTM D-445	128
Appearance	Visual	Red
Texture	Visual	Smooth/Buttery
Copper Corrosion	ASTM D-130A	1b
Corrosion Resistance	ASTM D-1743	Pass
Oil Separation	ASTM D-1742	<3.0%
Lincoln Ventmeter: Test Temperature: 77°F Average Ventmeter Pressure @ 30 Seconds	K95400	228 psi
Lincoln Ventmeter: Test Temperature: 30°F Average Ventmeter Pressure @ 30 Seconds	K95400	602 psi
Lincoln Ventmeter: Test Temperature: 0°F Average Ventmeter Pressure @ 30 Seconds	K95400	1,494 psi

PACKAGING AVAILABLE

35 lb. Pail
120 lb. Quarter Size, Drum
Carton, 40/14 oz. Cartridges

Part No.

L0191-035
L0191-039
L0191-098