

# AMERICAN COATINGS CORPORATION

3037 NW 60th Street  
Fort Lauderdale, Florida 33309  
(800)533-0151

[amercoat@bellsouth.net](mailto:amercoat@bellsouth.net)

## S D S SAFETY DATA SHEET — 16 Sections

### SECTION 1 — CHEMICAL PRODUCT AND COMPANY IDENTIFICATION

Product Identifier CC 2B		October 29, 2015	
Product Use Bridging & Encasement Sealant			
Manufacturer's for: American Coatings Corporation		Supplier's Name	
Street Address 3037 NW 60th Street		Street Address	
City Fort Lauderdale	State: FL	City	
Postal Code 33309	Emergency Phone 800-533-0151	Postal Code	Emergency Telephone
Prepared by: John Tidquist		Phone Number (304) 755-3328	

### SECTION 2 — COMPOSITION/INFORMATION ON INGREDIENTS

Hazardous Ingredients ( <i>specific</i> )	%	CAS Number	LD <sub>50</sub> of Ingredient ( <i>specify species and route</i> )	LC <sub>50</sub> of Ingredi
Vinyl acetate	<0.5	105-05-4	10 ppm	N/A
Phenol, Isopropylated phosphate	<5	68937-41-7	N/A	N/A

### SECTION 3 — HAZARDS IDENTIFICATION

<p><b>Primary Routes of Entry:</b> Dermal or inhalation</p> <p><b>Eye:</b> May be an irritant; <b>Skin:</b> Prolonged contact may cause irritation dermatitis;</p> <p><b>Ingestion:</b> No information assumed to cause gastro irritation. Low toxicity;</p> <p><b>Inhalation:</b> May cause irritation to the respiratory tracts. Overexposure could cause headache, nausea, fatigue.</p> <p><b>GHS Labeling:</b> Not a hazardous mixture.</p>
---

## Product Identifier – CC 2B, American Coatings Corporation

### SECTION 4 — FIRST AID MEASURES

**Skin:** Wash with soap and water

**Eyes:** Flush with clean water at least 15 minutes, if irritation persists, consult physician.

**Inhalation:** Remove to fresh air. If breathing is difficult, administer oxygen. If irritation persists, consult physician

**Ingestion:** Give two glasses of water, induce vomiting, consult physician or poison control center. Never give anything by mouth to an unconscious person.

### SECTION 5 — FIRE FIGHTING MEASURES

Flammable <b>No</b>	If yes, under which conditions?	
Means of Extinction: Foam, Alcohol Foam, CO <sub>2</sub> , Dry Chemical, Water Fog		
Flashpoint: No flash to boiling 212°F (TCC)	Upper Flammable Limit (% by volume) <b>No data available</b>	Lower Flammable Limit (% by volume) <b>No data available</b>
Autoignition Temperature ( ° C) <b>No data available</b>	Explosion Data: <b>None known</b>	Explosion Data — Sensitivity to Static Discharge <b>None</b>
Hazardous Combustion Products: Thermal decomposition will yield CO, CO <sub>2</sub> , and HPO <sub>x</sub> .		
DECOMPOSITION TEMPERATURE: Approx. 275°F (135°C)		
Product will not burn until water has boiled or evaporated. For dried film or residual solids, full protective equipment is recommended, including self-contained breathing apparatus		

### SECTION 6 — ACCIDENTAL RELEASE MEASURES

Spills should be collected for disposal; eliminate all ignition sources. Prevent material from entering drains, sewers and waterways. Before drying product may be washed away with water; after drying, remove with a paint scraper or strong solvent.

### SECTION 7 — HANDLING AND STORAGE

Thoroughly cleanse hands after handling. Launder contaminated clothing before reuse.

Protect from freezing.

Do not use empty containers for potables or edibles.

Store indoors at temperatures of 40°F to 90°F. Do not store at elevated temperatures, as containers could pressurize and rupture

## Product Identifier – CC 2B, American Coatings Corporation

### SECTION 8 — EXPOSURE CONTROL / PERSONAL PROTECTION

Exposure limits: Not available

In restricted ventilation areas, use approved chemical respirator, avoid inhalation of airborne particulates by using an approved respirator. General (mechanical) room ventilation is expected to be satisfactory. Supplementary local exhaust and respiratory protection may be needed in poorly ventilated spaces, or evaporation from large surfaces when spraying.

Personal Protection: Impervious gloves, goggles, face shield or other eyewear to protect from splash.

### SECTION 9 — PHYSICAL AND CHEMICAL PROPERTIES

Physical State: paste consistency	Odor : Mild latex odor	Wt/Gal: 10.4 lbs.
Specific Gravity: 1.21	Vapor Density (air = 1): Lighter than air	Viscosity: 5,000 to 10,000 cps
Evaporation Rate: slower than ether	Boiling Point : 212°F (100°C)	Freezing Point : 32°F (0°C)
pH 8 - 9	VOC (lbs/gal): 0	Volatile Volume: 50%

### SECTION 10 — STABILITY AND REACTIVITY

Chemical Stability: Stable

Avoid materials that are incompatible with water and oxidizers.

### SECTION 11 — TOXICOLOGICAL INFORMATION

Not available

### SECTION 12 — ECOLOGICAL INFORMATION

Not available

### SECTION 13 — DISPOSAL CONSIDERATIONS

Dispose of in accordance with all applicable regulations. Review hazard section of this sheet before attempting cleanup. Spills may be slippery. Before drying, product may be washed away with water; after drying remove with a paint scraper or strong solvent. Empty containers are non hazardous under RCRA as industrial waste.

**Product Identifier – CC 2B, American Coatings Corporation**

**SECTION 14 — TRANSPORT INFORMATION**

US Dept. of Transportation (DOT): Not regulated  
International Maritime Dangerous Goods Code (IMDG): Not regulated

**SECTION 15 — REGULATORY INFORMATION**

**SARA Title III, Section 302.311/312, 325: none**  
**CERCLA Reportable Quantity: None**

**SECTION 16 — OTHER INFORMATION**

For industry/professional use only. Not intended for retail sale or use by individual consumers.

**HMIS Hazard Rating**

Health: 1      Flammability: 0      Physical Hazard: 0

**NFPA**

Health: 1      Flammability: 0      Instability: 0