



SAFETY DATA SHEET HYDRAULIC OIL HO-68

According to Appendix D, OSHA Hazard Communication Standard 29 CFR §1910.1200

1. Identification

Product identifier

Product name HYDRAULIC OIL HO-68
Product number L0772-057, L0772-060, L0772-061, L0772-062

Recommended use of the chemical and restrictions on use

Application Petroleum lubricating oil
Uses advised against No specific uses advised against are identified.

Details of the supplier of the safety data sheet

Manufacturer Lubriplate Lubricants Co.
Corporate Headquarters
129 Lockwood Street
Newark, NJ 07105

Midwest Office & Plant
1500 Oakdale Ave.
Toledo, OH 43605
419-691-2491
419-693-3806

Emergency telephone number

Emergency telephone Chem-Tel: 1-800-255-3924 (US & Canada only)
01-813-248-0585 (Outside US & Canada) Europe: +49 4262 79 9603

2. Hazard(s) identification

Classification of the substance or mixture

Physical hazards Not Classified
Health hazards Not Classified
Environmental hazards Not Classified

Label elements

Hazard statements NC Not Classified

Other hazards

This product does not contain any substances classified as PBT or vPvB.

HYDRAULIC OIL HO-68

3. Composition/information on ingredients

4. First-aid measures

Description of first aid measures

| | |
|-----------------------------------|--|
| General information | If in doubt, get medical attention promptly. Show this Safety Data Sheet to the medical personnel. |
| Inhalation | No specific recommendations. If throat irritation or coughing persists, proceed as follows. Move affected person to fresh air and keep warm and at rest in a position comfortable for breathing. Loosen tight clothing such as collar, tie or belt. Get medical attention if any discomfort continues. |
| Ingestion | No specific recommendations. If throat irritation or coughing persists, proceed as follows. Rinse mouth. Get medical attention if any discomfort continues. |
| Skin Contact | No specific recommendations. Rinse with water. Get medical attention if any discomfort continues. |
| Eye contact | Remove any contact lenses and open eyelids wide apart. Rinse with water. Get medical attention if any discomfort continues. |
| Protection of first aiders | Use protective equipment appropriate for surrounding materials. |

Most important symptoms and effects, both acute and delayed

| | |
|----------------------------|---|
| General information | The severity of the symptoms described will vary dependent on the concentration and the length of exposure. |
| Inhalation | No specific symptoms known. Spray/mists may cause respiratory tract irritation. |
| Ingestion | No specific symptoms known. May cause discomfort if swallowed. |
| Skin contact | No specific symptoms known. May cause discomfort. |
| Eye contact | No specific symptoms known. May be slightly irritating to eyes. |

Indication of immediate medical attention and special treatment needed

| | |
|-----------------------------|--------------------------------|
| Notes for the doctor | Treat symptomatically. |
| Specific treatments | No special treatment required. |

5. Fire-fighting measures

Extinguishing media

| | |
|---------------------------------------|--|
| Suitable extinguishing media | The product is not flammable. Extinguish with alcohol-resistant foam, carbon dioxide, dry powder or water fog. Use fire-extinguishing media suitable for the surrounding fire. |
| Unsuitable extinguishing media | Do not use water jet as an extinguisher, as this will spread the fire. |

Special hazards arising from the substance or mixture

| | |
|--------------------------------------|---|
| Specific hazards | Containers can burst violently or explode when heated, due to excessive pressure build-up. |
| Hazardous combustion products | Thermal decomposition or combustion products may include the following substances: Harmful gases or vapors. |

Advice for firefighters

| | |
|---|---|
| Protective actions during firefighting | Avoid breathing fire gases or vapors. Evacuate area. Cool containers exposed to heat with water spray and remove them from the fire area if it can be done without risk. Cool containers exposed to flames with water until well after the fire is out. If a leak or spill has not ignited, use water spray to disperse vapors and protect men stopping the leak. |
|---|---|

HYDRAULIC OIL HO-68

Special protective equipment for firefighters Wear positive-pressure self-contained breathing apparatus (SCBA) and appropriate protective clothing. Standard Firefighter's clothing including helmets, protective boots and gloves will provide a basic level of protection for chemical incidents.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Personal precautions No specific recommendations. For personal protection, see Section 8.

Environmental precautions

Environmental precautions Avoid discharge into drains or watercourses or onto the ground.

Methods and material for containment and cleaning up

Methods for cleaning up Reuse or recycle products wherever possible. Absorb spillage to prevent material damage. Flush contaminated area with plenty of water. Wash thoroughly after dealing with a spillage. Dispose of contents/container in accordance with national regulations.

Reference to other sections For personal protection, see Section 8. For waste disposal, see Section 13.

7. Handling and storage

Precautions for safe handling

Usage precautions Read and follow manufacturer's recommendations. Wear protective clothing as described in Section 8 of this safety data sheet. Keep away from food, drink and animal feeding stuffs. Handle all packages and containers carefully to minimize spills. Keep container tightly sealed when not in use. Avoid the formation of mists.

Advice on general occupational hygiene Wash promptly if skin becomes contaminated. Take off contaminated clothing and wash before reuse. Wash contaminated clothing before reuse.

Conditions for safe storage, including any incompatibilities

Storage precautions Store away from incompatible materials (see Section 10). No specific recommendations.

Storage class Unspecified storage.

Specific end uses(s)

Specific end use(s) The identified uses for this product are detailed in Section 1.

8. Exposure controls/Personal protection

Control parameters

Occupational exposure limits

Mineral oil, excluding metal working fluids (pure, highly and severely refined)
Long-term exposure limit (8-hour TWA): ACGIH 5 mg/m³ inhalable fraction

Distillates (petroleum), hydrotreated heavy naphthenic

Mineral oil, excluding metal working fluids (pure, highly and severely refined)
ACGIH

White mineral oil (petroleum)

Mineral oil, excluding metal working fluids (pure, highly and severely refined)
Long-term exposure limit (8-hour TWA): ACGIH 5 mg/m³ inhalable fraction
ACGIH = American Conference of Governmental Industrial Hygienists.

Exposure controls

HYDRAULIC OIL HO-68

Protective equipment



Appropriate engineering controls

No specific ventilation requirements.

Eye/face protection

No specific eye protection required during normal use. Large Spillages: Eyewear complying with an approved standard should be worn if a risk assessment indicates eye contact is possible.

Hand protection

No specific hand protection recommended. Large Spillages: Wear protective gloves.

Other skin and body protection

Wear appropriate clothing to prevent repeated or prolonged skin contact.

Hygiene measures

Wash after use and before eating, smoking and using the toilet. Do not eat, drink or smoke when using this product.

Respiratory protection

No specific recommendations. Provide adequate ventilation. Large Spillages: If ventilation is inadequate, suitable respiratory protection must be worn.

Environmental exposure controls

Not regarded as dangerous for the environment.

9. Physical and chemical properties

Information on basic physical and chemical properties

| | |
|---|---|
| Appearance | Oily liquid. Transparent. |
| Color | Straw. to Yellowish. |
| Odor | Mineral oil |
| Odor threshold | Not available. |
| pH | Not available. |
| Melting point | Not available. |
| Initial boiling point and range | >288°C (>550.4°F) |
| Flash point | 246°C/475°F Cleveland open cup. |
| Evaporation rate | < 0.01 (butyl acetate = 1) |
| Evaporation factor | Not available. |
| Flammability (solid, gas) | Not applicable. |
| Upper/lower flammability or explosive limits | Lower flammable/explosive limit: 0.9 % Upper flammable/explosive limit: 7 % |
| Vapor pressure | <0.0013 kPa @ 20°C |
| Vapor density | > 5 |
| Relative density | 0.87 |
| Bulk density | Not available. |
| Solubility(ies) | Insoluble in water. |
| Partition coefficient | Not available. |

HYDRAULIC OIL HO-68

| | |
|----------------------------------|---|
| Auto-ignition temperature | Not available. |
| Decomposition Temperature | Not available. |
| Viscosity | 68 cSt @ 40°C/104°F |
| Explosive properties | Not considered to be explosive. |
| Oxidizing properties | Does not meet the criteria for classification as oxidizing. |

10. Stability and reactivity

| | |
|---|---|
| Reactivity | See the other subsections of this section for further details. |
| Stability | Stable at normal ambient temperatures and when used as recommended. Stable under the prescribed storage conditions. |
| Possibility of hazardous reactions | No potentially hazardous reactions known. |
| Conditions to avoid | There are no known conditions that are likely to result in a hazardous situation. |
| Materials to avoid | No specific material or group of materials is likely to react with the product to produce a hazardous situation. |
| Hazardous decomposition products | Does not decompose when used and stored as recommended. Thermal decomposition or combustion products may include the following substances: Harmful gases or vapors. |

11. Toxicological information

Information on toxicological effects

| | |
|---|--|
| Toxicological effects | Not regarded as a health hazard under current legislation. |
| <u>Acute toxicity - oral</u> | |
| Notes (oral LD₅₀) | Based on available data the classification criteria are not met. |
| <u>Acute toxicity - dermal</u> | |
| Notes (dermal LD₅₀) | Based on available data the classification criteria are not met. |
| <u>Acute toxicity - inhalation</u> | |
| Notes (inhalation LC₅₀) | Based on available data the classification criteria are not met. |
| <u>Skin corrosion/irritation</u> | |
| Animal data | Based on available data the classification criteria are not met. |
| <u>Serious eye damage/irritation</u> | |
| Serious eye damage/irritation | Based on available data the classification criteria are not met. |
| <u>Respiratory sensitization</u> | |
| Respiratory sensitization | Based on available data the classification criteria are not met. |
| <u>Skin sensitization</u> | |
| Skin sensitization | Based on available data the classification criteria are not met. |
| <u>Germ cell mutagenicity</u> | |
| Genotoxicity - in vitro | Based on available data the classification criteria are not met. |
| <u>Carcinogenicity</u> | |
| Carcinogenicity | Based on available data the classification criteria are not met. |

HYDRAULIC OIL HO-68

| | |
|--|---|
| IARC carcinogenicity | None of the ingredients are listed or exempt. |
| <u>Reproductive toxicity</u> | |
| Reproductive toxicity - fertility | Based on available data the classification criteria are not met. |
| Reproductive toxicity - development | Based on available data the classification criteria are not met. |
| <u>Specific target organ toxicity - single exposure</u> | |
| STOT - single exposure | Not classified as a specific target organ toxicant after a single exposure. |
| <u>Specific target organ toxicity - repeated exposure</u> | |
| STOT - repeated exposure | Not classified as a specific target organ toxicant after repeated exposure. |
| <u>Aspiration hazard</u> | |
| Aspiration hazard | Based on available data the classification criteria are not met. |
| General information | |
| | No specific health hazards known. The severity of the symptoms described will vary dependent on the concentration and the length of exposure. |
| Inhalation | No specific symptoms known. Spray/mists may cause respiratory tract irritation. |
| Ingestion | No specific symptoms known. May cause discomfort if swallowed. |
| Skin Contact | No specific symptoms known. May cause discomfort. |
| Eye contact | No specific symptoms known. May be slightly irritating to eyes. |
| Route of exposure | Ingestion Inhalation Skin and/or eye contact |
| Target Organs | No specific target organs known. |

12. Ecological information

| | |
|---|---|
| Ecotoxicity | Not regarded as dangerous for the environment. However, large or frequent spills may have hazardous effects on the environment. |
| Toxicity | Based on available data the classification criteria are not met. |
| <u>Persistence and degradability</u> | |
| Persistence and degradability | The degradability of the product is not known. |
| <u>Bioaccumulative potential</u> | |
| Bio-Accumulative Potential | No data available on bioaccumulation. |
| Partition coefficient | Not available. |
| <u>Mobility in soil</u> | |
| Mobility | No data available. |
| <u>Other adverse effects</u> | |
| Other adverse effects | None known. |

13. Disposal considerations

Waste treatment methods

| | |
|----------------------------|---|
| General information | The generation of waste should be minimized or avoided wherever possible. Reuse or recycle products wherever possible. This material and its container must be disposed of in a safe way. |
|----------------------------|---|

HYDRAULIC OIL HO-68

Disposal methods Dispose of surplus products and those that cannot be recycled via a licensed waste disposal contractor. Waste packaging should be collected for reuse or recycling. Incineration or landfill should only be considered when recycling is not feasible. Waste should not be disposed of untreated to the sewer unless fully compliant with the requirements of the local water authority.

14. Transport information

General Not regulated.

Environmental hazards

Environmentally Hazardous Substance

No.

15. Regulatory information

US Federal Regulations

SARA Section 302 Extremely Hazardous Substances Tier II Threshold Planning Quantities

None of the ingredients are listed or exempt.

CERCLA/Superfund, Hazardous Substances/Reportable Quantities (EPA)

None of the ingredients are listed or exempt.

SARA Extremely Hazardous Substances EPCRA Reportable Quantities

None of the ingredients are listed or exempt.

SARA 313 Emission Reporting

None of the ingredients are listed or exempt.

CAA Accidental Release Prevention

None of the ingredients are listed or exempt.

FDA - Essential Chemical

None of the ingredients are listed or exempt.

FDA - Precursor Chemical

None of the ingredients are listed or exempt.

SARA (311/312) Hazard Categories

None of the ingredients are listed or exempt.

OSHA Highly Hazardous Chemicals

None of the ingredients are listed or exempt.

US State Regulations

California Proposition 65 Carcinogens and Reproductive Toxins

None of the ingredients are listed or exempt.

California Air Toxics "Hot Spots" (A-I)

None of the ingredients are listed or exempt.

California Air Toxics "Hot Spots" (A-II)

None of the ingredients are listed or exempt.

California Directors List of Hazardous Substances

None of the ingredients are listed or exempt.

HYDRAULIC OIL HO-68

Massachusetts "Right To Know" List

None of the ingredients are listed or exempt.

Rhode Island "Right To Know" List

None of the ingredients are listed or exempt.

Minnesota "Right To Know" List

None of the ingredients are listed or exempt.

New Jersey "Right To Know" List

None of the ingredients are listed or exempt.

Pennsylvania "Right To Know" List

None of the ingredients are listed or exempt.

Inventories

US - TSCA

The following ingredients are listed or exempt:

Methacrylate copolymer

White mineral oil (petroleum)

Alkyl methacrylate

Distillates (petroleum), hydrotreated middle

Distillates (petroleum), hydrotreated heavy paraffinic

Distillates (petroleum), hydrotreated heavy paraffinic

2,6-di-tert-butylphenol

Distillates (petroleum), hydrotreated heavy naphthenic

US - TSCA 12(b) Export Notification

None of the ingredients are listed or exempt.

16. Other information

Training advice Only trained personnel should use this material.

Revision date 9/4/2018

SDS No. 5039

End of SDS

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty, guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.