



## SAFETY DATA SHEET

### Poly HP-2

According to Appendix D, OSHA Hazard Communication Standard 29 CFR §1910.1200

#### 1. Identification

##### Product identifier

**Product name** Poly HP-2

**Product number** L0191-035, L0191-039, L0191-098, L0191-040, L0191-040B, L0191-100

##### Recommended use of the chemical and restrictions on use

**Application** Lubricating grease.

**Uses advised against** No specific uses advised against are identified.

##### Details of the supplier of the safety data sheet

**Manufacturer** Lubriplate Lubricants Co.  
Corporate Headquarters  
129 Lockwood Street  
Newark, NJ 07105

Midwest Office & Plant  
1500 Oakdale Ave.  
Toledo, OH 43605  
419-691-2491  
419-693-3806

##### Emergency telephone number

**Emergency telephone** Chem-Tel: 1-800-255-3924 (US & Canada only)  
01-813-248-0585 (Outside US & Canada)

#### 2. Hazard(s) identification

##### Classification of the substance or mixture

**Physical hazards** Not Classified

**Health hazards** Skin Sens. 1 - H317

**Environmental hazards** Not Classified

##### Label elements

##### Hazard symbols



**Signal word** Warning

**Hazard statements** H317 May cause an allergic skin reaction.

## Poly HP-2

<b>Precautionary statements</b>	P261 Avoid breathing dust.
	P272 Contaminated work clothing must not be allowed out of the workplace.
	P280 Wear protective gloves/ protective clothing/ eye protection/ face protection.
	P302+P352 If on skin: Wash with plenty of water.
	P321 Specific treatment (see medical advice on this label).
	P333+P313 If skin irritation or rash occurs: Get medical advice/ attention.
	P362+P364 Take off contaminated clothing and wash it before reuse.
P501 Dispose of contents/ container in accordance with national regulations.	

**Contains** Polyurea grease

### Other hazards

This product does not contain any substances classified as PBT or vPvB.

### 3. Composition/information on ingredients

#### Mixtures

<b>Distillates (petroleum), hydrotreated heavy naphthenic</b>	<b>60-100%</b>
CAS number: 64742-52-5	
<b>Classification</b>	
Not Classified	
<b>Polyurea grease</b>	<b>10-30%</b>
CAS number: —	
<b>Classification</b>	
Skin Sens. 1B - H317	
Aquatic Chronic 4 - H413	
<b>1-H benzotriazole-1-methanamine, N,N-bis(2-ethylhexyl)-methyl-</b>	<b>&lt;1%</b>
CAS number: 94270-86-7	
<b>Classification</b>	
Acute Tox. 4 - H302	
Acute Tox. 4 - H312	
Skin Irrit. 2 - H315	
Eye Irrit. 2A - H319	
Skin Sens. 1B - H317	
Aquatic Chronic 2 - H411	

The full text for all hazard statements is displayed in Section 16.

**Composition comments** \* The exact percentage withheld as a trade secret in accordance with 29 CFR 1910.1200.

### 4. First-aid measures

#### Description of first aid measures

**General information** Get medical attention immediately. Show this Safety Data Sheet to the medical personnel.

## Poly HP-2

<b>Inhalation</b>	Remove affected person from source of contamination. Move affected person to fresh air and keep warm and at rest in a position comfortable for breathing. Maintain an open airway. Loosen tight clothing such as collar, tie or belt. When breathing is difficult, properly trained personnel may assist affected person by administering oxygen. Place unconscious person on their side in the recovery position and ensure breathing can take place.
<b>Ingestion</b>	Rinse mouth thoroughly with water. Give a few small glasses of water or milk to drink. Stop if the affected person feels sick as vomiting may be dangerous. Do not induce vomiting unless under the direction of medical personnel. If vomiting occurs, the head should be kept low so that vomit does not enter the lungs. Never give anything by mouth to an unconscious person. Move affected person to fresh air and keep warm and at rest in a position comfortable for breathing. Place unconscious person on their side in the recovery position and ensure breathing can take place. Maintain an open airway. Loosen tight clothing such as collar, tie or belt.
<b>Skin Contact</b>	It is important to remove the substance from the skin immediately. In the event of any sensitization symptoms developing, ensure further exposure is avoided. Remove contamination with soap and water or recognized skin cleansing agent. Get medical attention if symptoms are severe or persist after washing.
<b>Eye contact</b>	Rinse immediately with plenty of water. Remove any contact lenses and open eyelids wide apart. Continue to rinse for at least 10 minutes.
<b>Protection of first aiders</b>	First aid personnel should wear appropriate protective equipment during any rescue. Wash contaminated clothing thoroughly with water before removing it from the affected person, or wear gloves. It may be dangerous for first aid personnel to carry out mouth-to-mouth resuscitation.

### Most important symptoms and effects, both acute and delayed

<b>General information</b>	See Section 11 for additional information on health hazards. The severity of the symptoms described will vary dependent on the concentration and the length of exposure.
<b>Inhalation</b>	A single exposure may cause the following adverse effects: Temporary irritation.
<b>Ingestion</b>	May cause sensitization or allergic reactions in sensitive individuals. May cause discomfort if swallowed. May cause stomach pain or vomiting.
<b>Skin contact</b>	May cause skin sensitization or allergic reactions in sensitive individuals. Prolonged contact may cause dryness of the skin.
<b>Eye contact</b>	May be slightly irritating to eyes.

### Indication of immediate medical attention and special treatment needed

<b>Notes for the doctor</b>	Treat symptomatically. May cause sensitization or allergic reactions in sensitive individuals.
-----------------------------	--

## 5. Fire-fighting measures

### Extinguishing media

**Suitable extinguishing media** The product is not flammable. Extinguish with alcohol-resistant foam, carbon dioxide, dry powder or water fog. Use fire-extinguishing media suitable for the surrounding fire.

**Unsuitable extinguishing media** Do not use water jet as an extinguisher, as this will spread the fire.

### Special hazards arising from the substance or mixture

**Specific hazards** None known.

**Hazardous combustion products** Thermal decomposition or combustion products may include the following substances: Harmful gases or vapors.

## Poly HP-2

### Advice for firefighters

#### **Protective actions during firefighting**

Avoid breathing fire gases or vapors. Evacuate area. Cool containers exposed to heat with water spray and remove them from the fire area if it can be done without risk. Cool containers exposed to flames with water until well after the fire is out. Control run-off water by containing and keeping it out of sewers and watercourses. If risk of water pollution occurs, notify appropriate authorities.

#### **Special protective equipment for firefighters**

Wear positive-pressure self-contained breathing apparatus (SCBA) and appropriate protective clothing. Standard Firefighter's clothing including helmets, protective boots and gloves will provide a basic level of protection for chemical incidents.

## 6. Accidental release measures

### Personal precautions, protective equipment and emergency procedures

#### **Personal precautions**

No action shall be taken without appropriate training or involving any personal risk. Keep unnecessary and unprotected personnel away from the spillage. Wear protective clothing as described in Section 8 of this safety data sheet. Follow precautions for safe handling described in this safety data sheet. Wash thoroughly after dealing with a spillage. Ensure procedures and training for emergency decontamination and disposal are in place. Do not touch or walk into spilled material. Avoid contact with skin and eyes.

### Environmental precautions

#### **Environmental precautions**

Large Spillages: Inform the relevant authorities if environmental pollution occurs (sewers, waterways, soil or air).

### Methods and material for containment and cleaning up

#### **Methods for cleaning up**

Wear protective clothing as described in Section 8 of this safety data sheet. Clear up spills immediately and dispose of waste safely. Approach the spillage from upwind. Collect spillage with a shovel and broom, or similar and reuse, if possible. Collect and place in suitable waste disposal containers and seal securely. Flush contaminated area with plenty of water. Wash thoroughly after dealing with a spillage. Dispose of waste to licensed waste disposal site in accordance with the requirements of the local Waste Disposal Authority.

#### **Reference to other sections**

For personal protection, see Section 8. See Section 11 for additional information on health hazards. See Section 12 for additional information on ecological hazards. For waste disposal, see Section 13.

## 7. Handling and storage

### Precautions for safe handling

#### **Usage precautions**

Read and follow manufacturer's recommendations. Wear protective clothing as described in Section 8 of this safety data sheet. Keep away from food, drink and animal feeding stuffs. Keep container tightly sealed when not in use. Do not handle until all safety precautions have been read and understood. Do not handle broken packages without protective equipment. Do not reuse empty containers.

#### **Advice on general occupational hygiene**

Wash promptly if skin becomes contaminated. Take off contaminated clothing and wash before reuse. Wash contaminated clothing before reuse. Do not eat, drink or smoke when using this product. Wash at the end of each work shift and before eating, smoking and using the toilet. Change work clothing daily before leaving workplace.

### Conditions for safe storage, including any incompatibilities

## Poly HP-2

<b>Storage precautions</b>	Store away from incompatible materials (see Section 10). Store in accordance with local regulations. Keep only in the original container. Keep container tightly closed, in a cool, well ventilated place. Keep containers upright. Protect containers from damage. Utilize retaining walls to prevent soil and water pollution in the event of spillage. The storage area floor should be leak-tight, jointless and not absorbent.
<b>Storage class</b>	Chemical storage.
<b>Specific end uses(s)</b>	
<b>Specific end use(s)</b>	The identified uses for this product are detailed in Section 1.

### 8. Exposure controls/Personal protection

#### Control parameters

#### Occupational exposure limits

#### Distillates (petroleum), hydrotreated heavy naphthenic

Mineral oil, excluding metal working fluids (pure, highly and severely refined)

ACGIH

ACGIH = American Conference of Governmental Industrial Hygienists.

#### Exposure controls

#### Protective equipment



#### Appropriate engineering controls

Provide adequate ventilation. Personal, workplace environment or biological monitoring may be required to determine the effectiveness of the ventilation or other control measures and/or the necessity to use respiratory protective equipment. Use process enclosures, local exhaust ventilation or other engineering controls as the primary means to minimize worker exposure. Personal protective equipment should only be used if worker exposure cannot be controlled adequately by the engineering control measures. Ensure control measures are regularly inspected and maintained. Ensure operatives are trained to minimize exposure.

#### Eye/face protection

Eyewear complying with an approved standard should be worn if a risk assessment indicates eye contact is possible. Personal protective equipment for eye and face protection should comply with OSHA 1910.133. Unless the assessment indicates a higher degree of protection is required, the following protection should be worn: Tight-fitting safety glasses.

#### Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn if a risk assessment indicates skin contact is possible. The most suitable glove should be chosen in consultation with the glove supplier/manufacturer, who can provide information about the breakthrough time of the glove material. To protect hands from chemicals, gloves should comply with OSHA 1910.138 and be demonstrated to be impervious to the chemical and resist degradation. Considering the data specified by the glove manufacturer, check during use that the gloves are retaining their protective properties and change them as soon as any deterioration is detected. Frequent changes are recommended.

#### Other skin and body protection

Appropriate footwear and additional protective clothing complying with an approved standard should be worn if a risk assessment indicates skin contamination is possible.

#### Hygiene measures

Provide eyewash station and safety shower. Contaminated work clothing should not be allowed out of the workplace. Wash contaminated clothing before reuse. Clean equipment and the work area every day. Good personal hygiene procedures should be implemented. Wash at the end of each work shift and before eating, smoking and using the toilet. When using do not eat, drink or smoke. Preventive industrial medical examinations should be carried out. Warn cleaning personnel of any hazardous properties of the product.

## Poly HP-2

<b>Respiratory protection</b>	Respiratory protection complying with an approved standard should be worn if a risk assessment indicates inhalation of contaminants is possible. Ensure all respiratory protective equipment is suitable for its intended use and is NIOSH approved. Check that the respirator fits tightly and the filter is changed regularly. Gas and combination filter cartridges should comply with OSHA 1910.134. Full face mask respirators with replaceable filter cartridges should comply with OSHA 1910.134. Half mask and quarter mask respirators with replaceable filter cartridges should comply with OSHA 1910.134.
<b>Environmental exposure controls</b>	Keep container tightly sealed when not in use.

### 9. Physical and chemical properties

#### Information on basic physical and chemical properties

<b>Appearance</b>	Solid.
<b>Color</b>	Red.
<b>Odor</b>	Mild.
<b>Odor threshold</b>	Not available.
<b>pH</b>	Not available.
<b>Melting point</b>	Not available.
<b>Initial boiling point and range</b>	>288°C (>550.4°F)
<b>Flash point</b>	> 246°C/475°F Cleveland open cup.
<b>Evaporation rate</b>	< 0.01 (butyl acetate = 1)
<b>Upper/lower flammability or explosive limits</b>	Not available.
<b>Vapor pressure</b>	Not available.
<b>Vapor density</b>	Not available.
<b>Relative density</b>	0.89
<b>Solubility(ies)</b>	Insoluble in water.
<b>Partition coefficient</b>	Not available.
<b>Auto-ignition temperature</b>	Not available.
<b>Decomposition Temperature</b>	Not available.
<b>Viscosity</b>	Not available.
<b>Explosive properties</b>	Not applicable.
<b>Oxidizing properties</b>	Not available.
<b>Other information</b>	None.

### 10. Stability and reactivity

<b>Reactivity</b>	See the other subsections of this section for further details.
<b>Stability</b>	Stable at normal ambient temperatures and when used as recommended. Stable under the prescribed storage conditions.

## Poly HP-2

<b>Possibility of hazardous reactions</b>	No potentially hazardous reactions known.
<b>Conditions to avoid</b>	There are no known conditions that are likely to result in a hazardous situation.
<b>Materials to avoid</b>	No specific material or group of materials is likely to react with the product to produce a hazardous situation.
<b>Hazardous decomposition products</b>	Does not decompose when used and stored as recommended. Thermal decomposition or combustion products may include the following substances: Harmful gases or vapors.

### 11. Toxicological information

#### Information on toxicological effects

##### Acute toxicity - oral

**Summary** Based on available data the classification criteria are not met.

**Notes (oral LD<sub>50</sub>)** Based on available data the classification criteria are not met.

##### Acute toxicity - dermal

**Summary** Based on available data the classification criteria are not met.

**Notes (dermal LD<sub>50</sub>)** Based on available data the classification criteria are not met.

##### Acute toxicity - inhalation

**Summary** Based on available data the classification criteria are not met.

**Notes (inhalation LC<sub>50</sub>)** Based on available data the classification criteria are not met.

##### Skin corrosion/irritation

**Summary** Based on available data the classification criteria are not met.

**Animal data** Based on available data the classification criteria are not met.

##### Serious eye damage/irritation

**Summary** Based on available data the classification criteria are not met.

**Serious eye damage/irritation** Based on available data the classification criteria are not met.

##### Respiratory sensitization

**Summary** Based on available data the classification criteria are not met.

**Respiratory sensitization** Based on available data the classification criteria are not met.

##### Skin sensitization

**Summary** May cause an allergic skin reaction.

**Skin sensitization** May cause skin sensitization or allergic reactions in sensitive individuals.

##### Germ cell mutagenicity

**Summary** Based on available data the classification criteria are not met.

**Genotoxicity - in vitro** Based on available data the classification criteria are not met.

##### Carcinogenicity

**Summary** Based on available data the classification criteria are not met.

**Carcinogenicity** Based on available data the classification criteria are not met.

**IARC carcinogenicity** None of the ingredients are listed or exempt.

##### Reproductive toxicity

## Poly HP-2

<b>Summary</b>	Based on available data the classification criteria are not met.
<b>Reproductive toxicity - fertility</b>	Based on available data the classification criteria are not met.
<b>Reproductive toxicity - development</b>	Based on available data the classification criteria are not met.
<b><u>Specific target organ toxicity - single exposure</u></b>	
<b>Summary</b>	Based on available data the classification criteria are not met.
<b>STOT - single exposure</b>	Not classified as a specific target organ toxicant after a single exposure.
<b><u>Specific target organ toxicity - repeated exposure</u></b>	
<b>Summary</b>	Based on available data the classification criteria are not met.
<b>STOT - repeated exposure</b>	Not classified as a specific target organ toxicant after repeated exposure.
<b><u>Aspiration hazard</u></b>	
<b>Summary</b>	Not relevant. Solid.
<b>Aspiration hazard</b>	Not relevant. Solid.
<b><u>General information</u></b>	
	The severity of the symptoms described will vary dependent on the concentration and the length of exposure.
<b>Inhalation</b>	A single exposure may cause the following adverse effects: Temporary irritation.
<b>Ingestion</b>	May cause sensitization or allergic reactions in sensitive individuals. May cause discomfort if swallowed. May cause stomach pain or vomiting.
<b>Skin Contact</b>	May cause skin sensitization or allergic reactions in sensitive individuals. Prolonged contact may cause dryness of the skin.
<b>Eye contact</b>	May be slightly irritating to eyes.
<b>Route of exposure</b>	Ingestion Inhalation Skin and/or eye contact
<b>Target Organs</b>	No specific target organs known.
<b>Medical considerations</b>	Skin disorders and allergies.

### 12. Ecological information

<b>Ecotoxicity</b>	Not regarded as dangerous for the environment. However, large or frequent spills may have hazardous effects on the environment.
<b>Toxicity</b>	Based on available data the classification criteria are not met.
<b><u>Acute aquatic toxicity</u></b>	
<b>Summary</b>	Based on available data the classification criteria are not met.
<b><u>Chronic aquatic toxicity</u></b>	
<b>Summary</b>	Based on available data the classification criteria are not met.
<b><u>Persistence and degradability</u></b>	
<b>Persistence and degradability</b>	The degradability of the product is not known.
<b><u>Bioaccumulative potential</u></b>	
<b>Bio-Accumulative Potential</b>	No data available on bioaccumulation.
<b>Partition coefficient</b>	Not available.



## Poly HP-2

### Mobility in soil

**Mobility** No data available.

### Other adverse effects

**Other adverse effects** None known.

## 13. Disposal considerations

### Waste treatment methods

#### **General information**

The generation of waste should be minimized or avoided wherever possible. Reuse or recycle products wherever possible. This material and its container must be disposed of in a safe way. Disposal of this product, process solutions, residues and by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any local authority requirements. When handling waste, the safety precautions applying to handling of the product should be considered. Care should be taken when handling emptied containers that have not been thoroughly cleaned or rinsed out. Empty containers or liners may retain some product residues and hence be potentially hazardous.

#### **Disposal methods**

Do not empty into drains. Dispose of surplus products and those that cannot be recycled via a licensed waste disposal contractor. Waste, residues, empty containers, discarded work clothes and contaminated cleaning materials should be collected in designated containers, labeled with their contents. Incineration or landfill should only be considered when recycling is not feasible.

## 14. Transport information

#### **General**

The product is not covered by international regulations on the transport of dangerous goods (IMDG, IATA, DOT).

#### UN Number

**UN No. (International)** Not applicable.

#### UN proper shipping name

**Proper shipping name (International)** Not applicable.

#### Transport hazard class(es)

**Transport Labels (International)** No transport warning sign required.

#### **Transport labels**

No transport warning sign required.

#### **DOT transport labels**

No transport warning sign required.

#### Packing group

**Packing group (International)** Not applicable.

#### Environmental hazards

#### **Environmentally Hazardous Substance**

No.

#### Special precautions for user

Not applicable.

#### **DOT TIH Zone**

Not applicable.

## Poly HP-2

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code Not applicable.

### 15. Regulatory information

**Regulatory References** OSHA Hazard Communication Standard 29 CFR §1910.1200

#### US Federal Regulations

**SARA Section 302 Extremely Hazardous Substances Tier II Threshold Planning Quantities**

None of the ingredients are listed or exempt.

**CERCLA/Superfund, Hazardous Substances/Reportable Quantities (EPA)**

None of the ingredients are listed or exempt.

**SARA Extremely Hazardous Substances EPCRA Reportable Quantities**

None of the ingredients are listed or exempt.

**SARA 313 Emission Reporting**

None of the ingredients are listed or exempt.

**CAA Accidental Release Prevention**

None of the ingredients are listed or exempt.

**FDA - Essential Chemical**

None of the ingredients are listed or exempt.

**FDA - Precursor Chemical**

None of the ingredients are listed or exempt.

**SARA (311/312) Hazard Categories**

Respiratory or skin sensitization

**OSHA Highly Hazardous Chemicals**

None of the ingredients are listed or exempt.

#### US State Regulations

**California Proposition 65 Carcinogens and Reproductive Toxins**

None of the ingredients are listed or exempt.

**California Air Toxics "Hot Spots" (A-I)**

None of the ingredients are listed or exempt.

**California Air Toxics "Hot Spots" (A-II)**

None of the ingredients are listed or exempt.

**California Directors List of Hazardous Substances**

The following ingredients are listed or exempt:

*Tetrasodium pyrophosphate*

**Massachusetts "Right To Know" List**

The following ingredients are listed or exempt:

*Tetrasodium pyrophosphate*

## Poly HP-2

### Rhode Island "Right To Know" List

The following ingredients are listed or exempt:

*Tetrasodium pyrophosphate*

### Minnesota "Right To Know" List

The following ingredients are listed or exempt:

*Tetrasodium pyrophosphate*

### New Jersey "Right To Know" List

The following ingredients are listed or exempt:

*Tetrasodium pyrophosphate*

### Pennsylvania "Right To Know" List

The following ingredients are listed or exempt:

*Tetrasodium pyrophosphate*

### Inventories

#### US - TSCA

All the ingredients are listed or exempt.

#### US - TSCA 12(b) Export Notification

None of the ingredients are listed or exempt.

### 16. Other information

#### Abbreviations and acronyms used in the safety data sheet

TDG: The transport of dangerous goods act

IATA: International air transport association.

ICAO: Technical instructions for the safe transport of dangerous goods by air.

IMDG: International maritime dangerous goods.

CAS: Chemical abstracts service.

ATE: Acute toxicity estimate.

LC<sub>50</sub>: Lethal concentration to 50 % of a test population.

LD<sub>50</sub>: Lethal dose to 50% of a test population (median lethal dose).

EC<sub>50</sub>: 50% of maximal effective concentration.

PBT: Persistent, bioaccumulative and toxic substance.

vPvB: Very persistent and very bioaccumulative.

#### Classification abbreviations and acronyms

Skin Sens. = Skin sensitisation

#### Training advice

Read and follow manufacturer's recommendations. Only trained personnel should use this material.

#### Revision comments

Revised classification.

#### Revision date

5/10/2022

#### Revision

2

#### Supersedes date

8/19/2021

#### SDS No.

4930

## Poly HP-2

### Hazard statements in full

H302 Harmful if swallowed.

H312 Harmful in contact with skin.

H315 Causes skin irritation.

H317 May cause an allergic skin reaction.

H319 Causes serious eye irritation.

H411 Toxic to aquatic life with long lasting effects.

H413 May cause long lasting harmful effects to aquatic life.

### End of SDS

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty, guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.