

## **SECTION 1. INDENTIFICATION**

Product Name: Sea Foam Finish Fast Interior Detailer

Item #:ID24Other name/SDS identifier:W447eChemical Name:MixtureCAS No:MixtureDate Issued/Modified11/21/2019

**Recommended use:** Spray on, wipe off detailer.

**Recommended Restrictions:** None known

Manufacturer/Supplier/Distributor

information Sea Foam Sales Company.

Company name: 510 North Chestnut. Address: Chaska, IL 55318

United States of America

**Telephone:** (952) 938-4811

**Emergency Telephone number**: Infotrac 24 hr.: 1 (800) 535-5053

International: +1 (352) 323-3500

## **SECTION 2. HAZARDS IDENTIFICATION**

#### Classification of substance or mixture

GHS-US classification (29 CFR 1910.1200):

Eye irritant, Category 2.

Label elements (GHS)



Hazard Symbol(s):
Signal Word(s):
Warning!

## **Precautionary Measures**

Wear eye protection and use under ventilation.

### SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

This product is a mixture.

Ingredients*	% w	CAS No.
Proprietary Mixture	100	

<sup>\*</sup>Product does not contain other hazardous components at reportable quantities.



## **SECTION 4. FIRST-AID MEASURES**

**Inhalation:** Remove from area of exposure. If not breathing, give artificial respiration. If

breathing is difficult, give oxygen. Get immediate medical attention if symptoms

persist.

**Skin contact:** Remove contaminated clothing and wash with plenty of soap and water.

**Eye contact:** Rinse cautiously with water for several minutes. Remove contact lenses, if present

and easy to do. Continue rinsing. Get medical attention if symptoms persist.

**Ingestion:** Do not induce vomiting. Treat symptomatically.

**Most important symptoms:** Potential for eye irritation.

**Indication of any immediate medical attention and special treatment needed**None known.

## **SECTION 5. FIRE FIGHTING MEASURES**

**Extinguishing Media** 

**Suitable extinguishing media:** Carbon dioxide, dry chemical, foam, water fog.

**Unsuitable extinguishing media:** Water-jet.

**Unusual fire and explosion hazards:** Vapors/dust may cause flash fire or explosion.

Advice for fire-fighters: As in any fire, wear self-contained breathing apparatus and

complete protective clothing. Use water spray to cool

containers or protect personnel. Use with caution and avoid

use of solid water streams.

### SECTION 6. ACCIDENTAL RELEASE MEASURES

#### Personal precautions, protective equipment and emergency procedures:

Avoid contact with eyes and skin. Work under sufficient ventilation. Eliminate all ignition sources if safe to do so. Avoid breathing fume/gas/mist/vapors/spray.

## **Environmental precautions:**

Prevent release to the environment. Prevent liquid entering sewers, basements and work pits. Collect spills.

#### Methods and material for containment and cleaning up:

Contain spillages with absorbent material (sand, earth, universal binder or any suitable material). Dispose of absorbed material in accordance with the regulations.

#### **SECTION 7. HANDLING AND STORAGE**

#### **Precautions for safe handling:**

Avoid eye contact and wear protective clothing. Wash thoroughly after handling. Use in a well ventilated area.

## Conditions for safe storage, including any incompatibilities

Store in tightly closed containers at room temperature in well ventilated area.

Prevent contact with heat, sparks, flame and oxidizers.

#### SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

United States 11/21/2019 Page 2/4



## **Ingredients with exposure limits:**

Isopropyl alcohol (CAS: 67-63-0)

OSHA Z1, 02/2006; PEL: 400 ppm, 980 mg/m3.

## **Exposure Controls**

## **Engineering controls**

Proper industrial hygiene, including ready access to eye-wash station, is recommended for a work-place.

## **Personal Protective equipment**

Personal protective equipment including safety glasses, nitrile gloves and body-covering clothing are recommended.

#### SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

**Appearance:** Liquid.

Odor: alcohol, fruity. Odor threshold: Not available.

**pH:** 6.5-7.5

Melting point/freezing point:Not available.Boiling point:Not available.Flash point:>212 °F (>100 °C)Evaporation rate:Not available.Flammability (solid, gas):Not available.Explosive limit ranges:Not available.

**Specific Gravity:** .99g/ml

Vapor pressure:

Vapor Density:

Not available.

Not available.

1 mg/mL.

**Solubility in water:** Soluble/dispersible; product is mostly water.

**Viscosity:** Water-like.

**Volatile organic content:** <3%.

## **SECTION 10. STABILITY AND REACTIVITY**

**Reactivity:** Product is not expected to be a reactivity hazard if used as

supplied.

**Chemical stability:** Stable under normal condition.

**Possibility of hazardous reactions:** None known.

Conditions to avoid: Ignition sources and excess heat. Incompatible materials: Strong oxidizing agents and acids.

**Hazardous decomposition products:** Thermal decomposition can release toxic fumes and gasses

including carbon monoxide and carbon dioxide.

#### SECTION 11. TOXICOLOGICAL INFORMATION

The toxicological effect of this product has not been tested. The information below has been compiled from the data reported for the concentrated individual components.

United States 11/21/2019 Page 3/4



Isopropyl alcohol (CAS: 67-63-0): Contact through eye, skin, inhalation and ingestion are primary routes of entry. Inhalation can cause irritation of respiratory tract and dizziness and drowsiness. Prolonged and repeated skin contact can result in skin defatting, irritation and rash. Eye contact will cause serious irritation and ingestion can cause irritation in mouth, throat and stomach. Oral LD 50: 4396 mg/kg; Dermal LD50: 12870 mg/kg; vapor LC50: 46.6 mg/L.

### **SECTION 12. ECOLOGICAL INFORMATION**

The ecological effect of this product has not been tested. The information below has been compiled from the data reported for the concentrated individual components. Product is not expected bio-accumulate and is not expected cause severe ecological harm.

### **SECTION 13. DISPOSAL CONSIDERATIONS**

Waste treatment methods: Disposal should be in accordance with local, state or national

legislation. Consult an accredited waste disposal contractor or the

local authority for advice.

**Additional information:** None known

#### SECTION 14. TRANSPORT INFORMATION

Not regulated for **Road Transport** (**USDOT**)

Not regulated for **Sea Transport (IMDG)** 

Not regulated for Air Transport (ICAO-IATA/DGR)

## **SECTION 15. REGULATORY INFORMATION**

#### TSCA (Toxic Substance Control Act)

All components are registered in the US EPA TSCA inventory list or are exempted.

**SARA Title III** 

Section 302: None known. Section 304: None known.

**Section 312**: Acute (immediate): yes; Chronic: yes; Fire: yes; Pressure: no; Reactive: no.

### California Proposition 65:

No component of this product is classified by the State of California to cause cancer, birth defects or other reproductive harm.

#### **SECTION 16. OTHER INFORMATION**

Date of first issue: Sept 20, 2019 Updated: November 21, 2019

**Disclaimer**: Information provided in this document is presented in good faith and is believed to be correct at the time of preparation. No guarantee of completeness, accuracy or reliability is made and the Sea Foam Sales Company does not accept any liability for damages and losses resulting from the use or reliance of the information herein. This document is designed to provide the user guidance on safe handling, storage, etc., and it is entirely up to the user to determine the completeness of information and its suitability for their purpose.

United States 11/21/2019 Page 4/4