## **SAFETY DATA SHEET**

## SECTION 1 – PRODUCT AND COMPANY IDENTIFICATION

Product Identifier : Henry® FRC Vinyl/Linoleum Repair Adhesive

Product Code : 700118324

Trade Name/Synonyms : Henry Vinyl and Linoleum Repair, LIREP Recommended Use : Polymer emulsion-based adhesive.

Uses Advised Against : Use only as recommended in the product's Technical Data Sheet.

Manufacturer's name and address:

ARDEX L.P.

400 Ardex Park Drive

Aliquippa, PA 15001 USA

Information Telephone No. : (800) 232-4832 or (724) 203-8000 Website Address : http://www.ardexamericas.com

24 Hr Emergency Telephone # : CHEM-TEL: 1-800-255-3924 OR 1-813-248-0585 (call collect)

## **SECTION 2 – HAZARDS IDENTIFICATION**

GHS Classification per 29 CFR 1910.1200 (OSHA HCS 2012) and HPR (WHMIS 2015)

Not classified as hazardous.

**GHS Pictograms** 

None.

Signal Word

None.

**Hazard Statements** 

None.

Safe Handling Instructions: Avoid eye and skin contact. It is recommended to use safety glasses and

gloves during handling. During installation process, adequate ventilation of the work area should be maintained. Although the adhesive is low VOC, persons who are sensitive to odors or chemicals should avoid the work area during

installation. Keep container closed.

During normal usage of the product as recommended, airborne dusts and mists will

not be present. See Section 7 (Handling and Storage) for further details.

**Hazards Not Otherwise Classified** 

None.

% with Unknown Acute Toxicity

5% of this product consists of ingredients with unknown acute toxicity.

# **SECTION 3 – COMPOSITION/INFORMATION ON INGREDIENTS**

Ingredients	CAS#	% (by weight)
Barium sulfate	7727-43-7	1 – 5

# **SECTION 4 – FIRST AID MEASURES**

General : Call a Poison Center or doctor if you feel unwell.

Inhalation : Remove person to fresh air and keep at rest in a position comfortable for

breathing.-Get medical attention.

**Skin contact**: Remove contaminated clothing. Flush affected skin with water. If irritation or

rash occurs, seek medical attention/advice.

Eye contact : Rinse cautiously with water for several minutes. Remove contact lenses, if

present and easy to do. Continue rinsing. Get medical attention.

Ingestion : Rinse mouth. Do NOT induce vomiting. Call a POISON CENTER or

doctor/physician if you feel unwell.

Notes for Physician : Treat symptomatically.

## Signs and symptoms of short-term (acute) exposure

Inhalation : None known.

Skin : Symptoms may include mild redness or itching.

Eyes : Symptoms may include mild redness, itching, or pain.

Ingestion : None known.

### Effects of long-term (chronic) exposure

: None known.

### Indication of need for immediate medical attention or special treatment

: Difficulty breathing persists after removing the person to fresh air.

Any exposure to the eye which causes irritation.

# **SECTION 5 – FIRE FIGHTING MEASURES**

Suitable extinguishing media

: Carbon dioxide, dry chemical powder, water, alcohol foam or water spray.

Unsuitable extinguishing media

None known.

**Hazardous combustion products** 

Carbon monoxide, carbon dioxide, as well as other toxic vapors and gases which

are common to thermal degradation of organic compounds.

## Special fire-fighting procedures/equipment

Firefighters should wear proper protective equipment and self-contained breathing apparatus with full face piece operated in positive pressure mode. Move containers from fire area if safe to do so. Water spray may be useful in cooling equipment exposed to heat and flame. After fires have been extinguished, carefully clean all

equipment and surfaces exposed to fumes.

**Environmental precautions** : Do not allow material to enter drains or contaminate ground water system.

# Fire hazards/conditions of flammability

: Not flammable under normal conditions of use. Closed containers may rupture if

exposed to excess heat or flame due to a build-up of internal pressure.

### Flammability classification (OSHA 29 CFR 1910.1200, WHMIS 2015)

: Not flammable.

NFPA Rating : <u>0 - Minimal 1 - Slight 2 - Moderate 3 - Serious 4 - Severe</u>

Health: 1 Flammability 1 Instability 0 Special Hazards: None

# SECTION 6 – ACCIDENTAL RELEASE MEASURES

Personal precautions : Restrict access to area until completion of clean-up. All persons dealing with

clean-up should wear the appropriate chemically protective equipment.

Protective equipment : Refer to Section 8 for additional information on acceptable personal protective

equipment.

Emergency Procedures : This product does not contain chemicals requiring EPA notification for spills. In

case of a chemical spill, call the emergency telephone number listed in Section

1.

US CERCLA Reportable quantity (RQ): None reported.

### Methods and materials for containment and cleaning up

: Ventilate area of release. Stop spill or leak at source if safely possible. Contain product with inert absorbent material, preventing it from entering sewer lines or waterways. Gather up spilled material and place in suitable container for later disposal (see Section 13). Residual of product, while still wet, can be cleaned up with warm soapy water. Notify the appropriate authorities as required.

Prohibited materials

: None known.

**Environmental precautions** 

: Do not allow product to enter drains or waterways. Do not allow material to

contaminate ground water system.

Reference to other sections

: See Section 13 for disposal information.

## **SECTION 7 – HANDLING AND STORAGE**

Safe handling procedures : Wear suitable protective equipment during handling. (See Section 8.) Observe

good hygiene standards. Use only with adequate ventilation. Wash thoroughly after handling. Avoid contact with eyes, skin, or clothing. Sanding and grinding dusts may be harmful if inhaled. When removing this product from existing flooring (i.e. during a renovation), wear safety goggles and respiratory protection from dust due to grinding, chipping, or mechanically pulverizing. Keep container tightly closed.

**Storage requirements** : Store in a cool, dry, well-ventilated area. Store away from heat and open flame.

Avoid storing in direct sunlight. Store in original container. Keep tightly closed when not in use. Do not reuse empty container without commercial cleaning or

reconditioning.

Incompatible materials

: See Section 10.

Special packaging materials

: Always keep in containers made of the same materials as the supply container.

# **SECTION 8 – EXPOSURE CONTROLS AND PERSONAL PROTECTION**

**Permissible Exposure Limits** 

: No exposure limits have been established for the product itself. Below are exposure limits for the components in the product.

Ingredients	CAS#	ACGIH TLV		OSHA PEL	
		TWA	STEL	PEL	STEL
Barium sulfate	7727-43-7	10 mg/m <sup>3</sup>	N/Av	15 mg/m <sup>3</sup> (total dust) 5 mg/m3 (respirable)	N/Av

**Engineering Controls** 

: Use general or local exhaust ventilation to maintain air concentrations below recommended exposure limits. Ventilation should effectively remove and prevent buildup of any vapor generated from the handling of this product.

**Personal Protection Equipment** 

Eye / face protection

: Chemical goggles or safety glasses, as appropriate for the job.

Skin protection

: Wear gloves which are impervious to the material. Materials such as nitrile rubber

or Viton (fluorocarbon rubber) are recommended.

**Body protection** 

: Where extensive exposure to product is possible, use resistant coveralls, apron and

boots to prevent contact.

Respiratory protection

Under normal conditions of use with adequate ventilation, respiratory protection should not be necessary. If work process generates excessive quantities of vapor or dust, or exposures in excess of any PEL, wear an appropriate organic vapor

respirator.

Site safety equipment

An eyewash station and safety shower should be made available in the immediate working area.

General hygiene considerations

: Avoid contact with eyes, skin and clothing. Avoid breathing vapors/dust. Do not eat, drink or smoke when using this product. Upon completion of work, wash hands thoroughly. Remove soiled clothing and wash it thoroughly before reuse. Clean all equipment and clothing at end of each work shift.

## **SECTION 9 – PHYSICAL AND CHEMICAL PROPERTIES**

Physical state : Paste Appearance : Off-white paste

Odor Mild Odor threshold : N/Av рΗ Specific gravity : 1.05 : 8.5 - 8.7**Boiling point** : 212°F (100°C) Coefficient of water/oil distribution : N/Av Melting/Freezing point Solubility in water : Dispersible : N/Av Vapor pressure (mm Hg @ 20°C / 68°F) : N/Av Evaporation rate (n-Butyl acetate = 1) : N/Av Vapor density (Air = 1) : N/Av Volatiles (% by weight) : 35.5 – 37.5

Volatile organic compounds (VOCs) : 0 g/L SCAQMD 1168

Particle size : N/Av Flammability classification : Not flammable Flash point : >93.3°C (>200°F) Lower flammable limit (% by vol) : Not available Flash point method : Setaflash closed Upper flammable limit (% by vol) : Not available **Auto-ignition temperature Decomposition temperature** : N/Av : Not available Viscosity : N/Av **Oxidizing properties** : Not available

Explosion data: Sensitivity to mechanical impact / static discharge

: Not expected to be sensitive to mechanical impact or static discharge.

## **SECTION 10 – REACTIVITY AND STABILITY INFORMATION**

Reactivity : Not reactive.

Stability : Stable under the recommended storage and handling conditions prescribed.

**Hazardous reactions** : Hazardous polymerization does not occur.

Conditions to avoid : Extreme heat.

Materials to avoid and incompatability

: Strong oxidizing agents.

Hazardous decomposition products

: None known, refer to hazardous combustion products in Section 5.

## **SECTION 11 – TOXICOLOGICAL INFORMATION**

Routes of exposure : Inhalation: YES Skin Absorption: NO Skin and Eyes: Yes Ingestion: YES

Symptoms of exposure : See Section 4.

Calculated Acute Toxicity Estimates for the Product

**Toxicological data** : See below for individual ingredient acute toxicity data.

	LC50 (4 hr)	LD50		
Ingredients	Inhalation, rat	Oral, rat	Dermal, rabbit	
Barium sulfate	N/Av	N/Av	N/Av	

**Skin corrosion or irritation** : May cause mild irritation to skin.

Serious eye damage / eye irritation : May cause mild, temporary irritation to eyes.

**Respiratory or skin sensitization** : None known. **Germ cell mutagenicity** : None known.

Carcinogenic status : This product contains less than 0.1% of any component classified as carcinogenic

by IARC, ACGIH, NTP, and OSHA. During normal usage of the product as recommended, airborne dusts will not be produced. See Section 7 for more

information.

Reproductive toxicity : None known.

Specific Target Organ Toxicity, Single Exposure

: None known.

Specific Target Organ Toxicity, Repeated Exposure

: None known.

**Aspiration hazard** : None known.

Additional information : N/Av

# **SECTION 12 – ECOLOGICAL INFORMATION**

Environmental effects : The product should not be allowed to enter drains or water courses or be deposited

where it can affect ground or surface waters.

 Ecotoxicity
 : No data available.

 Biodegradability
 : No data available.

 Bioaccumulative potential
 : No data available.

 Mobility in soil
 : No data available.

 PBT and vPvB assessment
 : No data available.

 Other adverse effects
 : No data available.

## **SECTION 13 – DISPOSAL CONSIDERATION**

Handling for disposal : Handle waste according to recommendations in Section 7.

Methods of disposal : Dispose in accordance with all applicable federal, state, provincial and local

regulations. Contact your local, state, provincial or federal environmental agency

for specific rules.

Packaging : Handle contaminated packaging in the same manner as the product.

RCRA : For disposal of unused or waste material, check with local, state and federal

environmental agencies.

## **SECTION 14 – TRANSPORTATION INFORMATION**

Regulatory Information	UN Number	Shipping Name	Class	Packing Group	Label
TDG	None	This product is not regulated according to Canadian TDG regulations.	None	None	None
TDG Additional Information	None				
49 CFR/DOT	None	This product is not regulated according to US DOT regulations.	None	None	None
49 CFR/DOT Additional Information	None				

Not regulated by IMDG. Not regulated by IATA. Not a Marine Pollutant.

## SECTION 15 – REGULATORY INFORMATION

## Canadian Information:

This product has been classified according to the hazard criteria of the Hazardous Products Regulations (HPR). This SDS contains all information required by the HPR.

Canadian Environmental Protection Act (CEPA) information: All ingredients appear on the Domestic Substances List (DSL).

### **US Federal Information:**

TSCA: All ingredients appear on the Toxic Substances Control Act (TSCA) inventory.

CERCLA Reportable Quantity (RQ) (40 CFR 117.302): None reported.

SARA TITLE III: Sec. 302, Extremely Hazardous Substances, 40 CFR 355: No Extremely Hazardous Substances are present in this material.

SARA TITLE III: Sec. 311 and 312, SDS Requirements, 40 CFR 370 Hazard Classes: Not Hazardous.

SARA TITLE III: Sec. 313, Toxic Chemicals Notification, 40 CFR 372: This product is not subject to SARA notification requirements, since it does not contain any Toxic Chemical constituents above *de minimus* concentrations.

#### **U.S. State Right To Know Laws**

California Proposition 65: See product label for information regarding Proposition 65.

Other State Right to Know Laws: Barium sulfate [CAS No. 7727-43-7] (MA, NJ, PA).

## **SECTION 16 – OTHER INFORMATION**

HMIS Rating : \*- Chronic Hazard 0 - Minimal 1 - Slight 2 - Moderate 3 - Serious 4 - Severe

Health: 1 Flammability 1 Physical Hazard: 0 PPE: Gloves, safety glasses

Legend : ACGIH: American Conference of Governmental Industrial Hygienists

CAS: Chemical Abstract Services

CERCLA: Comprehensive Environmental Response, Compensation, and Liability

Act of 1980

CFR: Code of Federal Regulations DOT: Department of Transportation DSL: Domestic Substances List EPA: Environmental Protection Agency GHS: Globally Harmonized System HPR: Hazardous Products Regulations

IARC: International Agency for Research on Cancer

Inh: Inhalation N/Av: Not Available N/Ap: Not Applicable

NIOSH: National Institute of Occupational Safety and Health

NTP: National Toxicology Program

OSHA: Occupational Safety and Health Administration

PEL: Permissible exposure limit

RCRA: Resource Conservation and Recovery Act SARA: Superfund Amendments and Reauthorization Act

STEL: Short Term Exposure Limit

TDG: Canadian Transportation of Dangerous Goods Act & Regulations

TLV: Threshold Limit Values TSCA: Toxic Substance Control Act TWA: Time Weighted Average

WHMIS: Workplace Hazardous Materials Identification System

### **Disclaimer of Liability**

The Information presented herein is supplied as a guide to those who handle or use this product and has been prepared in good faith by technically knowledgeable personnel. It is not intended to be all-inclusive. The manner and conditions of use and handling may involve other and additional considerations. Safe work practices must be employed when working with any materials. It is important that the end user determines the adequacy of the safety procedures employed during the use of this product. No warranty of any kind is given or implied. ARDEX L.P. will not be liable for any damages, losses, injuries or consequential damages which may result from the use or reliance on any information contained herein.

### Prepared By:

ARDEX L.P. 400 Ardex Park Drive Aliquippa, PA, U.S.A. 15001

(724) 203-8000

Visit our Website: http://www.ardexamericas.com

Revision date: : 12-May-2019

**End of Document**