



Brute Strength. Professional Grade.™

SAFETY DATA SHEET

GorillaPro® CA500RT

Version 1.0

Revision Date 01/12/2022

SECTION 1. PRODUCT AND COMPANY IDENTIFICATION

Product name : GorillaPro® CA500RT
Product code : 100000013113

Manufacturer or supplier's details

Company : H.B. Fuller Company
Address : 9001 W Fey Drive
Frankfort, IL, 60423
Telephone : 1-815-464-5606

Medical Emergency Phone Number (24 Hours): 1-888-853-1758

Transport Emergency Phone Number (CHEMTREC): 1-800-424-9300

Recommended use of the chemical and restrictions on use

Recommended use : Cyanoacrylate Adhesive
Restrictions on use : For industrial use only.

SECTION 2. HAZARDS IDENTIFICATION

Emergency Overview

Appearance	liquid
Color	black
Odor	pungent

GHS Classification

Flammable liquids : Category 4
Skin irritation : Category 2
Eye irritation : Category 2A
Skin sensitization : Category 1
Carcinogenicity : Category 2
Specific target organ toxicity - single exposure : Category 3 (Respiratory system)

GHS label elements

Hazard pictograms :





Brute Strength. Professional Grade.™

SAFETY DATA SHEET

GorillaPro® CA500RT

Version 1.0

Revision Date 01/12/2022

Signal Word : Warning

Hazard Statements:

H227 Combustible liquid. H315 Causes skin irritation. H317 May cause an allergic skin reaction. H319 Causes serious eye irritation. H335 May cause respiratory irritation. H351 Suspected of causing cancer.

Precautionary Statements:

Prevention: P201 Obtain special instructions before use. P202 Do not handle until all safety precautions have been read and understood. P210 Keep away from heat/ sparks/ open flames/ hot surfaces. No smoking. P261 Avoid breathing dust/ fume/ gas/ mist/ vapors/ spray. P264 Wash skin thoroughly after handling. P271 Use only outdoors or in a well-ventilated area. P272 Contaminated work clothing must not be allowed out of the workplace. P280 Wear protective gloves/ protective clothing/ eye protection/ face protection.

Response: P302 + P352 IF ON SKIN: Wash with plenty of soap and water. P304 + P340 + P312 IF INHALED: Remove person to fresh air and keep comfortable for breathing. Call a POISON CENTER/ doctor if you feel unwell. P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. P308 + P313 IF exposed or concerned: Get medical advice/ attention. P333 + P313 If skin irritation or rash occurs: Get medical advice/ attention. P337 + P313 If eye irritation persists: Get medical advice/ attention. P362 Take off contaminated clothing and wash before reuse. P370 + P378 In case of fire: Use dry sand, dry chemical or alcohol-resistant foam to extinguish.

Storage: P403 + P233 Store in a well-ventilated place. Keep container tightly closed. P403 + P235 Store in a well-ventilated place. Keep cool. P405 Store locked up.

Disposal: P501 Dispose of contents/ container to an approved waste disposal plant.

Potential Health Effects

Carcinogenicity:

IARC

Group 2B: Possibly carcinogenic to humans During normal handling of the product, this substance is encapsulated within the product and will not present a cancer exposure risk.

Carbon black

1333-86-4

Group 2B: Possibly carcinogenic to humans

OSHA

No component of this product present at levels greater than or equal to 0.1% is on OSHA's list of regulated carcinogens.

NTP

No ingredient of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Substance / Mixture : Mixture

Hazardous ingredients



Brute Strength. Professional Grade.™

SAFETY DATA SHEET

GorillaPro® CA500RT

Version 1.0

Revision Date 01/12/2022

Chemical name	CAS-No.	Concentration [%]
ethyl 2-cyanoacrylate	7085-85-0	90 - 100
Carbon black	1333-86-4	0.1 - 1
hydroquinone	123-31-9	0.1 - 1

Actual concentration is withheld as a trade secret

SECTION 4. FIRST AID MEASURES

- General advice : Show this material safety data sheet to the doctor in attendance.
- If inhaled : Move to fresh air.
If not breathing, give artificial respiration.
Keep patient warm and at rest.
Consult a physician after significant exposure.
- In case of skin contact : Wash off immediately with soap and plenty of water.
Call a physician if irritation develops or persists.
Cyanoacrylate. Danger. Bonds skin and eyes in seconds.
Keep out of the reach of children.
- In case of eye contact : Rinse immediately with plenty of water, also under the eyelids.
Seek medical advice.
- If swallowed : If swallowed, call a poison control center or doctor immediately.
Do not induce vomiting without medical advice.

SECTION 5. FIRE-FIGHTING MEASURES

- Suitable extinguishing media : Use water spray, alcohol-resistant foam, dry chemical or carbon dioxide.
- Unsuitable extinguishing media : Water spray jet
- Hazardous combustion products : Nitrogen oxides (NO_x)
- Specific extinguishing methods :
- Further information : Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
- Special protective equipment for fire-fighters : Wear an approved positive pressure self-contained breathing apparatus in addition to standard fire fighting gear.



Brute Strength. Professional Grade.™

SAFETY DATA SHEET

GorillaPro® CA500RT

Version 1.0

Revision Date 01/12/2022

SECTION 6. ACCIDENTAL RELEASE MEASURES

- Personal precautions, protective equipment and emergency procedures : Refer to protective measures listed in sections 7 and 8.
Ensure adequate ventilation.
- Environmental precautions : Prevent product from entering drains.
Do not flush into surface water or sanitary sewer system.
- Methods and materials for containment and cleaning up : Allow to solidify.
Pick up and transfer to properly labeled containers.
Ventilate the area.

SECTION 7. HANDLING AND STORAGE

- Local/Total ventilation : Use only with adequate ventilation.
- Advice on safe handling : Wear personal protective equipment.
Do not get on skin or clothing.
Use only in an area equipped with a safety shower.
- Conditions for safe storage : Keep containers tightly closed in a dry, cool and well-ventilated place.
Store in original container.
- Materials to avoid : Do not store together with oxidizing and self-igniting products.

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Ingredients with workplace control parameters

Components	CAS-No.	Value type (Form of exposure)	Control parameters / Permissible concentration	Basis
ethyl 2-cyanoacrylate	7085-85-0	PEL	0.2 ppm 1.02 mg/m ³	CAL PEL
		TWA	0.2 ppm	ACGIH
		STEL	1 ppm	ACGIH
Carbon black	1333-86-4	TWA	3.5 mg/m ³	ACGIH
		TWA	3.5 mg/m ³	OSHA Z-1
		TWA	3.5 mg/m ³	OSHA P0
		TWA (Inhalable)	3 mg/m ³	ACGIH



Brute Strength. Professional Grade.™

SAFETY DATA SHEET

GorillaPro® CA500RT

Version 1.0

Revision Date 01/12/2022

		particulate matter)		
		PEL	3.5 mg/m ³	CAL PEL
hydroquinone	123-31-9	TWA	1 mg/m ³	ACGIH
		TWA	2 mg/m ³	OSHA Z-1
		TWA	2 mg/m ³	OSHA P0

Personal protective equipment

Respiratory protection : Use respiratory protection unless adequate local exhaust ventilation is provided or exposure assessment demonstrates that exposures are within recommended exposure guidelines.

Filter type : Combined particulates and organic vapor type

Hand protection

Material : Nitrile rubber

Remarks : Do not wear cotton or natural fiber gloves.

Eye protection

: Tightly fitting safety goggles
Ensure that eyewash stations and safety showers are close to the workstation location.

Skin and body protection

: Long sleeved clothing
Preventive skin protection

Protective measures

: Avoid contact with skin.

Hygiene measures

: Avoid contact with skin, eyes and clothing.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance

: liquid

Color

: black

Odor

: pungent

Odor Threshold

: No data available

Melting point/freezing point

: is not determined

Boiling point/boiling range

: is not determined

Flash point

: 80 °C Method: closed cup

Evaporation rate

: is not determined

Flammability (solid, gas)

: Not classified as a flammability hazard

Upper explosion limit

: Upper flammability limit
is not determined



Brute Strength. Professional Grade.™

Print Date 08/21/2020
Page 6 of 10

SAFETY DATA SHEET

GorillaPro® CA500RT

Version 1.0

Revision Date 01/12/2022

Lower explosion limit	:	Lower flammability limit is not determined
Density	:	ca. 1.05 g/cm ³
Solubility(ies)	:	
Water solubility	:	is not determined
Partition coefficient: n-octanol/water	:	No data available
Autoignition temperature	:	is not determined
Viscosity	:	
Viscosity, kinematic	:	is not determined

SECTION 10. STABILITY AND REACTIVITY

Chemical stability	:	The product is chemically stable.
Hazardous decomposition products	:	Stable under normal conditions.

SECTION 11. TOXICOLOGICAL INFORMATION

Acute toxicity

Product:

Acute dermal toxicity : Acute toxicity estimate : > 5,000 mg/kg
Method: Calculation method

Components:

hydroquinone:

Acute oral toxicity : LD50 Oral Rat: 320 mg/kg

Acute dermal toxicity : LD50 Dermal Rat: > 900 mg/kg

Skin corrosion/irritation

No data available

Serious eye damage/eye irritation

No data available

Respiratory or skin sensitization

No data available



Brute Strength. Professional Grade.™

Print Date 08/21/2020
Page 7 of 10

SAFETY DATA SHEET

GorillaPro® CA500RT

Version 1.0

Revision Date 01/12/2022

Germ cell mutagenicity

No data available

Carcinogenicity

No data available

Reproductive toxicity

No data available

STOT-single exposure

No data available

STOT-repeated exposure

No data available

Aspiration toxicity

No data available

SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity

Components: hydroquinone :

Toxicity to fish : LC50 (Oncorhynchus mykiss (rainbow trout)): 0.044 mg/l
Exposure time: 96 h
Test Method: flow-through test

Toxicity to daphnia and other : EC50 (Daphnia magna (Water flea)): 0.29 mg/l
aquatic invertebrates : Exposure time: 48 h
Test Method: static test

Toxicity to algae : EC50 (Pseudokirchneriella subcapitata (microalgae)): 0.335
mg/l
Exposure time: 72 h
Test Type: flow-through test

Persistence and degradability

No data available

Bioaccumulative potential

Mobility in soil

No data available



Brute Strength. Professional Grade.™

SAFETY DATA SHEET

GorillaPro® CA500RT

Version 1.0

Revision Date 01/12/2022

Other adverse effects

No data available

SECTION 13. DISPOSAL CONSIDERATIONS

Disposal methods

Waste from residues : Do not dispose of together with household waste.
Do not dispose of waste into sewer.
To the best of our knowledge, this product does not meet the definition of hazardous waste under the U.S. EPA Hazardous Waste Regulations 40 CFR 261. Disposal via incineration at an approved facility is recommended, as industry best practice. Consult state, local or provincial authorities for more restrictive requirements.

SECTION 14. TRANSPORT INFORMATION

Special precautions for user

Remarks : 49CFR: Not dangerous goods in non-bulk packaging.

Domestic regulation

49 CFR

UN/ID/NA number : 1993
Proper shipping name : Combustible liquid, n.o.s.
(ethyl 2-cyanoacrylate)
Class : CBL
Packing group : III
ERG Code : 128
Marine pollutant : no

International Regulations

UNRTDG

Not regulated as a dangerous good

IATA-DGR

Not regulated as a dangerous good

IMDG-Code

Not regulated as a dangerous good

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code



Brute Strength. Professional Grade.™

Print Date 08/21/2020
Page 9 of 10

SAFETY DATA SHEET

GorillaPro® CA500RT

Version 1.0

Revision Date 01/12/2022

Not applicable for product as supplied.

SECTION 15. REGULATORY INFORMATION

SARA 311/312 Hazards : Flammable (gases, aerosols, liquids, or solids)
Respiratory or skin sensitization
Carcinogenicity
Skin corrosion or irritation
Serious eye damage or eye irritation
Specific target organ toxicity (single or repeated exposure)

SARA 302 : This material does not contain any components with a section 302 EHS TPQ.

SARA 313 : This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

Clean Air Act

The following chemical(s) are listed as HAP under the U.S. Clean Air Act, Section 112 (40 CFR 61):

hydroquinone	123-31-9
--------------	----------

US State Regulations

California Prop 65 Please contact Supplier for more information.

The ingredients of this product are reported in the following inventories:

TSCA	All substances listed as active on the TSCA inventory
ENCS	On the inventory, or in compliance with the inventory
IECSC	On the inventory, or in compliance with the inventory

Inventories Legend TSCA (USA), DSL (Canada), REACH(Europe), AICS (Australia), NZIoC (New Zealand), ENCS (Japan), KECl (Korea), PICCS (Philippines), IECSC (China), TWINV (Taiwan)

SECTION 16. OTHER INFORMATION

Prepared by: Global Regulatory Department - phone: 1-651-236-5842 - email: msds.request@hbfuller.com



Brute Strength. Professional Grade.™

SAFETY DATA SHEET


GorillaPro® CA500RT

Version 1.0

Revision Date 01/12/2022

Further information

NFPA:



HMIS III:

HEALTH	2*
FLAMMABILITY	2
PHYSICAL HAZARD	0

0 = not significant, 1 =Slight,
2 = Moderate, 3 = High
4 = Extreme, * = Chronic

The information and recommendations set forth herein are believed to be accurate. Because some of the information is derived from information provided to the H.B. Fuller Company from its suppliers, and because the H.B. Fuller Company has no control over the conditions of handling and use, the H.B. Fuller Company makes no warranty, expressed or implied, regarding the accuracy of the data or the results to be obtained from the use thereof. The information is supplied solely for your information and consideration, and the H.B. Fuller Company assumes no responsibility for use or reliance thereon. It is the responsibility of the user of H.B. Fuller Company products to comply with all applicable federal, state and local laws and regulations.

Unless otherwise noted, trademarks are property of H.B. Fuller Company or one of its affiliated entities. Gorilla and GorillaPro are registered trademarks of The Gorilla Glue Company. © H.B. Fuller Company, 2022.