

# AT5 TIMING PULLEY BAR STOCK

AT5 mm Pitch  
Aluminum

METRIC TIMING PULLEY STOCK



Timing Pulley Stock

Part Number	No. of Teeth	Metric		Inch		Shank Diameter	Shank Length	Minimum Usable Length	Overall Length
		Pitch Diameter	Outside Diameter	Pitch Diameter	Outside Diameter				
12AT5-PS140A	12	19.1 mm	17.9 mm	0.752"	0.703"	0.500"	0.800"	5.500"	6.300"
13AT5-PS140A	13	20.7 mm	19.5 mm	0.814"	0.766"	0.500"	0.800"	5.500"	6.300"
14AT5-PS140A	14	22.3 mm	21.1 mm	0.877"	0.829"	0.500"	0.800"	5.500"	6.300"
15AT5-PS140A	15	23.9 mm	22.7 mm	0.940"	0.892"	0.500"	0.800"	5.500"	6.300"
16AT5-PS140A	16	25.5 mm	24.2 mm	1.002"	0.953"	0.500"	0.800"	5.500"	6.300"
17AT5-PS140A	17	27.1 mm	25.8 mm	1.065"	1.016"	0.500"	0.800"	5.500"	6.300"
18AT5-PS140A	18	28.7 mm	27.4 mm	1.128"	1.079"	0.500"	0.800"	5.500"	6.300"
19AT5-PS140A	19	30.2 mm	29.0 mm	1.190"	1.142"	0.500"	0.800"	5.500"	6.300"
20AT5-PS160A	20	31.8 mm	30.6 mm	1.253"	1.205"	0.500"	0.800"	6.300"	7.100"
21AT5-PS160A	21	33.4 mm	32.3 mm	1.315"	1.272"	0.500"	0.800"	6.300"	7.100"
22AT5-PS160A	22	35.0 mm	33.9 mm	1.378"	1.333"	0.500"	0.800"	6.300"	7.100"
23AT5-PS160A	23	36.6 mm	35.5 mm	1.441"	1.396"	0.500"	0.800"	6.300"	7.100"
24AT5-PS160A	24	38.2 mm	37.0 mm	1.504"	1.457"	0.500"	0.800"	6.300"	7.100"
25AT5-PS160A	25	39.8 mm	38.6 mm	1.566"	1.520"	0.500"	0.800"	6.300"	7.100"
26AT5-PS160A	26	41.4 mm	40.2 mm	1.628"	1.583"	0.500"	0.800"	6.300"	7.100"
27AT5-PS160A	27	43.0 mm	41.8 mm	1.691"	1.646"	0.500"	0.800"	6.300"	7.100"
28AT5-PS160A	28	44.6 mm	43.4 mm	1.754"	1.707"	0.500"	0.800"	6.300"	7.100"
29AT5-PS160A	29	46.2 mm	45.0 mm	1.817"	1.770"	0.500"	0.800"	6.300"	7.100"
30AT5-PS160A	30	47.8 mm	46.6 mm	1.880"	1.833"	0.750"	0.800"	6.300"	7.100"
31AT5-PS160A	31	49.3 mm	48.2 mm	1.941"	1.896"	0.750"	0.800"	6.300"	7.100"
32AT5-PS160A	32	50.9 mm	49.7 mm	2.005"	1.957"	0.750"	0.800"	6.300"	7.100"
33AT5-PS160A	33	52.5 mm	51.3 mm	2.067"	2.020"	0.750"	0.800"	6.300"	7.100"
34AT5-PS160A	34	54.1 mm	52.9 mm	2.130"	2.081"	0.750"	0.800"	6.300"	7.100"