

T2.5 TIMING BELTS

2.5 mm Pitch


Standard Widths:

4 mm, 6 mm, 8 mm, 10 mm, 12 mm

Polyurethane Construction

Steel Reinforcements

(Note: Custom belt widths are available upon request.)




Part Number	No. of Teeth	Pitch Length (mm)
T2.5/120	48	120.0
T2.5/145	58	145.0
T2.5/160	64	160.0
T2.5/177.5	71	177.5
T2.5/200	80	200.0
T2.5/210	84	210.0
T2.5/230	92	230.0
T2.5/245	98	245.0
T2.5/265	106	265.0

Part Number	No. of Teeth	Pitch Length (mm)
T2.5/285	114	285.0
T2.5/290	116	290.0
T2.5/305	122	305.0
T2.5/317.5	127	317.5
T2.5/330	132	330.0
T2.5/342.5	137	342.5
T2.5/380	152	380.0
T2.5/420	168	420.0
T2.5/480	192	480.0

Part Number	No. of Teeth	Pitch Length (mm)
T2.5/500	200	500.0
T2.5/540	216	540.0
T2.5/600	240	600.0
T2.5/650	260	650.0
T2.5/780	312	780.0
T2.5/915	366	915.0
T2.5/950	380	950.0
T2.5/990	396	990.0

Polyurethane T2.5 timing belt part numbers can be determined as follows:
Width Code + T2.5/ + Pitch Length Code

T pitch belts are very similar to imperial pitch belts and are commonly used for conveying applications. Due to the slightly deeper tooth engagement, the tooth meshing is more dependable, but these belts can be slightly more prone to backlash than imperial pitches.



For T2.5 pitch timing pulley stock and flanges, see page 276.



For T2.5 timing pulleys, see page 75.