

2 MM POWERHOUSE™ BELTS

(Compatible with PowerGrip® GT2® and PowerGrip® GT3® pitches)


Standard Widths:

3 mm, 6 mm, 9 mm

Neoprene Construction

Fiberglass Reinforcements

(Note: Custom belt widths are available upon request.)



Timing Belts




Part Number	No. of Teeth	Pitch Length (mm)
690-2P	345	690.0
696-2P	348	696.0
702-2P	351	702.0
726-2P	363	726.0
742-2P	371	742.0
744-2P	372	744.0
752-2P	376	752.0
760-2P	380	760.0
772-2P	386	772.0
782-2P	391	782.0
800-2P	400	800.0
810-2P	405	810.0
816-2P	408	816.0
848-2P	424	848.0
852-2P	426	852.0
860-2P	430	860.0
866-2P	433	866.0
892-2P	446	892.0
900-2P	450	900.0


Part Number	No. of Teeth	Pitch Length (mm)
930-2P	465	930.0
950-2P	475	950.0
956-2P	478	956.0
976-2P	488	976.0
994-2P	497	994.0
1004-2P	502	1004.0
1028-2P	514	1028.0
1032-2P	516	1032.0
1066-2P	533	1066.0
1068-2P	534	1068.0
1078-2P	539	1078.0
1110-2P	555	1110.0
1140-2P	570	1140.0
1164-2P	582	1164.0
1180-2P	590	1180.0
1210-2P	605	1210.0
1228-2P	614	1228.0
1234-2P	617	1234.0
1256-2P	628	1256.0

Part Number	No. of Teeth	Pitch Length (mm)
1310-2P	655	1310.0
1320-2P	660	1320.0
1344-2P	672	1344.0
1360-2P	680	1360.0
1386-2P	693	1386.0
1434-2P	717	1434.0
1524-2P	762	1524.0
1558-2P	779	1558.0
1660-2P	830	1660.0
1688-2P	844	1688.0
1700-2P	850	1700.0
1810-2P	905	1810.0
1850-2P	925	1850.0
1860-2P	930	1860.0
1910-2P	955	1910.0


Neoprene 2 mm POWERHOUSE™ timing belt part numbers can be determined as follows:
Pitch Length Code + -2P- + Width Code



For idler pulleys, see page 366.



For 2 mm POWERHOUSE™ pitch pulley stock and flanges, see page 308.



For 2 mm POWERHOUSE™ pitch timing pulleys, see page 121.