


# XL TIMING PULLEY FLANGES

0.200" / 5.08 mm Pitch  
Aluminum



Timing Pulley Flanges

Part Number	Metric				Inch			
	Inside Diameter	Outside Diameter	Stock Thickness	Overall Formed Thickness	Inside Diameter	Outside Diameter	Stock Thickness	Overall Formed Thickness
10XL-FA	12.8 mm	22.2 mm	1.0 mm	1.7 mm	0.503"	0.875"	0.040"	0.065"
11XL-FA	14.3 mm	23.8 mm	1.0 mm	1.7 mm	0.562"	0.938"	0.040"	0.065"
12XL-FA	14.3 mm	25.4 mm	1.0 mm	1.7 mm	0.562"	1.000"	0.040"	0.065"
13XL-FA	15.9 mm	27.0 mm	1.0 mm	1.7 mm	0.625"	1.063"	0.040"	0.065"
14XL-FA	17.4 mm	27.8 mm	1.0 mm	1.7 mm	0.684"	1.094"	0.040"	0.065"
15XL-FA	19.0 mm	30.2 mm	1.0 mm	1.7 mm	0.748"	1.188"	0.040"	0.065"
16XL-FA	20.6 mm	31.8 mm	1.0 mm	1.7 mm	0.810"	1.250"	0.040"	0.065"
17XL-FA	22.5 mm	33.4 mm	1.0 mm	1.7 mm	0.887"	1.313"	0.040"	0.065"
18XL-FA	23.8 mm	34.9 mm	1.0 mm	1.7 mm	0.936"	1.375"	0.040"	0.065"
19XL-FA	25.4 mm	36.5 mm	1.0 mm	1.7 mm	1.000"	1.438"	0.040"	0.065"
20XL-FA	27.0 mm	38.1 mm	1.0 mm	1.7 mm	1.062"	1.500"	0.040"	0.065"
21XL-FA	28.6 mm	39.7 mm	1.0 mm	1.7 mm	1.125"	1.563"	0.040"	0.065"
22XL-FA	29.5 mm	41.3 mm	1.0 mm	1.7 mm	1.160"	1.625"	0.040"	0.065"
23XL-FA	31.0 mm	42.9 mm	1.0 mm	1.7 mm	1.222"	1.688"	0.040"	0.065"
24XL-FA	31.0 mm	44.5 mm	1.0 mm	1.7 mm	1.222"	1.750"	0.040"	0.065"
25XL-FA	31.8 mm	46.1 mm	1.0 mm	1.7 mm	1.250"	1.813"	0.040"	0.065"
26XL-FA	34.2 mm	47.6 mm	1.0 mm	1.7 mm	1.347"	1.875"	0.040"	0.065"
28XL-FA	36.2 mm	50.8 mm	1.0 mm	1.7 mm	1.425"	2.000"	0.040"	0.065"
30XL-FA	39.4 mm	54.0 mm	1.0 mm	1.7 mm	1.550"	2.125"	0.040"	0.065"
32XL-FA	42.5 mm	57.2 mm	1.0 mm	1.7 mm	1.675"	2.250"	0.040"	0.065"



SAI GLOBAL  
ISO 9001  
Quality

B&B Manufacturing, Inc. is pleased to announce the certification of our Quality Management System to the ISO 9001:2008 standard. The certification of compliance with the ISO 9001:2008 standard recognizes that the policies, practices and procedures of B&B Manufacturing provide consistent quality in the products that we provide to our customers. B&B Manufacturing engaged in a demanding and detailed evaluation process of our entire quality management system with SAI Global. This evaluation reviewed system development, documentation, internal audits, clearance of non-conformances and every quality management procedure in the company. This proactive decision to become ISO 9001:2008 certified demonstrates our commitment to providing our customers with high quality precision mechanical components and power transmission products. It is another step in its commitment to continual improvement and customer service.