



# L TIMING PULLEY BAR STOCK

0.375" / 9.525 mm Pitch  
Steel



Timing Pulley Stock

Part Number	No. of Teeth	Metric		Inch		Shank Diameter	Shank Length	Minimum Usable Length	Overall Length
		Pitch Diameter	Outside Diameter	Pitch Diameter	Outside Diameter				
10L-PS8S	10	30.3 mm	29.6 mm	1.194"	1.164"	0.750"	0.750"	8.000"	8.750"
11L-PS8S	11	33.4 mm	32.6 mm	1.313"	1.283"	0.750"	0.750"	8.000"	8.750"
12L-PS8S	12	36.4 mm	35.6 mm	1.432"	1.402"	1.000"	1.000"	8.000"	9.000"
13L-PS8S	13	39.4 mm	38.7 mm	1.552"	1.522"	1.000"	1.000"	8.000"	9.000"
14L-PS8S	14	42.4 mm	41.7 mm	1.671"	1.641"	1.000"	1.000"	8.000"	9.000"
15L-PS8S	15	45.5 mm	44.7 mm	1.790"	1.760"	1.000"	1.000"	8.000"	9.000"
16L-PS8S	16	48.5 mm	47.8 mm	1.910"	1.880"	1.000"	1.000"	8.000"	9.000"
17L-PS8S	17	51.5 mm	50.8 mm	2.029"	1.999"	1.000"	1.000"	8.000"	9.000"
18L-PS8S	18	54.6 mm	53.8 mm	2.149"	2.119"	1.000"	1.000"	8.000"	9.000"
19L-PS8S	19	57.6 mm	56.8 mm	2.268"	2.238"	1.000"	1.000"	8.000"	9.000"
20L-PS8S	20	60.6 mm	59.9 mm	2.387"	2.357"	1.000"	1.000"	8.000"	9.000"
21L-PS8S	21	63.7 mm	62.9 mm	2.507"	2.477"	1.000"	1.000"	8.000"	9.000"
22L-PS8S	22	66.7 mm	65.9 mm	2.626"	2.596"	1.000"	1.000"	8.000"	9.000"
23L-PS8S	23	69.7 mm	69.0 mm	2.745"	2.715"	1.000"	1.000"	8.000"	9.000"
24L-PS8S	24	72.8 mm	72.0 mm	2.865"	2.835"	1.000"	1.000"	8.000"	9.000"
25L-PS8S	25	75.8 mm	75.1 mm	2.985"	2.955"	1.000"	1.000"	8.000"	9.000"
26L-PS8S	26	78.8 mm	78.1 mm	3.104"	3.074"	1.000"	1.000"	8.000"	9.000"



For matching L pitch belts, see page 194.



For L pitch timing pulleys, see page 30.