

T10 TIMING BELTS

10 mm Pitch

Standard Widths:


10 mm, 12 mm, 16 mm, 20 mm,

25 mm, 32 mm, 50 mm

Polyurethane Construction

Steel Reinforcements

(Note: Custom belt widths are available upon request.)



Part Number	No. of Teeth	Pitch Length (mm)
T10/260	26	260.0
T10/320	32	320.0
T10/350	35	350.0
T10/370	37	370.0
T10/400	40	400.0
T10/410	41	410.0
T10/440	44	440.0
T10/450	45	450.0
T10/500	50	500.0
T10/530	53	530.0
T10/550	55	550.0
T10/560	56	560.0
T10/600	60	600.0
T10/610	61	610.0
T10/630	63	630.0
T10/650	65	650.0
T10/660	66	660.0
T10/690	69	690.0
T10/700	70	700.0
T10/720	72	720.0
T10/750	75	750.0
T10/780	78	780.0
T10/800	80	800.0

Part Number	No. of Teeth	Pitch Length (mm)
T10/810	81	810.0
T10/840	84	840.0
T10/850	85	850.0
T10/880	88	880.0
T10/890	89	890.0
T10/900	90	900.0
T10/910	91	910.0
T10/920	92	920.0
T10/950	95	950.0
T10/960	96	960.0
T10/970	97	970.0
T10/980	98	980.0
T10/1000	100	1000.0
T10/1010	101	1010.0
T10/1050	105	1050.0
T10/1080	108	1080.0
T10/1100	110	1100.0
T10/1110	111	1110.0
T10/1140	114	1140.0
T10/1150	115	1150.0
T10/1200	120	1200.0
T10/1210	121	1210.0
T10/1240	124	1240.0

Part Number	No. of Teeth	Pitch Length (mm)
T10/1250	125	1250.0
T10/1300	130	1300.0
T10/1320	132	1320.0
T10/1350	135	1350.0
T10/1390	139	1390.0
T10/1400	140	1400.0
T10/1420	142	1420.0
T10/1440	144	1440.0
T10/1450	145	1450.0
T10/1460	146	1460.0
T10/1500	150	1500.0
T10/1560	156	1560.0
T10/1600	160	1600.0
T10/1610	161	1610.0
T10/1700	170	1700.0
T10/1750	175	1750.0
T10/1780	178	1780.0
T10/1800	180	1800.0
T10/1880	188	1880.0
T10/1960	196	1960.0
T10/2250	225	2250.0

Polyurethane T10 timing belt part numbers can be determined as follows:
Width Code + T10/ + Pitch Length Code