


# 3 MM POWERHOUSE™ HTD® TIMING PULLEY BAR STOCK

3 mm Pitch  
Aluminum



Part Number	No. of Teeth	Metric		Inch		Shank Diameter	Shank Length	Minimum Usable Length	Overall Length
		Pitch Diameter	Outside Diameter	Pitch Diameter	Outside Diameter				
75-3M-PS8A	75	71.8 mm	70.9 mm	2.826"	2.790"	0.750"	0.750"	8.000"	8.750"
80-3M-PS8A	80	76.4 mm	75.6 mm	3.008"	2.978"	0.750"	0.750"	8.000"	8.750"
90-3M-PS8A	90	86.0 mm	85.2 mm	3.384"	3.354"	0.750"	0.750"	8.000"	8.750"
100-3M-PS8A	100	95.5 mm	94.7 mm	3.760"	3.730"	0.750"	0.750"	8.000"	8.750"
110-3M-PS8A	110	105.1 mm	104.3 mm	4.136"	4.106"	0.750"	0.750"	8.000"	8.750"
120-3M-PS8A	120	114.6 mm	113.8 mm	4.511"	4.481"	0.750"	0.750"	8.000"	8.750"
130-3M-PS8A	130	124.1 mm	123.4 mm	4.887"	4.857"	0.750"	0.750"	8.000"	8.750"
140-3M-PS8A	140	133.7 mm	132.9 mm	5.263"	5.233"	0.750"	0.750"	8.000"	8.750"
150-3M-PS8A	150	143.2 mm	142.5 mm	5.639"	5.609"	0.750"	0.750"	8.000"	8.750"
160-3M-PS8A	160	152.8 mm	152.0 mm	6.015"	5.985"	0.750"	0.750"	8.000"	8.750"

## Are you looking for expertly crafted miniature components?

B&B Manufacturing prides ourselves on offering superior mechanical components at low factory prices from our highly skilled machinists. B&B provides the expert product information you need, when you need it. For more information on miniature precision mechanical components, B&B Manufacturing engineers are only an email or phone call away from providing the support and product information you need to make informed decisions. Our engineering and application support, shortened lead times, lean enterprise, low factory prices, custom component capabilities, and industry applications sets B&B Manufacturing apart from other precision mechanical component manufacturers and distributors. B&B Manufacturing is constantly adding services, features, and improvement programs in order to help us better serve our mechanical parts customers.