

L TIMING BELTS

0.375" Pitch


Standard Widths:

1/2", 3/4", and 1"

Neoprene Construction

Fiberglass Reinforcements

(Note: Custom belt widths are available upon request.)



Part Number	No. of Teeth	Pitch Length (in)
98L	26	9.750
109L	29	10.875
124L	33	12.375
135L	36	13.500
150L	40	15.000
154L	41	15.375
157L	42	15.750
165L	44	16.500
169L	45	16.875
172L	46	17.250
176L	47	17.625
187L	50	18.750
195L	52	19.500
199L	53	19.875
203L	54	20.250
206L	55	20.625
210L	56	21.000
218L	58	21.750
225L	60	22.500
232L	62	23.250
236L	63	23.625
240L	64	24.000
244L	65	24.375
247L	66	24.750
251L	67	25.125

Part Number	No. of Teeth	Pitch Length (in)
255L	68	25.500
259L	69	25.875
263L	70	26.250
270L	72	27.000
277L	74	27.750
285L	76	28.500
300L	80	30.000
304L	81	30.375
315L	84	31.500
320L	85	31.875
322L	86	32.250
334L	89	33.375
337L	90	33.750
345L	92	34.500
352L	94	35.250
360L	96	36.000
367L	98	36.750
375L	100	37.500
382L	102	38.250
390L	104	39.000
394L	105	39.375
405L	108	40.500
420L	112	42.000
424L	113	42.375
427L	114	42.750

Part Number	No. of Teeth	Pitch Length (in)
435L	116	43.500
436L	116	43.500
439L	117	43.875
446L	119	44.625
450L	120	45.000
454L	121	45.375
465L	124	46.500
480L	128	48.000
510L	136	51.000
514L	137	51.375
525L	140	52.500
540L	144	54.000
548L	146	54.750
570L	152	57.000
581L	155	58.125
600L	160	60.000
605L	161	60.375
619L	165	61.875
630L	168	63.000
640L	171	64.125
653L	174	65.250
660L	176	66.000
697L	186	69.750
720L	192	72.000
728L	194	72.750

Neoprene L timing belt part numbers can be determined as follows:
Pitch Length Code + L + Width Code + (G for fiberGlass reinforcements)