

# 3V V-BELT SHEAVES

For 3V V-Belts

1 Groove

0.688" Face Width


Cast Iron

QD® Style




Part Number	Type	Pitch Dia. "3V" Belts (in)	Out. Dia. (in)	Bushing	Bore Range	E	L	M	Wt. Ea. (Lbs.)
13V220JA	E1	2.15	2.20	JA	0.500" - 1.250"	0.625	1.000	0.938	0.4
13V235JA	E1	2.30	2.35	JA	0.500" - 1.250"	0.594	1.000	0.906	0.4
13V250JA	E1	2.45	2.50	JA	0.500" - 1.250"	0.594	1.000	0.906	0.5
13V265JA	D1	2.60	2.65	JA	0.500" - 1.250"	0.375	1.000	0.063	0.6
13V280JA	D1	2.75	2.80	JA	0.500" - 1.250"	0.375	1.000	0.063	0.7
13V300JA	D1	2.95	3.00	JA	0.500" - 1.250"	0.375	1.000	0.063	0.8
13V315JA	D1	3.10	3.15	JA	0.500" - 1.250"	0.375	1.000	0.063	0.9
13V335JA	D1	3.30	3.35	JA	0.500" - 1.250"	0.375	1.000	0.063	1.0
13V365SH	D1	3.60	3.65	SH	0.500" - 1.625"	0.656	1.313	0.031	1.3
13V412SH	D1	4.07	4.12	SH	0.500" - 1.625"	0.656	1.313	0.031	1.8
13V450SH	D1	4.45	4.50	SH	0.500" - 1.625"	0.656	1.313	0.031	2.1
13V475SH	D1	4.70	4.75	SH	0.500" - 1.625"	0.656	1.313	0.031	2.4
13V500SH	D1	4.95	5.00	SH	0.500" - 1.625"	0.656	1.313	0.031	2.7
13V530SH	D1	5.25	5.30	SH	0.500" - 1.625"	0.656	1.313	0.031	2.9
13V560SH	D2	5.55	5.60	SH	0.500" - 1.625"	0.656	1.313	0.031	3.0
13V600SH	D2	5.95	6.00	SH	0.500" - 1.625"	0.656	1.313	0.031	3.2
13V650SH	D2	6.45	6.50	SH	0.500" - 2.000"	0.656	1.313	0.031	4.2
13V690SH	D3	6.85	6.90	SH	0.500" - 2.000"	0.656	1.313	0.031	4.4
13V800SDS	D3	7.95	8.00	SDS	0.500" - 2.000"	0.656	1.313	0.031	5.8
13V1060SDS	D3	10.55	10.60	SDS	0.500" - 2.000"	0.656	1.313	0.031	7.9
13V1400SK	C3	13.95	14.00	SK	0.500" - 2.625"	0.781	1.938	0.469	14.8
13V1900SK	C3	18.95	19.00	SK	0.500" - 2.625"	0.781	1.938	0.469	24.0

TYPE C



TYPE D



TYPE E

