

L TIMING PULLEYS

0.375" Trapezoidal Pitch


For 1" Wide Belts

Hub and Flanges


Steel/Iron

Black Oxide Plating

Minimum Plain Bore



Part Number	No. of Teeth	Type	Pitch Dia (in)	Out. Dia (in)	Flange Dia. (in)	Bore (in)	Face Width (in)	Overall Length (in)	Hub Dia. (in)
13L100-6FS5	13	6F	1.552	1.522	1.781	0.375	1.250	1.750	1.125
14L100-6FS5	14	6F	1.671	1.641	1.906	0.375	1.250	1.750	1.125
15L100-6FS6	15	6F	1.790	1.760	2.031	0.500	1.250	1.750	1.344
16L100-6FS6	16	6F	1.910	1.880	2.125	0.500	1.250	1.750	1.437
17L100-6FS6	17	6F	2.029	1.999	2.250	0.500	1.250	1.750	1.437
18L100-6FS6	18	6F	2.149	2.119	2.375	0.500	1.250	1.750	1.563
19L100-6FS6	19	6F	2.268	2.238	2.500	0.500	1.250	1.750	1.687
20L100-6FS6	20	6F	2.387	2.357	2.625	0.500	1.250	1.750	1.687
21L100-6FS7	21	6F	2.507	2.477	2.750	0.625	1.250	1.750	2.000
22L100-6FS7	22	6F	2.626	2.596	2.875	0.625	1.250	1.750	2.000
24L100-6FS7	24	6F	2.865	2.835	3.094	0.625	1.250	1.750	2.250
26L100-6FS7	26	6F	3.104	3.074	3.330	0.625	1.250	1.750	2.250
28L100-6FS7	28	6F	3.342	3.312	3.566	0.625	1.250	1.750	2.250
30L100-6FS7	30	6F	3.581	3.551	3.800	0.625	1.250	1.750	2.250
32L100-6FS7	32	6F	3.820	3.790	4.044	0.625	1.250	1.750	2.625
36L100-6FS7	36	6F	4.297	4.267	4.520	0.625	1.250	1.750	3.500
40L100-6FS7	40	6F	4.775	4.745	5.000	0.625	1.250	1.750	3.625



Our veteran sales staff is available to help you make informed decisions on which precision mechanical or power transmission components are best for your project.

Let us help you!
Call us today!

