



H TIMING PULLEY FLANGES

0.500" Pitch
Steel



Timing Pulley Flanges

Part Number	Metric				Inch			
	Inside Diameter	Outside Diameter	Stock Thickness	Overall Formed Thickness	Inside Diameter	Outside Diameter	Stock Thickness	Overall Formed Thickness
14H-FS	44.6 mm	62.5 mm	2.3 mm	3.2 mm	1.754"	2.461"	0.090"	0.125"
16H-FS	54.1 mm	70.6 mm	2.3 mm	3.2 mm	2.129"	2.780"	0.090"	0.125"
17H-FS	57.3 mm	74.6 mm	2.3 mm	3.2 mm	2.255"	2.938"	0.090"	0.125"
18H-FS	60.4 mm	78.7 mm	2.3 mm	3.2 mm	2.379"	3.100"	0.090"	0.125"
19H-FS	63.6 mm	82.7 mm	2.3 mm	3.2 mm	2.504"	3.256"	0.090"	0.125"
20H-FS	66.8 mm	86.9 mm	2.3 mm	3.2 mm	2.629"	3.420"	0.090"	0.125"
21H-FS	71.6 mm	90.8 mm	2.3 mm	3.2 mm	2.817"	3.574"	0.090"	0.125"
22H-FS	76.3 mm	94.9 mm	2.3 mm	3.2 mm	3.004"	3.735"	0.090"	0.125"
24H-FS	85.8 mm	102.9 mm	2.3 mm	3.2 mm	3.379"	4.050"	0.090"	0.125"
26H-FS	92.2 mm	111.0 mm	2.3 mm	3.2 mm	3.629"	4.369"	0.090"	0.125"
28H-FS	95.4 mm	119.0 mm	2.3 mm	3.2 mm	3.754"	4.687"	0.090"	0.125"
30H-FS	101.7 mm	127.1 mm	2.3 mm	3.2 mm	4.004"	5.005"	0.090"	0.125"
32H-FS	114.4 mm	135.1 mm	2.3 mm	3.2 mm	4.504"	5.320"	0.090"	0.125"
36H-FS	128.7 mm	151.4 mm	2.3 mm	3.2 mm	5.067"	5.959"	0.090"	0.125"
40H-FS	143.0 mm	167.6 mm	2.3 mm	3.2 mm	5.629"	6.600"	0.090"	0.125"
44H-FS	158.9 mm	183.7 mm	2.3 mm	3.2 mm	6.254"	7.231"	0.090"	0.125"
48H-FS	174.7 mm	199.8 mm	2.3 mm	3.2 mm	6.879"	7.867"	0.090"	0.125"



For matching
H pitch belts,
see page 199.



For H pitch
timing pulleys,
see page 48.

B&B Manufacturing offers a free online service
for locating and downloading CAD models in most CAD file formats.

Find this convenient engineering tool and others on our website at www.bbman.com.