

8 MM POWERHOUSE™ HTD® BELTS

Standard Widths:

20 mm, 30 mm, 50 mm, 85 mm

Neoprene Construction

Fiberglass Reinforcements

(Note: Custom belt widths are available upon request.)



Timing Belts




Part Number	No. of Teeth	Pitch Length (mm)
1424-8M	178	1424.0
1432-8M	179	1432.0
1440-8M	180	1440.0
1480-8M	185	1480.0
1512-8M	189	1512.0
1520-8M	190	1520.0
1552-8M	194	1552.0
1600-8M	200	1600.0
1680-8M	210	1680.0
1696-8M	212	1696.0
1728-8M	216	1728.0
1760-8M	220	1760.0
1800-8M	225	1800.0


Part Number	No. of Teeth	Pitch Length (mm)
1896-8M	237	1896.0
1904-8M	238	1904.0
1936-8M	242	1936.0
2000-8M	250	2000.0
2056-8M	257	2056.0
2080-8M	260	2080.0
2104-8M	263	2104.0
2160-8M	270	2160.0
2200-8M	275	2200.0
2240-8M	280	2240.0
2248-8M	281	2248.0
2272-8M	284	2272.0
2288-8M	286	2288.0

Part Number	No. of Teeth	Pitch Length (mm)
2400-8M	300	2400.0
2504-8M	313	2504.0
2600-8M	325	2600.0
2800-8M	350	2800.0
3048-8M	381	3048.0
3200-8M	400	3200.0
3280-8M	410	3280.0
3360-8M	420	3360.0
3600-8M	450	3600.0
3824-8M	478	3824.0
4400-8M	550	4400.0
4464-8M	558	4464.0
4960-8M	620	4960.0

Neoprene 8 mm POWERHOUSE™ HTD® timing belt part numbers can be determined as follows:
Pitch Length Code + -8M- + Width Code



For idler pulleys, see page 366.



For 8 mm POWERHOUSE™ HTD® pitch pulley stock and flanges, see page 302.



For 8 mm POWERHOUSE™ HTD® pitch timing pulleys, see page 110.